Clean Tubing: Polyolefin Tubing TPH Series



Model/Specifications

● — 20 m roll □ — 100 m roll



Complies with FDA (U.S. Food and Drug Administration) §175.300 dissolution test

	Applicable —: Non-conformance
White (W)	•
Black (B)	—
Red (R)	—
Blue (BU)	•
Yellow (Y)	•
Green (G)	—


Model		TPH0425	TPH0604	TPH0806	TPH1075	TPH1209	
O.D. (mm)	4	6	8	10	12	
I.D. (mm)		2.5	4	6	7.5	9	
White (W))	—— • ——	— •	•	——•	— •	
Black (B)		—— • ——	— •	•	——•	— •	
Red (R)		——•	— <u> </u>	——•	— <u> </u>	—— • —	
Blue (BU))	——•	— <u> </u>	——•	—— <u> </u>	—— • —	
Yellow (Y)	— <u></u>	•	•	— <u></u>	•	
Green (G))			•			
Fluid Note 1)							
Fluid Note I)		Air/N2/Water/DI water (Pure water)					
Max. operating	20°C	1	1	0.7	0.7	0.7	
	40°C	0.8	0.8	0.57	0.57	0.57	
pressure (MPa)	60°C	0.6	0.6	0.43	0.43	0.43	
<u> </u>	80°C	0.4	0.4	0.3	0.3	0.3	
Operating vacuum pressure (kPa) Note 2)		- 101.3					
Min. bending radius	mm) Note 3)	15	25	35	45	55	
Applicable fittings Note 1)		Clean one-touch fittings One-touch fittings, Metal: KQB2 series One-touch fittings, Stainless steel 316: KQG2 series Insert fittings					
Operating temp	erature	– 20 to 80°C, For water 5 to 80°C					
Material Note 4)		Polyolefin resin					

must be no more than the maximum operating pressure. A surge pressure higher than the maximum operating pressure can cause breakage of the fitting or bursting of the tubing. Furthermore, abnormal temperature rise caused by adiabatic compression may result in the tube bursting.

Note 2) The operating vacuum pressure varies depending on the applicable fitting, so refer to the fitting specifications for details. Note 3) The minimum bending radius indicates the value at a temperature of 20°C with an outside diameter rate of change of 10% or less


Note 4) Polyolefin resin is not suitable for regular pneumatic equipment piping because it is not resistant to mineral oil.

Max. Operating Pressure



Made to Order

How to Order



Length per roll

symbol	Length		
20	20 m roll		
100	100 m roll		

(Please contact SMC for specifications in detail, dimensions, delivery and specifications other than those mentioned above.)

500 m longer length reel ø6, Black, White, and Blue only: Suffix "-X40" to the end of part number. Ex.) TPH0604B-500-X40

