
Specialized Product **PG**. information

High Vacuum Angle Valve/ Manual Lever Operation Type **XLH/XMH-X163**



Specifications

∧ Caution

Valve type	Manual (Lever type)
Shaft seal type	Bellows seal
Operating pressure range	Atmospheric pressure to 1 x 10 ⁻⁶ Pa
Fluid	Inert gas under vacuum
Internal leakage	1.3 x 10 ⁻¹⁰ Pa⋅m ³ /s or less ^{*1}
External leakage	1.3 x 10 ⁻¹¹ Pa⋅m ³ /s or less ^{*1}
Operating temperature	5 to 150°C
Conductance	5 L/s*2
Flange	KF16

*1 The value at normal temperature, excluding gas permeation

*2 The conductance value is the value at the "molecular flow" of an elbow with the same dimensions.



SMC Corporation 4-14-1, SOTO-KANDA, CHIYODA-KU, TOKYO 101-0021, JAPAN URL: https://www.smcworld.com ©2020 SMC Corporation All Rights Reserved

"Safety Instructions" in our "Best Pneumatics" catalog before use.

To ensure the safest possible operation of this product, please be sure to thoroughly read the