


Specialized Product **PG**. information

Compact 2-Port Solenoid Valve SX21-X2



Specifications

Valve specifications	Valve construction		Direct-operated poppet
	Fluid		Air
	Orifice diameter	mmø	1
	Operating pressure	range MPa	0 to 0.7
	Flow rate characteristics	С	0.14
		b	0.4
		Cv	0.04
	Ambient temperature °C		-10 to 50
	Fluid temperature °C		1 to 50 (No freezing)
	Environment		Location without the presence of corrosive gases or explosive gases
	Leakage rate cm ³ /min (ANR)		1 or less
	Fluid contact material		Stainless steel, Resin, NBR
Coil specifications	Rated voltage V		24 VDC
	Allowable voltage fluctuation V		$\pm 10\%$ of the rated voltage
	Power consumption W		1.5

▲ Caution

To ensure the safest possible operation of this product, please be sure to thoroughly read the "Safety Instructions" in our "Best Pneumatics" catalog before use.



SMC Corporation 4-14-1, SOTO-KANDA, CHIYODA-KU, TOKYO 101-0021, JAPAN URL: https://www.smcworld.com ©2020 SMC Corporation All Rights Reserved