Diaphragm Valve for Ultra High Purity Air Operated Type AZ3542 & 4542 25A Series

 Suitable for UHP gas supply line Body material: 316L SS Pneumatically actuated normally closed **How to Order** (Inlet) (Outlet) AZ 3 542 S 2P MV4 25A Size Series compatible with Code Cv secondary batteries 3 0.29 4 0.5 Model • Connections Code Status Maximum operating pressure AZ3 AZ4 Size Normally closed 125 psig Code Connections 542 2PW 2P 2PW 2P Port (0.9 MPa) (N.C.) MV4 1/4 inch face seal (Male) Material FV4 1/4 inch face seal (Female) Code Body material TW4 1/4 inch tube weld 316L SS S MV6 3/8 inch face seal (Male)

FV6

TW6

TW8

 Code
 Ports
 Connection

 2P
 2 ports
 Machined

 2PW
 Welded

Ports 4

Only available with the same type fittings inlet and outlet.

3/8 inch face seal (Female)

3/8 inch tube weld

1/2 inch tube weld

* 1) Fixed fitting (no rotating nut)

Specifications

Operating Parameters	AZ3542□25A	AZ4542□25A
Weight	0.26 kg *1)	

^{*1)} Weight for AZ3542S2PMV4MV4 including individual boxed weight. It may vary depending on connections or options.


 Some parts have sizes and shapes that are different from the standard products.


For details, refer to the Web Catalog.

Dimensions


AZ3542 & 4542

Ports: 2P (Machined)






Connections: MV□





Connections: TW□




Ports	Connections	Α	В	
2P (Machined)	MV4	1.14 (29.0)	1.12 sq. (28.4)	
	TW4	0.875 (22.2)		
	MV6	1.5 (38.1)	1.48 sq. (37.6)	
	TW6	0.875 (22.2)	1.12 sq. (28.4)	
	TW8	1.125 (28.6)	1.12 Sq. (20.4)	

Ports: 2PW (Welded)






Connections: MV□




Connections: TW□



Ports	Connections	Α	
2PW (Welded)	MV4	1.39 (35.3)	
	FV4		
	TW4	1.06 (26.9)	
	MV6	1.93 (49.0)	
	FV6		
	TW6	1.325 (33.7)	



Diaphragm Valves for General Applications Air Operated Type AK3542 & 4542 25A Series



^{*} Specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.