
# **Membrane Air Dryer**

# 25A-IDG Series

# Single Unit/Standard Dew Point –40°C/–60°C Specifications





# **Bracket Assembly (Accessory) Part Nos.**

Part no.	Applicable model
25A-BM64	25A-IDG30LA, 50LA
25A-BM65	25A-IDG60LA, 75LA, 100LA

<sup>\*</sup> The assembly consists of a bracket and 2 mounting screws.


\* Some parts have dimensions that are different from those of the standard model. Refer to page 228 for details. Other specifications are the same as those of the standard model.


For details, refer to the Web Catalog.




# Membrane Air Dryer 25A-IDG Series


# **Dimensions**





25A-IDG60LA 25A-IDG75LA 25A-IDG100LA





Model



# **Compressed Air Preparation Filter**

Line Filter/Mist Separator/Micro Mist Separator

# 25A-AFF/AM/AMD-D Series










**How to Order** 

FF AM

AME



Option/Semi-standard: Select one each for a to c.
Option/Semi-standard symbol: When more than one specification is required, indicate in alphanumeric order.
Example) 25A-AM30-N03B-RZ-D

Series compatible with secondary batteries

	Sy						2			
			Symbol Description		Description	Body size				
					20	30	40	50	60	
				AFF	Nominal filtration rating: 1 μm					
				AFF	Water droplet removal ratio: 99%		_			
Ω			Filter type	AM	Nominal filtration rating: 0.1 μm					
v			riiter type	AW	Oil mist concentration on the outlet side: 1 mg/m <sup>3</sup>		•			
				AMD	Nominal filtration rating: 0.01 μm					
				AMD	Oil mist concentration on the outlet side: 0.1 mg/m <sup>3</sup>		•			•
				+						
				Nil	Rc	•	•	•	•	•
8			Thread type	N	NPT	•	•	•	•	•
				F	G	•	•	•	•	•
+										
				01	1/8	•	_	_	_	_
				02	1/4	•	•	•	_	_
A		Port size		03	3/8	_	•	•	_	_
U			1 011 3126	04	1/2	_	_	•	_	_
				06	3/4	_	_		•	_
				10	1	_	_	_	•	•
				+						
6	Option	а	Mounting	Nil	Without mounting option	•	•	•	•	•
lacksquare	O Nour tilling		B*1	With bracket	•	•	•	•	•	
				+						
	rg l	b	Flow direction	Nil	Flow direction: Left to right	•	•	•	•	•
	nde		1 low direction	R	Flow direction: Right to left	•	•	•	•	•
6	Semi-standard			+						
	emi	С	Unit	Nil	Name plate and caution plate for bowl in SI units: MPa, °C	•	•	•	•	•
	S C	Offic	<b>Z</b> *2	Name plate and caution plate for bowl in imperial units: psi, °F	○*3	○*3	○*3	○*3	○*3	

<sup>\*1</sup> Option B is included in the package with the product but does not come assembled. The assembly consists of 2 types of the bracket and 2 mounting screws.

This product is for overseas use only according to the new Measurement Act. (The SI unit type is provided for use in Japan.)

## 25A-Bracket, Bowl Assembly/Part Nos.

Description	Size 20	Size 30	Size 40	Size 50	Size 60
Bracket assembly*1	25A-AF24P-070AS	25A-AF34P-070AS	25A-AF44P-070AS	25A-AF54	IP-070AS
Bowl assembly	25A-C2SF-D	25A-C3SF-D	25A-C4SF-D	25A-AM54P-120AS	25A-AM64P-120AS

<sup>\*1</sup> The assembly consists of a bracket A/B and 2 mounting screws.



<sup>\*2</sup> For pipe thread type: NPT

<sup>\*3</sup> O: For pipe thread type: NPT only

<sup>\*</sup> The 25A- series specifications and dimensions are the same as those of the standard model.

# **Compressed Air Preparation Filter**


**Activated Carbon Filter** 

# 25A-AMK-D Series





# **How to Order**



Option/Semi-standard: Select one each for a to c.
Option/Semi-standard symbol: When more than one specification is required, indicate in alphanumeric order.
Example) 25A-AMK30-N03B-RZ-D

Series compatible with secondary batteries

			2 mbd					2			
	Syr		Symbol	Description		Body size					
					20	30	40	50	60		
0			Filter type	AMK	Activated carbon filter	•	•	•	•	•	
				+							
				Nil	Rc	•	•	•	•	•	
8			Thread type	N	NPT	•	•	•	•	•	
				F	G	•	•	•	•	•	
				+							
	Port size		01	1/8	•	_	_	_	_		
			02	1/4	•	•	•	_	_		
4			03	3/8	_	•	•	_	_		
U		FUIT SIZE	04	1/2	_	_	•	_	_		
			06	3/4	_	_	_	•	_		
				10	1	_	_	_	•	•	
	+										
•	ioi		Manustina	Nil	Without mounting option	•	•	•	•	•	
Ð	5 in the control of t		B*1	With bracket	•	•	•	•	•		
				+							
	5	<b>L</b>	Flow direction	Nil	Flow direction: Left to right	•	•	•	•	•	
	nda	b	riow direction	R	Flow direction: Right to left	•	•	•	•	•	
6	Semi-standard			+							
	Ë		Proceure unit	Nil	Name plate and caution plate in SI units: MPa/°C	•	•	•	•	•	
	S C	Pressure unit	Pressure unit	<b>Z</b> *2	Name plate and caution plate in imperial units: psi/°F	O*3	○*3	○*3	○*3	○*3	

<sup>\*1</sup> Option B is included in the package with the product but does not come assembled. The assembly consists of 2 types of the bracket and 2 mounting screws.

25A-Bracket, Bowl Assembly/Part Nos.

	,					
Description	Size 20	Size 30	Size 40	Size 50	Size 60	
Bracket assembly*1	25A-AF24P-070AS	25A-AF34P-070AS	25A-AF44P-070AS	25A-AF54P-070AS		
Bowl assembly	25A-C2SF-D-X401	25A-C3SK-D	25A-C4SK-D	Equivalent to the standard product	Equivalent to the standard product	

<sup>\*1</sup> The assembly consists of a bracket A/B and 2 mounting screws.



<sup>\*2</sup> For pipe thread type: NPT

This product is for overseas use only according to the new Measurement Act. (The SI unit type is provided for use in Japan.)


<sup>\*3</sup> O: For pipe thread type: NPT only

<sup>\*</sup> The 25A- series specifications and dimensions are the same as those of the standard model.

# **Main Line Filter** 25A-AFF Series RoHS







10

1

25A-AFF8C

25A-AFF11C

25A-AFF22C

25A-AM-BM103


25A-AM-BM104

25A-AM-BM105

Symbol Description

Nil

В



## Bracket Assembly Part Nos.\*3

Applicable model	Part no.
25A-AFF37B	25A-BM56
25A-AFF75B	25A-BM57

<sup>\*3</sup> The assembly consists of a bracket and 2 mounting screws.

can be selected. The drain cock, N.O. auto drain and drain guide cannot be selected together.

\* The 25A- series specifications and dimensions

are the same as those of the standard model.



<sup>\*3</sup> The assembly consists of a bracket and 2 mounting screws.


Bracket \*2 \*2 When symbol "B" is indicated, a bracket assembly with a part number shown in the left table is shipped together as an accessory but does not come assembled

assembly with a part number shown in the left table is shipped together as an accessory but does not come assembled.

# **Mist Separator** 25A-AM Series







### Bracket Assembly Part Nos.\*3

Applicable model	Part no.
25A-AM150C	25A-AM-BM101
25A-AM250C	25A-AM-BM102
25A-AM350C	25A-AM-BM103
25A-AM450C	25A-AM-BM104
25A-AM550C	25A-AM-BM105

<sup>\*3</sup> The assembly consists of a bracket and 2 mounting screws.

### Port size

Cumbal	Cizo	Ap	plica	ble bo	ody si	ze
Symbol	Size	150C	250C	350C	450C	550C
01	1/8		_	_	_	
02	1/4	•		_	_	_
03	3/8	_			_	
04	1/2	_	_			_
06	3/4	_	_	_		•
10	1	_	_	_	_	


### selected. The drain cock, N.C. auto drain, N.O. auto drain and drain guide cannot be selected together.

### Accessory Symbol Description Nil Bracket \*2

D

N.O. auto drain \*4 Only one drain exhaust method can be

# 25A-AM650/850



Symbol	Sizo	Applicable	body size
Symbol	Size	650	850
10	1	•	_
14	11/2	•	•
20	2	_	•

### Bracket Assembly Part Nos.\*3

Applicable model	Part no.
25A-AM650	25A-BM56
25A-AM850	25A-BM57

\*3 The assembly consists of a bracket and 2 mounting screws.

# Accessory 4

Symbol	Description
Nil	_
В	Bracket *1

\*1 When symbol "B" is indicated, a bracket assembly with a part number shown in the left table is shipped together as an accessory but does not come assembled.

## Option

Symbol	Description
Nil	_
<b>J</b> *4,*5	Drain guide 1/4 female threaded (650 only)
R	IN-OUT reversal direction
Т	With element service indicator

<sup>\*5</sup> Drain piping and piping for a stop valve such as ball valve are required.

### ♣Auto drain\*4

Symbol	Description	
Nil	Drain cock (Without auto drain) *2	
D	N.O. auto drain (650 only)	

- \*2 Body size 850 is equipped with a ball valve (Rc 3/8 female threaded).
- Body size 650: Only one drain exhaust method can be selected. The drain cock, N.O. auto drain and drain guide cannot be selected together.
  - \* The 25A- series specifications and dimensions are the same as those of the standard model.






<sup>\*2</sup> When symbol "B" is indicated, a bracket assembly with a part number shown in the left table is shipped together as an accessory but does not come assembled.


# **Micro Mist Separator**



# 25A-AMD Series



### 25A-AMD650/850



Description

Bracket \*1

#### 10 14 11/2 20 2

### Bracket Assembly Part Nos. \*3

Applicable model	Part no.
25A-AMD650	25A-BM56
25A-AMD850	25A-BM57

<sup>\*3</sup> The assembly consists of a bracket and 2 mounting screws.

Symbol

Nil

Symbol	Description	
Nil	Drain cock (Without auto drain) *2	
D	N.O. auto drain (650 only)	


- \*2 Body size 850 is equipped with a ball valve (Rc 3/8 female threaded).
- Body size 650: Only one drain exhaust method can be selected. The drain cock, N.O. auto drain and drain guide cannot be selected together.

<sup>\*1</sup> When symbol "B" is indicated, a bracket assembly with a part number shown in the left table is shipped together as an accessory but does not come assembled.

<sup>\*</sup> The 25A- series specifications and dimensions are the same as those of the standard model.








# 25A-AMH650/850

2 mounting screws.

\*3 The assembly consists of a bracket and



### Bracket Assembly Part Nos.\*3

Applicable mode	Part no.
25A-AMH650	25A-BM56
25A-AMH850	25A-BM57

<sup>\*3</sup> The assembly consists of a bracket and 2 mounting screws.

<sup>\*1</sup> When symbol "B" is indicated, a bracket assembly with a part number shown in the left table is shipped together as an accessory but does not come assembled.

Symbol	Description	
Nil	Drain cock (Without auto drain) *2	
D	N.O. auto drain (650 only)	

come assembled.

shipped together as an accessory but does not

- \*2 Body size 850 is equipped with a ball valve (Rc 3/8 female threaded).
- Body size 650: Only one drain exhaust method can be selected. The drain cock, N.O. auto drain and drain guide cannot be selected together.

<sup>\*</sup> The 25A- series specifications and dimensions are the same as those of the standard model. For details, refer to the Web Catalog.

