
Mini Free Mount Cylinder

25A-CUJ Series

Ø6, Ø8, Ø10





Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDUJB8-15DM


* The 25A- series specifications are the same as those of the standard model.


For details, refer to the Web Catalog.


Dimensions (Dimensions other than those shown below are the same as the standard model.) For details, refer to the Web Catalog.

25A-C□UJB 8

 $\ast\,$ The position of the width across flats may not be parallel to the cylinder tube








Mini Free Mount Cylinder

25A-CUJ Series

ø12, ø16, ø20





Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDUJB12-15DM




^{*} The 25A- series specifications and dimensions are the same as those of the standard model.

Free Mount Cylinder Double Acting, Single Rod

25A-CU Series Ø10, Ø16, Ø20, Ø25, Ø32

RoHS



Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch.
(Example) 25A-CDU20-25D


* The 25A- series specifications and dimensions are the same as those of the standard model.



Free Mount Cylinder: Non-rotating Rod Type Double Acting, Single Rod

25A-CUK Series Ø10, Ø16, Ø20, Ø25, Ø32

RoHS



Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDUK20-25D



^{*} The 25A- series specifications and dimensions are the same as those of the standard model.

Compact Cylinder: Standard Type Double Acting, Single Rod

25A-CQS Series

Ø12, Ø16, Ø20, Ø25

RoHS

How to Order

25A-CDQSB20-30D-M9BW

Series compatible with secondary batteries

With auto switch

Nil	Without magnet for switch*1	
D	With auto switch (Built-in magnet)	

*1 In the case of without magnet for switch, auto switch cannot be mounted.

Mounting 4

В	Through-hole/Both ends	
ט	tapped common (Standard)	
L	Foot	
LC Compact foot		
F Rod flange		
G	Head flange	
D	Double clevis	

- In the case of long strokes, use either ends tapped mounting or bracket mounting.
- Mounting brackets are shipped together with the product but do not come assembled.
- Cylinder mounting bolts are not included.

Bore size

Ξ			
	12	12 mm	
	16	16 mm	
	20	20 mm	
	25	25 mm	

Number of auto

0111101100		
Nil	2	
S	1	
-	-	

Auto switch

Nil Without auto switch

Click here for details on

 Click here for details on applicable auto switch models.

♦Body option

<Standard stroke> <Long stroke>

Nil	Nil Standard	
C With rubber bumper		
M Rod end male thread		
* Combination of body		
options is available.		

1=011g 011 0110r		
С	With rubber bumper Rod end female thread (Standard)	
СМ	With rubber bumper	

 Rubber bumper is standard equipment for long stroke type.

Action

D Double acting

♦Cylinder stroke [mm]

Bore size	Standard stroke	Long stroke
12, 16	5, 10, 15, 20, 25, 30	35, 40, 45, 50, 75, 100, 125, 150, 175, 200
20	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	75, 100, 125, 150, 175, 200
25		75, 100, 125, 150, 175, 200, 250, 300

Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch.
(Example) 25A-CDQSL25-30D

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Mounting Bracket Part Nos. for the 25A- Series


Bore size [mm]	Foot*1	Compact foot*1	Flange	Double clevis
12	25A-CQS-L012	25A-CQS-LC012	25A-CQS-F012	25-CQS-D012
16	25A-CQS-L016	25A-CQS-LC016	25A-CQS-F016	25-CQS-D016
20	25A-CQS-L020	25A-CQS-LC020	25A-CQS-F020	25-CQS-D020
25	25A-CQS-L025	25A-CQS-LC025	25A-CQS-F025	25-CQS-D025

- *1 When ordering foot and compact foot brackets, order 2 pieces per cylinder.
- Parts included with each type of bracket are as follows.
 Foot, Compact foot, Flange: Body mounting bolts

Double clevis type: Clevis pin, Type C retaining ring for axis, Body mounting bolt



Compact Cylinder: Standard Type Double Acting, Double Rod 25A-CQSV Series Ø12, Ø16, Ø20, Ø25



Mounting Bracket Part Nos. for the 25A- Series

Bore size [mm]	Foot*1	Compact foot*1	Flange
12	25A-CQS-L012	25A-CQS-LC012	25A-CQS-F012
16	25A-CQS-L016	25A-CQS-LC016	25A-CQS-F016
20	25A-CQS-L020	25A-CQS-LC020	25A-CQS-F020
25	25A-CQS-L025	25A-CQS-LC025	25A-CQS-F025

- st 1 When ordering foot and compact foot brackets, order 2 pieces per cylinder.
- * Body mounting bolts are included for each bracket.

Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDQSWL25-30D

* The 25A- series specifications and dimensions are the same as those of the standard model.




Compact Cylinder: Anti-lateral Load Type

25A-CQS Series

Ø12, Ø16, Ø20, Ø25



How to Order



Action

D Double acting

F Rod flange
G Head flange
D Double clevis

Mounting brackets are shipped together with the product but

Compact foot

do not come assembled.

* Cylinder mounting bolts are not included.

LC

Cushion

S Anti-lateral load type

Rore size

i	DOI 0 0.20				
	12	12 mm			
	16	16 mm			
	20	20 mm			
	25	25 mm			

Cylinder stroke [mm]

Bore size	Standard stroke	
12, 16	5, 10, 15, 20, 25, 30	
20, 25	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	

Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch.

(Example) 25A-CDQSLS12-25DC

* With cushion only.

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Mounting Bracket Part Nos. for the 25A- Series

Bore size [mm]	Foot*1	Compact foot*1	Flange	Double clevis
12	25A-CQS-L012	25A-CQS-LC012	25A-CQS-F012	25-CQS-D012
16	25A-CQS-L016	25A-CQS-LC016	25A-CQS-F016	25-CQS-D016
20	25A-CQS-L020	25A-CQS-LC020	25A-CQS-F020	25-CQS-D020
25	25A-CQS-L025	25A-CQS-LC025	25A-CQS-F025	25-CQS-D025

*1 When ordering foot and compact foot brackets, order 2 pieces per cylinder.

Parts included with each type of bracket are as follows.

Foot, Compact foot, Flange: Body mounting bolts

Double clevis type: Clevis pin, Type C retaining ring for axis, Body mounting bolt



Compact Cylinder: Standard Double Acting, Single Rod



25A-CQ2 Series

30D

Ø12, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

How to Order



Series compatible with secondary batteries With auto switch

25A - C D Q2 B 20

Nil	Without magnet fo	r switch*1
D	With auto switch (I	Built-in magnet)

*1 In the case of without magnet for switch, auto switch cannot be mounted.

Mounting •

В	Through-hole (Standard)	
Α	Both ends tapped	
L	Foot	
LC	Compact foot	
F	Rod flange	
G	Head flange	
D	Double clevis	

- Mounting brackets are shipped together with the product but do not come assembled.
- Cylinder mounting bolts are not included

•Auto switch

Nil Without auto switch				
* Click here for details on				
applicable auto switch				
models				

Number of auto switches Nil 2

n

n

applicable auto switch models.

♦ Auto switch mounting groove

7	ø12 to ø25	2 surfaces
_	ø32 to ø100	4 surfaces

"Z" is not available for ø12 to ø25 without auto switches.

Body option

Nil	Standard (Rod end female thread)	
С	With rubber bumper	
M	Rod end male thread	

Combination of body options is available.

•Action

D Double acting

12, 16	5, 10, 15, 20, 25, 30
20, 25	5, 10, 15, 20, 25, 30, 35, 40, 45, 50
32, 40	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100
50 to 100	10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDQ2L32-25DZ

Mounting Bracket Part Nos. for the 25A- Series

	Bore size [mm]	Foot*1	Compact foot*1	Flange	Double clevis	
12	Without auto switch	25A-CQ-L012	25A-CQ-LC012	25A-CQ-F012	25-CQ-D012	
12	With auto switch	witch 25A-CQ-LZ12 25A-CQ-LCZ12		25A-CQ-1012	25-00-0012	
16	Without auto switch	25A-CQ-L016	25A-CQ-LC016	25A-CQ-F016	0F 0O D016	
10	With auto switch	25A-CQ-LZ16	25A-CQ-LCZ16	25A-CQ-F016	25-CQ-D016	
20	Without auto switch	25A-CQ-L020	25A-CQ-LC020	25A-CQ-F020	05 00 0000	
20	With auto switch	auto switch 25A-CQ-LZ20 25A-CQ-LCZ20		25A-CQ-F020	25-CQ-D020	
25	Without auto switch	25A-CQ-L025	25A-CQ-LC025	25A-CQ-F025	25-CQ-D025	
25	With auto switch	n auto switch 25A-CQ-LZ25 25A-CQ-LCZ25		25A-CQ-F025	25-CQ-D025	
	32	25A-CQ-L032	25A-CQ-LC032	25A-CQ-F032	25-CQ-D032	
	40	25A-CQ-L040	25A-CQ-LC040	25A-CQ-F040	25-CQ-D040	
	50	25A-CQ-L050	25A-CQ-LC050	25A-CQ-F050	25-CQ-D050	
	63	25A-CQ-L063	25A-CQ-LC063	25A-CQ-F063	25-CQ-D063	
	80	25A-CQ-L080	25A-CQ-LC080	25A-CQ-F080	25-CQ-D080	
	100	25A-CQ-L100	25A-CQ-LC100	25A-CQ-F100	25-CQ-D100	

Bore size

Port thread type

M thread ø12 to ø25

63

80

| **32** | 32 mm | **100** | 100 mm

Rc

NPT

G

40 40 mm

50 mm

63 mm

80 mm

ø32 to ø100

12 mm

20 mm

16 16 mm

25 25 mm

20

Nil

ΤN

- *1 When ordering foot and compact foot brackets, the required quantity will be different depending on the bore size. a12 to a25:
 - Without auto switch: Order 2 pieces per cylinder.
 - With auto switch: Order 1 piece per cylinder. (Part number for a set of 2 foot brackets) ø32 to ø100:
 - Order 2 pieces per cylinder.
- * Parts included with each type of bracket are as follows.

Foot, Compact foot, Flange: Body mounting bolts, Double clevis: Clevis pin, Type C retaining rings for axis, Body mounting bolts

Simple Joint (Standard)/ Part Nos.

Bore size [mm]	Joint	Type A mounting bracket	Type B mounting bracket
32, 40	YU-03	YA-03	YB-03
50, 63	YU-05	YA-05	YB-05
80	YU-08	YA-08	YB-08
100	YU-10	YA-10	YB-10

<Ordering>

 Joints are not included with type A or B mounting brackets. Order them separately. (Example)

Bore size Ø40	Part no.
 Type A mounting 	bracket ······YA-03

• Joint......YU-03





Compact Cylinder: Standard Double Acting, Double Rod



25A-CQ2W Series

30 D

Ø12, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

How to Order



Series compatible with secondary batteries

With auto switch

Nil	Without magnet for switch*1
D	With auto switch (Built-in magnet)

*1 In the case of without magnet for switch, auto switch cannot be mounted.

Mounting

- Mounting brackets are shipped together with the product but do not come assembled.
- Cylinder mounting bolts are not included.

	Wounting	
В	Through-hole (Standard)	
Α	Both ends tapped	
L	Foot	
LC	Compact foot	
F	Flange	

25A - CD Q2W B 20

Bore size

12	12 mm	40	40 mm
16	16 mm	50	50 mm
20	20 mm	63	63 mm
25	25 mm	80	80 mm
32	32 mm	100	100 mm

Mounting Bracket Part Nos. for the 25A- Series

E	Bore size [mm]	Foot*1	Compact foot*1	Flange		
12	Without auto switch	25A-CQ-L012	25A-CQ-LC012	25A-CQ-F012		
	With auto switch	25A-CQ-LZ12	25A-CQ-LCZ12			
16	Without auto switch	25A-CQ-L016	25A-CQ-LC016	054 00 5040		
10	With auto switch	25A-CQ-LZ16	25A-CQ-LCZ16	25A-CQ-F016		
20	Without auto switch	25A-CQ-L020	25A-CQ-LC020	25A-CQ-F020		
20	With auto switch	25A-CQ-LZ20	25A-CQ-LCZ20	25A-CQ-F020		
25	Without auto switch	25A-CQ-L025	25A-CQ-LC025	25A-CQ-F025		
25	With auto switch	25A-CQ-LZ25	25A-CQ-LCZ25	25A-CQ-F025		
	32	25A-CQ-L032	25A-CQ-LC032	25A-CQ-F032		
	40	25A-CQ-L040	25A-CQ-LC040	25A-CQ-F040		
	50	25A-CQ-L050	25A-CQ-LC050	25A-CQ-F050		
63		25A-CQ-L063	25A-CQ-LC063	25A-CQ-F063		
80		25A-CQ-L080	25A-CQ-LC080	25A-CQ-F080		
100		25A-CQ-L100	25A-CQ-LC100	25A-CQ-F100		

*1 When ordering foot and compact foot brackets, the required quantity will be different depending on the bore size.

ø12 to ø25:

- · Without auto switch: Order 2 pieces per cylinder.
- With auto switch: Order 1 piece per cylinder. (Part number for a set of 2 foot brackets)

ø32 to ø100:

- · Order 2 pieces per cylinder.
- * Body mounting bolts are included for each bracket.

Number of auto switches

Nil	2
S	1
n	n

Auto switch

Nil Without auto switch

Click here for details on applicable auto switch models.

Auto switch mounting groove

7	ø12 to ø25	
	ø32 to ø100	4 surfaces

Z-M9BW

"Z" is not available for Ø12 to Ø25 without auto switches.

Body option

Nil Standard (Rod end female threa		
С	With rubber bumper	
M	Rod end male thread	

* Combination of body options is available.

Action

D Double acting

Cylinder stroke [mm]

12, 16	5, 10, 15, 20, 25, 30
20, 25	5, 10, 15, 20, 25, 30, 35, 40, 45, 50
32, 40	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100
50 to 100	10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100

Port thread type

Nil	M thread	ø12 to ø25
INII	Rc	
TN	NPT	ø32 to ø100
TF	G	

Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch.

(Example) 25A-CDQ2WL32-25DZ

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Simple Joint (Standard)/Part Nos.

Bore size [mm]	Joint	Type A mounting bracket	Type B mounting bracket
32, 40	YU-03	YA-03	YB-03
50, 63	YU-05	YA-05	YB-05
80	YU-08	YA-08	YB-08
100	YU-10	YA-10	YB-10

<Ordering>

Joints are not included with type A or B mounting brackets. Order them separately.

(Example)


Bore size ø40 Part no Type A mounting bracket ········· YA-03



Compact Cylinder: Large Bore Size Double Acting, Single Rod

25A-CQ2 Series ø125, ø140, ø160, ø180, ø200





Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDQ2B140-30DCZ




^{*} The 25A- series specifications and dimensions are the same as those of the standard model.

Compact Cylinder: Long Stroke Double Acting, Single Rod



Ø32, Ø40, Ø50, Ø63, Ø80, Ø100



Simple Joint (Standard)/Part Nos.

Bore size [mm]	Joint	Type A mounting bracket	Type B mounting bracket
32, 40	YU-03	YA-03	YB-03
50, 63	YU-05	YA-05	YB-05
80	YU-08	YA-08	YB-08
100	YU-10	YA-10	YB-10

<Ordering>

 Joints are not included with type A or B mounting brackets. Order them separately. (Example)

Mounting Bracket Part Nos. for the 25A- Series

Bore size [mm]	Foot*1	Compact foot*1	Flange	Double clevis
32	25A-CQ-L032	25A-CQ-LC032	25A-CQ-F032	25-CQ-D032
40	25A-CQ-L040	25A-CQ-LC040	25A-CQ-F040	25-CQ-D040
50	25A-CQ-L050	25A-CQ-LC050	25A-CQ-F050	25-CQ-D050
63	25A-CQ-L063	25A-CQ-LC063	25A-CQ-F063	25-CQ-D063
80	25A-CQ-L080	25A-CQ-LC080	25A-CQ-F080	25-CQ-D080
100	25A-CQ-L100	25A-CQ-LC100	25A-CQ-F100	25-CQ-D100

^{*1} Order 2 pieces per cylinder.

* The 25A- series specifications and dimensions are the same as those of the standard model.




Parts included with each type of bracket are as follows.
 Foot, Compact foot, Flange: Body mounting bolts, Double clevis: Clevis pin, Type C retaining rings for axis, Body mounting bolts

Compact Cylinder: Anti-lateral Load

25A-CQ2 Series

Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

RoHS



Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDQ2LS40-30DCZ

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Mounting Bracket Part Nos. for the 25A- Series

Bore size [mm]	Foot*1	Compact foot*1	Flange	Double clevis
32	25A-CQ-L032	25A-CQ-LC032	25A-CQ-F032	25-CQ-D032
40	25A-CQ-L040	25A-CQ-LC040	25A-CQ-F040	25-CQ-D040
50	25A-CQ-L050	25A-CQ-LC050	25A-CQ-F050	25-CQ-D050
63	25A-CQ-L063	25A-CQ-LC063	25A-CQ-F063	25-CQ-D063
80	25A-CQ-L080	25A-CQ-LC080	25A-CQ-F080	25-CQ-D080
100	25A-CQ-L100	25A-CQ-LC100	25A-CQ-F100	25-CQ-D100

^{*1} Order 2 pieces per cylinder.

^{*} Parts included with each type of bracket are as follows.

Foot, Compact foot, Flange: Body mounting bolts, Double clevis: Clevis pin, Type C retaining rings for axis, Body mounting bolts


Compact Cylinder: With End Lock

25A-CBQ2 Series

Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100



How to Order



Built-in Magnet Cylinder Model

If a built-in magnet cylinder without an auto switch is required, there is no need to enter the symbol for the auto switch. (Example) 25A-CDBQ2L32-30DC-RN

Mounting Bracket Part Nos. for the 25A- Series

mountaing Bracket rate from the 2011 Corner					
Bore size [mm]	Foot*1	Compact foot*1	Flange	Double clevis	
20	25A-CQS-L020	25A-CQS-LC020	25A-CQS-F020	25-CQS-D020	
25	25A-CQS-L025	25A-CQS-LC025	25A-CQS-F025	25-CQS-D025	
32	25A-CQ-L032	25A-CQ-LC032	25A-CQ-F032	25-CQ-D032	
40	25A-CQ-L040	25A-CQ-LC040	25A-CQ-F040	25-CQ-D040	
50	25A-CQ-L050	25A-CQ-LC050	25A-CQ-F050	25-CQ-D050	
63	25A-CQ-L063	25A-CQ-LC063	25A-CQ-F063	25-CQ-D063	
80	25A-CQ-L080	25A-CQ-LC080	25A-CQ-F080	25-CQ-D080	
100	25A-CQ-L100	25A-CQ-LC100	25A-CQ-F100	25-CQ-D100	

^{*1} Order 2 pieces per cylinder.

* The 25A- series specifications and dimensions are the same as those of the standard model.


Parts included with each type of bracket are as follows: Foot, Compact foot, Flange: Body mounting bolts, Double clevis: Clevis pin, Type C retaining rings for axis, Body mounting bolts

Plate Cylinder: Double Acting, Single Rod

25A-MU Series

Ø25, Ø32, Ø40, Ø50, Ø63





^{*} The 25A- series specifications and dimensions are the same as those of the standard model.

