

Rotary Table: Vane Type **25A-MSUB Series** Size: 1, 3, 7, 20 RoHS



- * The 25A- series specifications and dimensions are the same as those of the standard model.
- * Zinc is used in part of deep groove ball bearing.

For details, refer to the Web Catalog.


Rotary Table/Rack & Pinion Type **25A-MSQ Series** Size: 10, 20, 30, 50



* Zinc is used in part of deep groove ball bearing and seal washer.

For details, refer to the Web Catalog.

the same as those of the standard model.



4 Number of					
auto switches					
Nil	2				
S	1				
n	n				

5 Port type						
End	port type	Size				
Nil	M5	10, 20				
Nil	Rc1/8					
-XF	G1/8	30, 50				
-XN	NPT1/8	30, 50				
-ХТ	NPTF1/8					

6 Made to order

	None
В	With interchangeable table

* Some parts have dimensions and shapes that are different from those of the standard model. Refer to page 176 for details. Other specifications are the same as those of the standard model.

For details, refer to the Web Catalog.

Internal Shock Absorber Part Nos. for the 25A- Series

* Zinc is used in part of deep groove ball bearing and seal washer.

Size	Part no.					
10	25A-RBA0805-X692					
20						
30	25A-RBA1006-X692					
50 25A-RBA1411-X692						
The part number is the same for the 25A-MSO-X251						


* The part number is the same for the 25A-MSQ-X251.




Rotary Table/Rack & Pinion Type **25A-MSQ** Series


Dimensions

Basic type 25A-MSQ⊡A





Internal shock absorber 25A-MSQ




					[mm]
Size	AU	AY	FU	HU	SU
10	6.5	6	32	18	24
20	7.5	8	36	26	34
30	7.5	8	34	24	32
50	10	10	54	34	45.5

* Dimensions other than those shown above are identical to the standard products.

For details, refer to the Web Catalog.

With vacuum port 25A-MSQ□A-X251




										[mm]
Size	AU	AY	DG	FU	н	HC	HU	SB	SU	UU
10	6.5	6	35h9	32	14.2	5	18	47.2	24	48.7
20	7.5	8	42h9	36	14	6	26	59.9	34	51
30	7.5	8	48h9	34	14	6	24	65.3	32	58
50	10	10	54h9	54	14	7	34	77.7	45.5	64

* Dimensions other than those shown above are identical to the standard products.


* The product with the vacuum port has no hollow shaft at its rotation center.

For details, refer to the Web Catalog.

Bumper 25A-MSQ⊡D-X251



Internal shock absorber 25A-MSQ□R-X251




MSQ Series Made to Order Nade Please contact SMC for detailed dimensions, specifications, and delivery times. Symbol 1 With Interchangeable Table and Plate - R -A. **Applicable Rotary Table** Hexagon socket head cap screw Made to order With interchangeable Mode With interchangeable With interchangeable With interchangeable Note Interchangeable table В table table and plate table plate 25A-MSQ \cap Ο 25A-MSQ
-B-X251 \cap Parallel pin With interchangeable (Built into the 111 fundant 1111 How to Order Α table and plate interchangeable table) Standard model no. Interchangeable tab Made to order The interchangeable table and plate A With interchangeable table and plate can be ordered separately. For details, **B** With interchangeable table refer to the tables below. With interchangeable plate С The interchangeable table and plate are assembled before shipment. Part Nos. of Interchangeable Parts Interchangeable A Unit (With Interchangeable Table and Plate) Interchangeable Contents plate Size Part no. Description (Qty.) 10 P891010-53 Interchangeable table (1) Parallel pin (1) P891020-53 20 Hexagon socket head cap screw (4) Interchangeable plate (1) 30 P891030-53 Cross recessed head machine P891040-53 50 screw for precision instruments (2) Interchangeable plate Interchangeable B Unit (With Interchangeable Table) Through hole Cross recessed head Contents Size Part no. machine screw for With interchangeable Ĵ Description (Qty.) precision instruments С plate 10 P891010-54 Interchangeable table (1) 20 P891020-54 Parallel pin (1) * To position the product, use the knock pin holes on the body instead of 30 P891030-54 Hexagon socket head cap screw (4) the through holes that are empty in the interchangeable plate. P891040-54 50 Dimensions: The dimensions of the 25A-MSQ are the same as those of Interchangeable C Unit (With Interchangeable Plate) the standard product. Contents Refer below for the dimensions of the 25A-MSQD-B-X251 Size Part no. Description (Qty.) with a vacuum port. 10 P891010-55 · Interchangeable plate (1) 20 P891020-55 Cross recessed head machine P891030-55 30 screw for precision instruments (2) 50 P891040-55 Refer to the Web Catalog for the tightening torque of the interchangeable parts. Mounting diagram of the interchangeable table Dimensions Dimensions other than those shown below are the same as those of the basic type. Refer to the Web Catalog for details. With vacuum port/With interchangeable table **Bumper** 25A-MSQD-B-X251 25A-MSQ

A-B-X251 M5 x 0.8 depth 5 Vacuum port \equiv Ā Max. ≈ HŲ 5.8 В Internal shock absorber 25A-MSQ
R-B-X251 AU øDG ပ္ SB Max. ~ SU No hollow shaft at the rotation center (mm) Size AU AY DG FU н HC HU UU SB SU Max. ≈ FU 10 24 6.5 6 35h9 32 21 5 18 47.2 55.7 Dimensions other than those shown above are identical 7.5 6 20 8 42h9 36 23 26 59.9 34 60 to the standard products. 7.5 30 8 48h9 34 23 6 24 65.3 32 67 The product with the vacuum port has no hollow shaft at 50 10 10 54h9 26 7 34 45.5 75.5 54 77.7 its rotation center.



Rotary Table/Rack & Pinion Type **25A-MSQ Series** Size: 10, 20, 30, 50, 70, 100, 200 RoHS



*1 Size 200 is produced upon receipt of order.

Series compatible with

secondary batteries

* Zinc is used in part of deep groove ball bearing and seal washer.

* Side port cannot be used.

SMC

Size

10

20

30

50

70 100

200*1

A With adjustment bolt

the same as those of the standard model. For details, refer to the Web Catalog.

Number of auto switches

2

1

n

Nil Without auto switch (Built-in magnet)

Click here for details on applicable auto switch models.

* Some parts have dimensions and shapes that are different from those of the standard model. Refer to page 179 for details. Other specifications are

Nil

S


n

Auto switch

25A-MSQ Series

Dimensions

25A-MSQB




		[mm]
Size	AY	SU
10	6	23.7
20	8	33
30	8	33
50	10	42.9
70	16	44.2
100	16	44.3
200	21	52.2

* Dimensions other than those shown above are identical to the standard products.

For details, refer to the Web Catalog.

25A-MSQB AX-X251




								[mm]
Size	AY	DG	FD	Н	HA	HB	SU	UU
10	6	35h9	11.5	20	5.5	5	23.7	59
20	8	40h9	11.5	22	5.5	6	33	65
30	8	48h9	11.5	22	5.5	6	33	68
50	10	54h9	11.5	24	5.5	7	42.9	77
70	16	50h9	12	25	6	7	44.2	85
100	16	52h9	12	27	6	7	44.3	93
200	21	64h9	15	32	7.5	8	52.2	114

* The product with the vacuum port has no hollow shaft at its rotation center.

* Dimensions other than those shown above are identical to the standard products.

For details, refer to the Web Catalog.

3-Position Rotary Table **25A-MSZ Series** Size: 10, 20, 30, 50 RoHS



* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.