PA□/PB Series

Related Products 1

<For driving PA3□□3, PAP3313, PAF3413 series> 5 port solenoid valve



<For driving PAF5413 series> 5 port solenoid valve $VQ44_{\,\,0}^{\,\,0}\,O$ (Exhaust center)



<For driving PA3□□3, PAP3313, PAF3413, PB1013A series> 3 port solenoid valve \$\(\frac{SYJ514}{714} \)



Regulator AR Series



Mist separator **AM** Series

AM series separates and removes the oil mist and removes fine particles of rust and carbon, etc., of 0.3 µm or larger.



Micro mist separator AMD Series

AMD series can separate and remove aerosol state oil mist and remove carbon or dust of more than 0.01 µm.



Refer to the Best Pneumatics No. 6 for further details.

Refer to the Best Pneumatics No. 6 for further details.

Refer to the Best Pneumatics No. 6 for further details.

Filter regulator + Mist seperator Air combination AC20D/30D/40D Series



Water separator AMG Series

The AMG series remove droplets of water from compressed air. Use it when it is necessary to remove water, but when air as dry as that from an air dryer is not necessary.



Membrane dryer IDG Series

Macromolecular membrane dryers that act like filters -2© low dew point just by installing on air pressure line. No power supply required.



Refer to the Best Pneumatics No. 6 for further details

Refer to the Best Pneumatics No. 6 for further details.


Refer to the Best Pneumatics No. 6 for further details.

<For strainer>
Industrial filter
Vessel type
FGD Series



Strainer **P257014A**

Strainer for the collection of fluids



Specifications

Part no.	P257014A
Fluid	Cutting oil
Applicable tube O.D/I.D	ø6/ø4.5
Nominal filtration rating	60 mesh wire
Material	Cast iron/Electroless Ni-P alloy plating
Weight kg	0.2

Refer to the Best Pneumatics No. 6 (HEP500-04) for further details.

PA□/**PB** Series

Related Products 2

High Purity Chemical Valves

LV Series

Refer to the Best Pneumatics No. 9 for further details.

Air operated Integrated fitting type **LVC** Series

Air operated Compact type

LVD Series



Air operated Threaded type LVA Series



Manually operated Integrated fitting type/Threaded type **LVH** Series



PA(P)

PAX

PB



Air operated/Manually operated Non-metallic exterior **LVQ** Series



SMC

Fluoropolymer Fittings Hyper Fitting **LQ1** Series



Refer to the Best Pneumatics No. 9 for further details.

Fluoropolymer Fittings Hyper Fitting/ Flare type



Refer to the Best Pneumatics No. 9 for further details.

Fluoropolymer Needle Valve LVN Series



Fluoropolymer Tubing **TL/TIL** Series



Refer to the Best Pneumatics No. 9 for further details.

Refer to the Best Pneumatics No. 9 for further details.