
Polyurethane Coil Tubing TCU Series



For flexible tubing Compact piping possible

Max. Operating Pressure



⚠ Precautions

Be sure to read this before handling the products. Refer to page 11 for safety instructions and pages 14 to 18 for fittings and tubing precautions.

∧ Caution


- Please consult with SMC regarding use with any fluids other than air.
- Abnormal temperature rise caused by adiabatic compression may result in the tube bursting.
- Please do not cut the coil and insert it into the fitting. This may cause air leakage, or tubing to come out after installation.
- Very slight leakage may occur in the multi-core tubing due to its characteristics.

Model/Specifications

Model	TCU 0425B-1	TCU 0425B-2	TCU 0425B-3	TCU 0604B-1	TCU 0604B-2	TCU 0604B-3	TCU 0805B-1			
Number of cores		1 core	2 cores	3 cores	1 core	2 cores	3 cores	1 core		
Tubing O.D. (mm)		4		6			8			
Tubing I.D. (mm)		2.5		4			5			
Fluid Air					Air					
Max. operating	20°C	0.8								
pressure (MPa)	40°C	0.65								
	60°C	0.5								
Operating vacuum pressure	-101.3									
Applicable fittings	One-touch fittings, Insert fittings, Self-align fittings, Miniature fittings									
Operating tempera	−20 to 60°C									
Material	Polyurethane									
Color		Black (Opaque)								

Note 1) The operating vacuum pressure varies depending on the applicable fitting, so refer to the fitting specifications for details.

Dimensions




_									
Specifications		Tubing size (mm)		Coil (mm)		No. of	No. of coil windings		Standard unit
Model		O.D. I.D. L Ø D		øD	cores	per tube length	length (m)	of packing	
TCU0	I0425B-1			210	18	1	52 ± 2	1.5	
TCU0	425B-2	4	2.5	280	28	2	35 ± 1	1.5	
TCU0	425B-3			265	20	3	22 ± 1	1	
TCU0	604B-1			325	24	1	54 ± 2	2	5 tubes/case
TCU0	TCU0604B-2		4	323	37	2	27 ± 1	1.5	
TCU0	604B-3			305	37	3	17 ± 1	1	
TCU0	TCU0805B-1		5	330	31	1	41 ± 2	2	

^{*} The number of coil windings per tube length and dimensions are changeable due to material.

Made to Order

Change of coil turns, Change of color

(Please contact SMC for specifications in detail, dimensions and delivery.)



Tube fastener (Multi-tube only)

Specifications	Tubing size (mm)		Coil (mm)		No. of	No. of coil windings per	Max. operating	
Model	O.D.	I.D.	L	øD	cores	tube length (N)	length (mm)	
TCU0425 □-1-N-X6			N x 4	18	1	3 to 90	L x 5.9 + 200	
TCU0425 □-2-N-X6	4	2.5	N x 8	28	2	3 to 90	L x 4.4 + 200	
TCU0425 □-3-N-X6			N x 12	28	3	3 to 63	L x 2.9 + 200	
TCU0604 □-1-N-X6			Nx6	24	1	3 to 90	L x 5.3 + 200	
TCU0604 □-2-N-X6	6	4	N x 12	37	2	3 to 66	L x 3.8 + 200	
TCU0604 □-3-N-X6]		N x 18	37	3	3 to 44	L x 2.5 + 200	

Specifications	Tubing size (mm)		Coil (mm)		No. of	No. of coil	Max. operating	
Model	O.D.	I.D.	L	øD	cores	windings per tube length (N)	length (mm)	
TCU0805 □-1-N-X6	8	5	N x 8	31	1	3 to 90	L x 5.2 + 200	
TCU0805 □-2-N-X6			N x 16	42	2	3 to 40	L x 3 + 200	
TCU1065 □-1-N-X6	10	6.5	N x 10	52	1	3 to 45	L x 5 + 200	
TCU1065 □-2-N-X6			N x 20	52	2	3 to 35	L x 3 + 200	
TCU1208 ☐-1-N-X6	12	8	N x 12	67	1	3 to 35	L x 5 + 200	
TCU1208 □-2-N-X6			N x 24	67	2	3 to 30	L x 3 + 200	

^{*} D: B (Black), W (White), R (Red), BU (Blue), Y (Yellow), G (Green), C (Clear), YR (Orange)



٨