
# Polyurethane Flat Tubing **TFU Series**





## Compact piping possible With line markings for piping differentiation

#### Max. Operating Pressure



### **⚠** Precautions

Be sure to read this before handling the products.
Refer to back page 50 for Safety Instructions
and pages 13 to 17 for Fittings and Tubing
Precautions.


#### **⚠**Caution

- Please consult with SMC regarding use with any fluids other than air.
- Abnormal temperature rise caused by adiabatic compression may result in the tube bursting.
- The value of the minimum bending radius is measured at the temperature of 20°C as shown in the figure on the right.
- As a result of product design characteristics, there are cases of very slight leakage.

#### Model/Specifications

Model		TFU 0425B-2	TFU 0425B-3	TFU 0604B-2	TFU 0604B-3	TFU 0805B-2	TFU 0805B-3	
No. of cores		2 cores	3 cores	2 cores	3 cores	2 cores	3 cores	
Tubing O.D. (mm)		4		6		8		
Tubing I.D. (mm)		2.5		4		5		
Fluid	Air							
Max. operating pressure (MPa)	20°C	0.8						
	40°C	0.65						
	60°C	0.5						
Applicable fittings		One-touch fittings, Insert fittings, Self-align fittings, Miniature fittings						
Operating temperature		-20 to +60°C (No freezing)						
Material		Polyurethane						
Color		Black						
Min. bending radius (mm)		1	0	1	5	2	0	
Tube length per roll (m)		10						

#### How to Order





Bend the tube into U-form at a temperature of 20°C. Fix one end and close loop gradually. Measure 2R when the tube breaks or is crushed.

#### Made to Order

(Please contact SMC for specifications in detail, dimensions and delivery.)

Model		TFU0425 □	TFU0604□	TFU0805 □	TFU1065 □	TFU1208 □
Tubing O.D. (mm)		4	6	8	10	12
Tubing I.D. (mm)		2.5	4	5	6.5	8
No. of cores	2				<b>—</b>	<del></del>
	3				<del></del>	<del></del>
	4	+	<del></del>	<del></del>	<del></del>	
	5	+	<del></del>	<del></del>	_	
	6	<b>+</b>	<del></del>	<del></del>		
	7	<b>—</b>	<b></b>			
	8	<b>—</b>	<b></b>			

## W: White, R: Red, BU: Blue, Y: Yellow, G: Green, C: Clear, YR: Orange, (All tubes are the same color regardless of 2 cores or 3 cores.) 2. Reel (50 m, 100 m length, Color changes)

Suffix "-X3" to the end of part number. Ex.) TFU0425B-2-50-X3

1. Change of color (10 m roll)
Suffix "-X4" to the end of part number.
Ex.) TFU0604BU-2-10-X4

#### 3. No. of cores (10 m roll, each color)

Suffix "-X4" to the end of part number. Ex.) TFU0604B-4-10-X4