
# **Digital Pressure Switch**

# (Built-in Regulator Type) ( E CA CAUS ROHS)





# How to Order



#### **Output specifications** 25 NPN output 65 PNP output

## Unit specifications

ſ	Nil	With unit conversion function Note 1)
	М	Fixed SI unit Note 2)
[	Р	Pressure unit: psi (Initial value), with unit conversion function Note 1)

Note 1) Under the New Measurement Law, sales of switches with the unit switching function have not been allowed for use in Japan. Note 2) Fixed unit: MPa



# Option/Part No.

When optional parts are required separately, use the following part numbers to place an order.

Name	Part No.	Note	
Lead wire with connector	ZS-32-A	Length: 2 m (With rubber cover)	
	ZS-32-C	For ISE35-□-A (AR/AW series) Mounting thread (3 x 7L, 2 pcs.), adapter, lock pin, O-ring are attached	
Mounting kit	ZS-32-D	For ISE35-□-B (ARM10/11 series) Mounting thread (M3 x 13, 2 pcs.), adapter, lock pin, O-ring are attached	
	ZS-32-C-X473	For ISE35-  -A-X523 (AR/AW-D series)  Mounting thread (3 x 8L, 2 pcs.),  adapter, lock pin, O-ring are attached	

## Made to Order (p. 128-1) Specifications X523 AR/AW-D Series Mounting kit is included \* Only applicable to Option 2 (A) Option 2

Nil AR/AW series mounting kit Lock pin Mounting thread Adanter Example) O-rinģ Regulator ARM10/11 series mounting kit Mounting thread O-ring В

Option 1 Nil None Lead wire with connector (Length: 2 m) L

# Applicable series

Product series that this product can be installed in.

Product series	Model
	AC20/AC25/AC30/AC50/AC55/AC60
F.R.L. combination	AC20A/AC30A/AC40A/AC50A/AC60A
	AC20B/AC25B/AC30B/AC50B/AC55B/
	AC60B
	AC20C/AC25C/AC30C/AC40C
	AC20D/AC30D/AC40D
Regulator	AR20 (K) /AR25 (K) /AR30 (K) /AR40 (K) /
negulator	AR50 (K) /AR55 (K) /AR60 (K)
Filter regulator	AW20 (K) /AW30 (K) /AW40 (K) /AW60 (K)
Mist separator regulator	AWM20/AWM30/AWM40
Micro mist separator regulator	AWD20/AWD30/AWD40
Compact manifold regulator	ARM10/ARM11
Direct precision operated regulator	ARP20 (K) /ARP30 (K) /ARP40 (P)

# Digital Pressure Switch ISE35 Series


# **Specifications**

Refer to pages 11 and 12 for Pressure Switch Precautions. For details about the Specific Product Precautions, refer to the Operation Manual on the SMC website, http://www.smcworld.com Click here for details.


	Model	ISE35	
Rated pressu	re range	0 to 1 MPa	
Display/settin	g pressure range	-0.1 to 1 MPa	ZSE20
Withstand pre	essure	1.5 MPa	ISE20
Minimum disp	play/setting unit	0.01 MPa	ZSE30 ISE30
Applicable flu	iid	Air, Non-corrosive gas, Non-flammable gas	ZSE40
Power supply	voltage	12 to 24 VDC ±10%, Ripple (p-p) 10% or less (With power supply polarity protection)	ISE40
Current consi	umption	55 mA or less (at no load)	ZSE10
Switch output	t	NPN or PNP open collector output: 1 output	ISE10
	Max. load current	80 mA	ISE70
	Max. applied voltage	30 V (With NPN output)	ZSE80
	Residual voltage	1 V or less (With load current of 80 mA)	ISE80
	Response time	1 s (0.25, 0.5, 2, 3s selections)	PS
Short circuit protection		Yes	
Repeatability		±1% F.S.	ISA3
Hysteresis	Hysteresis mode	Adjustable (can be set from 0)	ISA2
nysteresis	Window comparator mode		
Display		3-digit, 7-segment indicator, 2-color display (Red/Green) A switch can be operated simultaneously.	ISE35
Display accuracy		±2% F.S. ± 1 digit (at 25°C ±3°C ambient temperature)	DOE
Indicator light		Lights up when output is turned ON. (Green)	PSE
Environment	Enclosure	IP40	IS
Environment	Operating temperature range	−5 to 50°C (No freezing or condensation)	
		Oil resistance vinyl cabtyre cable	ISG
Lead wire with	h connector	3 core ø3.4 2 m	ZSM1
(Option: L)		Sectional area of conductor: 0.2 mm <sup>2</sup> (AWG25)	ZOWII
		Outside diameter of insulator: 1.16 mm	
Weight		Approx. 14 g (Body only) Approx. 38 g (Including lead wire with connector)	
Standard		CE/UKCA marking, UL/CSA (E216656)	

# **Internal Circuits and Wiring Examples**


#### -25 NPN (1 output)




#### -65 PNP (1 output)



### **Dimensions**



#### Lead wire with connector ZS-32-A




# ISE35 Series Made to Order

Please contact SMC for detailed dimensions, specifications and lead times.




# 1 AR/AW-D Series Mounting Kit is Included

Mounting screws, an adapter, a lock pin, and an O-ring are shipped together with the product.



#### **How to Order**

\* Refer to "How to Order" on page 126 for standard specifications.



#### Option/Part No.

option, artifor							
	Name	Part No.	Note				
	Mounting kit	ZS-32-C-X473	For ISE35-  -A-X523 (AR/AW-D series)  Mounting thread (3 x 8L, 2 pcs.), adapter, lock pin, O-ring are attached				

ZSE20 ISE20 ZSE30 ISE30

> ZSE40 ISE40 ZSE10 ISE10

ISE70

ZSE80 ISE80

ISA3

ISA2

ISE35

PSE IS

ISG

ZSM1