


All other specifications are the same as the standard products Series C85. Click here for details.

Refer to page 69 for applicable auto switches.

Mounting Bore size bracket (mm)		8	10	12	16	20	25
Mounting bracket	Foot (1 pc.)	C85L10A		C85L16A		C85L25A	
	Foot (2 pcs. with mounting nut 1 pc.)	C85L10B		C85L16B		C85L25B	
	Flange	C85F10		C85F16		C85F25	
	Trunnion	C85T10		C85T16		C85T25	
Ž	Clevis	C85C10		C85C16		C85C25	
۲ ۲	Rod end	KJ4D		KJ6D		KJ8D	KJ10D
Accessory	Double knuckle joint	GKM4-8		GKM6-12		GKM8 -16	GKM10 -20
	Floating joint	JA10-4-070		JA15-6-100		JA20 -8-125	JA30 -10-125



Mounting Bracket Part No.

Mounting Bore size bracket		8	10	12	16	20	25
Mounting bracket	Foot (1 pc.)	C85L10A		C85L16A		C85L25A	
	Foot (2 pcs. with mounting nut 1 pc.)	C85L10B		C85L16B		C85L25B	
	Flange	C85F10		C85F16		C85F25	
	Trunnion	C85T10		C85T16		C85T25	
Ž	Clevis	C85C10		C85C16		C85C25	
Z	Rod end	KJ4D		KJ6D		KJ8D	KJ10D
Accessory	Double knuckle joint	GKM4-8		GKM6-12		GKM8 -16	GKM10 -20
	Floating joint	JA10-4-070		JA15-6-100		JA20 -8-125	JA30 -10-125


* Not available with air cushion.

** Other strokes available on request.

All other specifications are the same as the standard products Series C85W. Click here for details.

Refer to page 69 for applicable auto switches.





Mounting Bracket Part No.

Mou	Bore size unting (mm) cket	8	10	12	16	20	25
Mounting bracket	Foot (1 pc.)	C85L10A		C85L16A		C85L25A	
	Foot (2 pcs. with mounting nut 1 pc.)	C85L10B		C85L16B		C85L25B	
	Flange	C85F10		C85F16		C85F25	
	Trunnion	C85T10		C85T16		C85T25	
Σ	Clevis	C85C10		C85C16		C85C25	
Accessory	Rod end	KJ4D		KJ6D		KJ8D	KJ10D
	Double knuckle joint	GKM4-8		GKM6-12		GKM8 -16	GKM10 -20
	Floating joint	JA10-4-070		JA15-6-100		JA20 -8-125	JA30 -10-125

All other specifications are the same as the standard products Series C85K. Click here for details.

Refer to page 69 for applicable auto switches.