## ATEX Compliant

Mechanically Jointed Rodless Cylinder/Slide Bearing Guide Type


## Series 55-MY1M Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63





**( €** ⟨Ex⟩ II 2G Ex h IIC T6..T5 Gb

## **How to Order**



- \* Long stroke can be ordered the same as the standard stroke. 55-MY1M20-3000
- \* Please be advised that with a stroke of 49 mm or less, there are cases where auto switch mounting is not possible, and the performance of the air cushion may decline.

All other specifications are the same as the standard products Series MY1M. Click here for details.

Refer to page 69 for applicable auto switches.

