## **ATEX Compliant**

## Mechanically Jointed Rodless Cylinder/Linear Guide Type

## **Series 55-MY1H** Ø10, Ø16, Ø20, Ø25, Ø32, Ø40



Maximum

manufacturable


stroke

1000

1500

**( €** ⟨**E**x⟩ II 2G Ex h IIC T6..T5 Gb

## **How to Order**



All other specifications are the same as the standard products Series MY1H. Click here for details.

Refer to page 69 for applicable auto switches.