
Replacement Procedure is on p. 405

Mechanically Jointed Rodless Cylinder/Cam Follower Guide Type

MY1C Series 016, 020, 025, 032 040, 050, 063

Construction



* The numbers correspond with those in the "Construction" of the MY1C series in the Web Catalog.

Replacement Parts: Seal Kit (14, 15, 16, 32, and 46 are not included in the seal kit. Order them as required with the individual part numbers provided.)

nepracement Farts. Sear Kit (14, 15, 16, 52, and 46 are not included in the searkit. Order them as required with the individual part numbers provided.)									
No.	Description	Qty.	MY1C16	MY1C20	MY1C25	MY1C32	MY1C40	MY1C50	MY1C63
14	Belt clamp	2	_	_	MYC25-31-29449B	MYC25-31-29449B	MYC40-31-29451B	_	_
15	Seal belt	1	MY16-16C-Stroke	MY20-16C-Stroke	MY25-16C-Stroke	MY32-16C-Stroke	MY40-16C-Stroke	MY50-16C-Stroke	MY63-16A-Stroke
16	Dust seal band	1	MY16-16B-Stroke	MY20-16B-Stroke	MY25-16B-Stroke	MY32-16B-Stroke	MY40-16B-Stroke	MY50-16B-Stroke	MY63-16B-Stroke
32	O-ring	2	KA00309	KA00311	KA00311	KA00320	KA00402	KA00777	KA00777
			(ø4 x ø1.8 x ø1.1)	(ø5.1 x ø3 x ø1.05)	(ø5.1 x ø3 x ø1.05)	(ø7.15 x ø3.75 x ø1.7)	(ø8.3 x ø4.5 x ø1.9)	_	_
46	Side scraper	2	_	_	_	_	_	MYM50-15CK0502B	MYM63-15CK0503B
25	Scraper	2 2 2 2	MY1M16-PS	MY1M20-PS	MY1M25-PS	MY1M32-PS	MY1M40-PS	MY1M50-PS	MY1M63-PS
29	Piston seal								
30	Cushion seal								
31)	Tube gasket								
43	O-ring	4							

^{*} The seal kit includes ②, ③, ③, ③, and ④. Order the seal kit based on each bore size.

Order with one of the following part numbers when only the grease pack is required.

Grease pack part no.: GR-S-010 (10 g), GR-S-020 (20 g)

Note) Two kinds of dust seal bands are available. Since the part number varies depending on the treatment of the hexagon socket head set screw ③, confirm before ordering.

A: Black zinc chromated \rightarrow MY \square -16B-stroke, B: Nickel plated \rightarrow MY \square -16BW-stroke



^{*} The seal kit includes a grease pack (10 g).

When (5) and (6) are shipped independently, a grease pack is included. (10 g per 1000 strokes)