

Non-Grease Blow Gun


SMC CORPORATION
1-16-4 Shimbashi, Minato-ku
Tokyo 105-0004, JAPAN
URL: <http://www.smcworld.com>

XT567-10

Feature 1: Non-Grease Specifications

Using no grease for the wetted parts (sealing parts).


Feature 2: Pen Type



Specifications

Model	XT567-10
Fluid	Air
Operating pressure range	0.1 ~ 1.0MPa
Proof pressure	1.5MPa
Ambient and fluid temperature	- 5 ~ 60°C (with no condensation)
Effective area	3.5 mm ²
Nozzle size	2
Port size	Rc1/8
Piping entry	Back side
Operational force (when the valve is fully open)	9N (supply pressure 0.5MPa)
Weight	100g

Dimensions: mm



NO.	Description	Material
	Body	Aluminium alloy
	Lever	Aluminium alloy
	Nozzle	Aluminium alloy
	Valve guide	Aluminium alloy
	Valve	Sainless steel
	Spring	Sainless steel
	Valve	FPM
	Plate	Sainless steel
	Snap ring	Sainless steel
	Straight pins	Sainless steel
	O-ring	FPM
	O-ring	FPM
	O-ring	FPM
	Cross recessed head screws	Sainless steel
	Label	Polyester



Caution: To ensure the safest possible operation of this product, please be sure to read thoroughly the "Safety Instructions" in our "Best Pneumatics" general catalog before use.