

Simple Specials: -XA1 to XA23/-XA26 to XA30: Change of Rod End Shape

These changes are dealt with Simple Specials System. Refer to the front matter pages for details.

4 CQ2/RQ/CLQ (ø32 to ø100)/CQ2 large bore size (ø125 to ø200) : Change of Rod End Shape

Applicable Series

Series		Action	Symbol for change of rod end shape
CQ2	Standard type	CQ2-Z	XA1 to 23 XA26 to 30
		CQ2W-Z	
	Axial piping type (Centralized piping type)	CQP2	
		CQ2-S-Z	
	Anti-lateral load	CQ2-Z	
	Long stroke	CQ2K-Z	
Non-rotating rod type	CQ2K-Z	XA1/XA2/XA6 XA10 to XA14 XA19/XA21	
	CQ2KW-Z	XA1 to 23 XA26 to 30	

Note) Single acting, spring extend type is available as a special order.

Series		Action	Symbol for change of rod end shape
CQ2	Large bore size ø125 to ø200	CQ2-Z	XA1 to 23 XA26 to 30
		CQ2W-Z	
RQ	Standard type	RQ	XA1 to 23 XA26 to 30
CLQ	With lock	CLQ	XA1 to 23 XA26 to 30

⚠ Precautions

- SMC will make appropriate arrangements if no dimension, tolerance, or finish instructions are given in the diagram.
- Standard dimensions marked with "*" will be as follows to the rod diameter (D).
Enter any special dimension you desire.
D – 2 mm
- In the case of double rod, fill in the dimension when the rod is retracted.

<p>Symbol: A1</p>	<p>Symbol: A2</p>	<p>Symbol: A3</p>	<p>Symbol: A4</p>
<p>Symbol: A5</p>	<p>Symbol: A6</p>	<p>Symbol: A7</p>	<p>Symbol: A8</p>
<p>Symbol: A9</p>	<p>Symbol: A10</p>	<p>Symbol: A11</p>	<p>Symbol: A12</p>

Simple Specials: Change of Rod End Shape

Symbol

-XA1 to XA23/-XA26 to XA30

<p>Symbol: A13</p>	<p>Symbol: A14</p>	<p>Symbol: A15</p>	<p>Symbol: A16</p>
<p>Symbol: A17</p>	<p>Symbol: A18</p>	<p>Symbol: A19</p>	<p>Symbol: A20</p>
<p>Symbol: A21</p>	<p>Symbol: A22</p>	<p>Symbol: A23</p>	<p>Symbol: A26</p>
<p>Symbol: A27</p>	<p>Symbol: A28</p>	<p>Symbol: A29</p>	<p>Symbol: A30</p>

-X□