

Made to Order Common Specifications: -XB10A: Intermediate Stroke (Spacer-installed type)



6 Intermediate Stroke (Spacer-installed type)

Symbol
-XB10A

Intermediate stroke: Available in 1 mm increments. A spacer is installed on tubes with a stroke longer than the specified stroke (● in the below table).

Applicable Series

Series	Model	Action	Note
CQ2	Standard type	CQ2-Z	Double acting, Single rod
			ø32 to ø100

Applicable Stroke

Intermediate stroke with ○: Available in 1 mm increments.

A spacer is installed on tubes with a stroke longer than the specified stroke (●).

◆: Standard stroke ●: Stroke in stock

Bore size (mm)	Stroke range	Type	Stroke																			
			55	60	65	70	75	80	85	90	95	100	55	60	65	70	75	80	85	90	95	100
32, 40	51 to 94	Spacer-installed type 2	○	●	○	●	○	●	○	●	○	●	○	●	○	●	○	●	○	●	○	●
50 to 100	51 to 94		○	●	○	●	○	●	○	●	○	●	○	●	○	●	○	●	○	●	○	●


Note) Specify a spacer-installed type 1 with standard model number for ordering an intermediate stroke with a * mark. Refer to the CQ2 series, page 775 for details.

Specifications: Same as standard type

How to Order **C□Q2** **Standard model no.** **-XB10 A**
 Intermediate stroke ●
 Spacer-installed type ◆

Order no.	CQ2B32-57DZ-XB10A (uses 60 mm stroke tube)
	● CQ2B32-60DZ-XB10 with 3 mm width spacer inside
	● The B dimension is 93 mm.

Dimensions: CQ2 Series



Symbol Stroke	A																B							
	51 to 54	56 to 59	61 to 64	66 to 69	76 to 79	81 to 84	86 to 89	91 to 94	51 to 54	56 to 59	61 to 64	66 to 69	76 to 79	81 to 84	86 to 89	91 to 94								
Bore size	95	100	105	110	120	125	130	135	88	93	98	103	113	118	123	128								
32	101.5	106.5	111.5	116.5	126.5	131.5	136.5	141.5	94.5	99.5	104.5	109.5	119.5	124.5	129.5	134.5								
40	103.5	108.5	113.5	118.5	128.5	133.5	138.5	143.5	95.5	100.5	105.5	110.5	120.5	125.5	130.5	135.5								
50	109	114	119	124	134	139	144	149	101	106	111	116	126	131	136	141								
63	118.5	123.5	128.5	133.5	143.5	148.5	153.5	158.5	108.5	113.5	118.5	123.5	133.5	138.5	143.5	148.5								
80	130	135	140	145	155	160	165	170	118	123	128	133	143	148	153	158								
100																								