



# CUK Series ø10, ø16, ø20, ø25, ø32



## Construction

With auto switch

ø10



ø16 to ø32



\* The numbers correspond with those in the "Construction" of the CUK series in the Best Pneumatics catalog.

### Seal Kit List

No.	Description	Material	Note
19	Piston seal	NBR	
20	Rod seal		
21	Gasket		

### Replacement Parts: Seal Kit

Bore size (mm)	Part no.	Contents
10	CU10D-PS	Set of nos. 19, 20, 21
16	CU16D-PS	
20	CU20D-PS	
25	CU25D-PS	
32	CU32D-PS	

\* ø6 cannot be repaired.

\* The seal kit includes 19, 20, 21. Order the seal kit based on each bore size.

\* The seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is required.


**Grease pack part no.: GR-S-010 (10 g)**

# CUK Series ø10, ø16, ø20, ø25, ø32


## Construction

### Single acting, spring return



ø10



### With auto switch



ø16 to ø32



\* The numbers correspond with those in the "Construction" of the CUK series in the Best Pneumatics catalog.

### Seal Kit List

No.	Description	Material	Note
23	Piston seal	NBR	
24	Gasket		

### Replacement Parts: Seal Kit

Bore size (mm)	Part no.	Contents
10	CU10S-PS	Set of nos. 23, 24
16	CU16S-PS	
20	CU20S-PS	
25	CU25S-PS	
32	CU32S-PS	

\* ø6 cannot be repaired.

\* The seal kit includes 23, 24. Order the seal kit based on each bore size.

\* The seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is required.


**Grease pack part no.: GR-S-010 (10 g)**

# CUK Series ø10, ø16, ø20, ø25, ø32


## Construction

### Single acting, spring extend



ø10



### With auto switch



ø16 to ø32



\* The numbers correspond with those in the "Construction" of the CUK series in the Best Pneumatics catalog.

### Seal Kit List

No.	Description	Material	Note
23	Piston seal	NBR	
24	Rod seal		

### Replacement Parts: Seal Kit

Bore size (mm)	Part no.	Contents
10	CU10T-PS	Set of nos. 23, 24
16	CU16T-PS	
20	CU20T-PS	
25	CU25T-PS	
32	CU32T-PS	

\* ø6 cannot be repaired.

\* The seal kit includes 23, 24. Order the seal kit based on each bore size.

\* The seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is required.

**Grease pack part no.: GR-S-010 (10 g)**

Actuators

Modular F.R.L.  
Pressure Control Equipment

Air Preparation  
Equipment

Industrial Filters

Replacement  
Procedure

Actuators

Modular F.R.L.  
Pressure Control Equipment



Industrial Filters

# CUK Series ø10, ø16, ø20, ø25, ø32



## Construction

With auto switch

ø10



ø16 to ø32



\* The numbers correspond with those in the "Construction" of the CUK series in the Best Pneumatics catalog.

### Seal Kit List

No.	Description	Material	Note
19	Piston seal	NBR	
20	Rod seal		
21	Gasket		

### Replacement Parts: Seal Kit

Bore size (mm)	Part no.	Contents
10	CU10D-PS	Set of nos. 19, 20, 21
16	CU16D-PS	
20	CU20D-PS	
25	CU25D-PS	
32	CU32D-PS	

\* ø6 cannot be repaired.

\* The seal kit includes 19, 20, 21. Order the seal kit based on each bore size.

\* The seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is required.

**Grease pack part no.: GR-S-010 (10 g)**

Actuators

Modular F.R.L.  
Pressure Control Equipment

Air Preparation  
Equipment

Industrial Filters

Replacement  
Procedure

Actuators

Modular F.R.L.  
Pressure Control Equipment

Industrial Filters