Soft Polyurethane Tubing **TUS Series**




Suitable for piping in confined spaces **Extremely flexible** Soft polyurethane tubing

TUS related accessories Inner sleeve

TJ series

Reinforces soft polyuretharane tubing. Insert an inner sleeve into soft polyurethane tubing when used with a



Model

Model	Applicable tubing model	Length	
TJ-0425	TUS0425	18	
TJ-0604	TUS0604	19	
TJ-0805	TUS0805	20.5	
TJ-1065	TUS1065	23	
TJ-1208	TUS1208	24	

Specifications

Material	C2700T (Electroless nickel plated)
Wall thickness	0.2 mm

Precautions

Be sure to read this before handling Ithe products. Refer to page 11 for I I safety instructions and pages 14 to I 18 for fittings and tubing precautions.

⚠ Caution

- 1. Use a nylon or polyurethane tubing for general industrial water, otherwise the tube may result in being fallen out or bursted when the max. operating pressure is lower and the surge pressure is occurred.
- 2. Abnormal temperature rise caused by adiabatic compression may result in the tube bursting.
 3. The value of the minimum bending radius
- is measured at the temperature of 20°C as shown in the figure on the right.
- Use inner sleeve, taking the removing force into consideration when used with One-touch fittings.

Model/Specifications



Model		TUS0425	TUS0604	TUS0805	TUS1065	TUS1208	
Tubing O.D.	(mm)	4	6	8	10	12	
Tubing I.D.	(mm)	2.5	4	5	6.5	8	
Black (B)		<u> </u>			_	_	
White (W)		-	-				
Red (R)		-					
Blue (BU)		<u> </u>					
Yellow (Y)							
Green (G)		-	-	-	-	-	
Translucent	Translucent (N)		-	-	-	-	
Yellow brov	vn (YB)	+	+	-	+	+	
Fluid		Air					
Max. operating	20°C	0.6					
pressure	40°C	0.6					
MPa	60°C	0.4					
Operating vacuum pr	essure (kPa) (1)						
Applicable fitting	js	One-touch fitting ⁽²⁾ , Insert tube fitting, Miniature fitting (Hose nipple type) ⁽³⁾					
Min. bending radius (mm)		8	15	15	22	29	
Operating temper	rature	-20 to 60°C (No freezing)					
Material		Polyurethane					
Tube drawing strength (N)	Without inner sleeve	15	60	60	85	110	
(Using One-touch fitting)	With inner sleeve	80	230	250	300	480	


Note 1) The operating vacuum pressure varies depending on the applicable fitting, so refer to the fitting specifications for details.

Note 2) Always use inner sleeve (TJ series) in safety circuit or critical area.


RoHS



Bend the tube into U-form at a temperature of 20°C. Fix one end and close loop gradually. Measure 2R when the tube breaks or is crushed.



How to Order



Made to Order

Multi-core, Multi-color Specification Flat Tubing

Refer to page 689 for details.

Red (Opaque) N Translucent (Material color)

BU Blue (Opaque) YB Yellow brown (Opaque)

