
Rotary Clamp Cylinder: Standard

25A-MK Series



Ø12, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63



- * The coil scraper is not built-in.
- * The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.




Stopper Cylinder/Fixed Mounting Height

25A-RSQ Series

Ø12, Ø16, Ø20, Ø32, Ø40, Ø50

RoHS






^{*} The 25A- series specifications and dimensions are the same as those of the standard model.

Heavy Duty Stopper Cylinder 25A-RSH Series



ø20, ø32



For details, refer to the Web Catalog.

^{*} The 25A- series specifications and dimensions are the same as those of the standard model.