
Pressure Gauge for General Purpose

G43-10-01-X300



How to Order



Internal/external parts copper-free type


Specifications


Type	Back side thread			
Thread type	R			
Pressure range	0-1.0 MPa			
Accuracy	±3% F.S			
Weight	82 g			

* The dimensions and shape may differ in some parts from those of the standard product.

Dimensions

G43-10-01-X300






Pressure Gauge for Clean Regulator/ With Limit Indicator

G46-SRB



How to Order



_		0	Description	G46
		Symbol	Description	G40
_		+		
		2	0.2 MPa	•
		4	0.4 MPa	•
Max. display pressure	7	0.7 MPa	•	
	10	1.0 MPa	•	
	P2 (1)	0.2 MPa, 30 psi	○ (2)	
	P10 (1)	1.0 MPa, 150 psi	O (2)	
		+		
2 Connection thread	01	R 1/8	•	
	02	R 1/4	•	
		+		
3 Option	Nil	_	•	
	M (3)	With M5 (Female thread)	•	
	•	+		
•	Grade	SRB	Component parts: General degreasing Assembly: General production line	•
		+		
5 Attachment	Nil	Without cover ring assembly	•	
	С	Clear cover has no protrusion. (Clear cover is irremovable.)	•	
	C2	Clear cover has protrusion. (Clear cover is removable.) The wrench flats protrude.	•	
		+		
6 Special specification	Nil	_	•	
	X30	Both MPa and psi	(2)	

Note 1) This symbol must be used with Special specification "X30."

For details, refer to the Web Catalog.



Note 2) Under the New Measurement Law, products for overseas use only (SI unit type for use in Japan)

Note 3) To use the pressure gauge with M5 (female thread), attach the joint when piping the tube. For combinations with the special specification products, please consult SMC separately.