SP107X-011E P: OW




# **Electric Stopper Cylinder LEBQ** Series

SMC CORPORATION 4-14-1, SOTO-KANDA, CHIYODA-KU, TOKYO 101-0021, JAPAN URL: http://www.smcworld.com

# Suitable for conveyor lines without an air supply

<Application Example>





Rod end shape Chamfered type, roller type and lever type are available.




- Energy saving: power consumption at rod stoppage is reduced by 60%.
- Height and mounting Compatible with Stopper Cylinder RSQ series

#### Easy setting


#### Easy adjustment on site with the programless controller

- No programming is required.
- Speed, acceleration and position can be set easily with the trimmer switch on the operation panel.
- •No PC or Teaching Box is required.
- 16 gradual adjustments for speed and acceleration
- 14 positioning points
- Applicable to motors with lock Applicable to electric actuators with vertical specifications
- Applicable to Electric Actuator LE series



LEC series controllers that are capable of detailed settings are also applicable to this stopper cylinder.

#### **■**How to Order



### Specifications:


Model			LEBQ32	LEBQ50
Actuator specifications	Stroke (mm)		20	30
	Force (N)		30	150
	Speed (mm/s)		80	135
	Screw lead (mm)		5	8
	Impact/Vibration resistance (m/sec²)		50/20	
	Actuation type		Sliding screw + Cam	
	Operating temp. range (°C)		5 to 40 (No freezing)	
7	Operating humidity range (%)		35 to 85 (No freezing)	
fications	Motor size		□28	□42
	Motor type		Step motor(Servo 24 V DC)	
	Encoder (Angular displacement sensor)		Incremental A/B phase (800 pulse/rotation)	
	Rated voltage (V)		24 V DC ± 10%	
	Power consumption (W)		29	36
	Standby power consumption when operating (W)		10	15
	Momentary max. power consumption(W)		37	46
	Controller weight (kg)	LECP6	0.15 (Screw mounting), 0.17 (DIN rail mounting)	
		LECP1	0.13	

Weight (kg


ਦਿ Rod end shape	LEBQ32	LEBQ50
Chamfered type, Roller type	0.81	1.76
Lever with a shock absorber built-in type	0.9	1.99

- ※ Power consumption means power consumption during operation including the controller.
- \* Standby power consumption when operating means power consumption at standby during operation including that at power saving holding.
- Momentary maximum power consumption means the maximum momentary electric power during operation including the controller. Use this to select power source capacity.


### In case of Program-less Controller (LECP1)



# In case of Program Controller (LECP/A6)




## ■Dimensions: mm【LEBQ32】




- \*The drawing shows the product with motor cover.
- XThe drawing shows the product with the rod chamfer facing the motor.
- \*\*The drawing shows the product with the chamfered type rod end. Refer to Fig.1 and Fig.2 for other specifications.


# ■Dimensions: mm【LEBQ50】




- XThe drawing shows the product with motor cover.
- XThe drawing shows the product with the rod chamfer facing the motor.
- \*The drawing shows the product with the chamfered type rod end. Refer to Fig.1 and Fig.2 for other specifications.

### ■Operating range







- Lever-type mass of transferred object and transfer speed graphs (graphs (2) and (3)) show the values at room temperature (20 to 25°C).
- When selecting cylinders, confirm the Specific Product Precautions as well.

#### ■Precautions

- 1. Since no magnet is mounted in this product, auto switches are not applicable.
- 2. In regard to the mass of the transferred object and the transfer speed, conform to the operating ranges.



Caution To ensure the safest possible operation of this product, please be sure to read thoroughly the "Safety Instructions" in our "Best Pneumatics" catalog before use.

©2010 SMC Corporation All Rights Reserved