
Compact Pressure Switch

Series ZSE2 (For Vacuum)/ISE2 (For Positive Pressure)

For General Pneumatics




Easy and simple wiring

Connector type

Compact Pressure Switch Series ZSE2/ISE2

How to Order



15 NPN open collector 55 PNP open collector

With Connector/How to Order

Without lead wire	Connector 1	nc Socket 3 pr	s) 75-10-A

With lead wire		-ZS-1	0-5A-🏳
Note) When ordering switch with 5 m long lead wire, indicate both part numbers.	Lead wire length		ength •
·		Nil	0.6 m
Ex.) ZSE2-01-15CN1 pc.		30	3 m
ZS-10-5 A-501 pc.		50	5 m
	<u> </u>		

Replacement Element (Filter) Part Number (Refer to page 843)

• Filter vessel assembly (Filter vessel, Filter element)	ZX1-FK-PC
Filter element	ZX1-FE
 Filter gasket 	.ZX1-FG

Compact Pressure Switch Series ZSE2/ISE2

Specifications

For details about the Pressure Switch Precautions, refer to pages 763 and 764. For details about the Specific Product Precautions, refer to the Operation Manual at SMC website. Click here for details.

	Model	ZSE2	ISE2L	ISE2
Model		For vacuum	For low pressure	For positive pressure
Rated pressure	range/Set pressure range	0 to -101 kPa	0 to 100 kPa	0 to 1 MPa
Proof pres	sure	500 kPa 1.5		1.5 MPa
Fluid		Air/Non-corrosive, non-flammable gas		
Power sup	ply voltage	12 to 24 VDC ±10%, Ripple (P-P) 10% or less (With power supply polarity protection)		pply polarity protection)
Current co	nsumption	17 mA or less at 24 VDC		
Response	time	5 ms or less		
Repeatabil	ity	±1% F.S. or less		
월 Enclos	ure	IP40		
8 Enclos Operatin Operatin	g temperature range	Operating: 0 to 60°C, Stored: -10 to 60°C (With no condensation and no freezing)		ation and no freezing)
a Operati	ng humidity range	Operating/Stored: 35 to 85%RH (With no condensation)		ensation)
Temperature cha	racteristics(Based on 25°C)	±3% F.S. or less		
Withstand	voltage	1000 VAC for 1 min. (between terminals and housing)		housing)
Insulation	resistance	50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing		een terminals and housing
Port size		01: R 1/8, M5 x 0.8 T1: NPTF 1/8, M5 x 0.8		0.8
FUIT SIZE		0X: With suction filter (For mo	unting on ZX unit) 0R: Base mount t	ype (For mounting on ZR unit)
Weight		35 g (Including 0.6 m-Long lead wire))
Lead wire	Grommet type	Oilproof heavy-duty vinyl cable 3 cores, ø3.4, Conductor area: 0.2 mm ² , Insulator O.D.:		2 mm ² , Insulator O.D.: 1.1 mm
Leau Wire	Connector type	Heat-resistant vinyl electric	wire, 3-wire, Conductor area: 0.31 m	m ² , Insulator O.D.: 1.55 mm
Standard		CE/UKCA marking		


Output Specifications

		ב וופר
–15	-55	ISC
NPN open collector 30V, 80 mA or less	PNP open collector 80 mA or less	70M
1 V or less (With load current of 80 mA)		ZSN
1		
3% F.S. or less (Fixed)		
ON: when output is ON (Red)		
	200°	
	NPN open collector 30V, 80 mA or less 1 V or less (With le 3% F.S. o ON: when ou	NPN open collector 30V, 80 mA or less PNP open collector 80 mA or less 1 V or less (With load current of 80 mA) 1 3% F.S. or less (Fixed) 3

Series ZSE2/ISE2

Calibration Procedure

 Set the ON-pressure by the pressure setting trimmer. Turning clockwise can set the high pressure/high vacuum pressure.



 Set the possible min. pressure for adsorption confirmation. If setting the pressure lower than that, switch becomes ON in case that adsorption is not completely done. If setting the pressure higher than that, switch does not become ON even though it may absorb workpieces.

4	J.		
High vacuum –			
Supply pressu	ire	I	Steady adsorption
Set point -	•		Oleady adsorption
]	Unsteady adsorption
Atmospheric	0]	Non adsorption
Atmospheric	0	,	


Regarding the pressure setting

Caution

Observe the following precautions for setting the vacuum pressure: Use your fingertips to gently turn the screwdriver. Do not use a screwdriver with a large grip or with a tip that does not fit into the trimmer groove because this could strip the groove.

Hysteresis


Hysteresis is the pressure difference between the ON and the OFF pressure of the output signal. The set pressure is the pressure selected to switch from OFF to ON condition.



How to Use Connector

1. Attaching and detaching connectors


- When assembling the connector to the switch housing, push the connector straight onto the pins until the lever locks into the housing slot.
- When removing the connector from the switch housing, push the lever down to unlock it from the slot and then withdraw the connector straight off of the pin.




2. Crimping of lead wires and sockets

Strip 3.2 to 3.7 mm at the end of the lead wires, insert the ends of core wires evenly into the sockets, and then crimp with a crimping tool. When this is done, take care that the coverings of the lead wires do not enter the core wire crimping area.


(Crimping tool: model no. DXT170-75-1)



- 3. Attaching and detaching lead wires with sockets
- Attaching
- Insert the sockets into the square holes of the connector (with +, 0, indication), and continue to push the sockets all the way in until they lock by hooking into the seats in the connector. (When they are pushed in their hooks open and they are locked automatically.) Then confirm that they are locked by ulling lightly on the lead wires.
- Detaching To detach a socket from a connector, pull out the lead wire while pressing the socket's hook with a stick having a thin tip (about 1 mm). If the socket will be used again, first spread the hook outward.



Internal Circuits and Wiring Examples



How to Replace Filter Element

If the filter element becomes clogged, leading to a reduced adsorption force or delayed response time, stop the operation and re-place the element.

(Element part number ZX1-FE) Verify that the filter gasket is placed properly in the gasket groove before installing an element.

(Filter gasket part no.: ZX1-FG) Filter vessel Filter element (ZX1-FE) Filter gasket (ZX1-FG) Gasket groove Filter vessel assembly (Filter vessel + Filter element)

Filter vessel

ZX1-FK-PC


Caution

 Do not use with thinner, carbon tetrachloride, chloroform, acetate, aniline, cyclohexane, trichloroethylene, sulfuric acid, lactic acid and watermiscible cutting fluid (alkaline).
 Operate it away from direct sunlight.

A 854




Dimensions




Series ZSE2/ISE2

Dimensions


Standard Type: ZSE2-⁰¹_{T1} Grommet type: ZSE2-⁰¹_{T1}-15




Base Mount Type: ZSE2-0R Grommet type: ZSE2-0R-15



Connector type: ZSE2- ⁰¹/_{T1}-15C




Connector type: ZSE2-0R-15C




Dimensions

ISE20-01

Grommet type: ISE2- ⁰¹_{T1}-15



Connector type: ISE2- ⁰¹_{T1}-15C



ISE70
ZSE80 ISE80 ZSE
ZSE□ ISE□
ZSP
PS
ISA2
PSE
IS
ISG
ZSM1

ZSE30 ISE30

ZSE40 ISE40

ZSE10 ISE10