Peltier-Type Thermoelectric Bath

Accurately controls the temperature of liquid in the bath. Square type is newly added to the product lineup.



_iahtweiaht

Current consumption 3.5 A to 6 A Power supply voltage 100 VAC to 240 VAC (Except for some models)



Peltier element

Low vibration and high accuracy when compared to the refrigerator.

Temperature sensor

Direct measurement of liquid temperature. Excellent display accuracy.

Circulating pump

Agitation by built-in circulating pump. Reduces the temperature distribution inside the bath.

Drain port Allows the liquid to drain without raising the equipment.

Application Examples



Temperature control of sample



Temperature control of source gas for MO-CVD or diffusion furnace



■Related Products

OFluoropolymer piping equipment Refer to the Web Catalog for details.

Fittings LQ1/LQ3 Series



Bore through connector LQHB Series











■ Variations

Model		Usable constant temperature liquid	Cooling method	Cooling capacity	Tank capacity	Temperature range	Temperature stability	
	INR-244-745 INR-244-733		Water-cooled	140 W	Approx. 10 L	0 to 60°C	±0.03°C	
	INR-244-747 INR-244-736	Water Ethylene glycol aqueous solution Fluorinated fluid (Square type can be used only at normal temperature.)	vvaler-cooled	320 W	Арріох. 10 Е	0 10 00 0	10.03 0	
	INR-244-746 INR-244-734		Water-cooled	320 W	Approx. 23 L	0 to 60°C	±0.03°C	
	INR-244-749 INR-244-748				Approx. 39 L			
	INR-244-757		(Square type can be used	Air-cooled	220 W	Approx. 17 L	0 to 60°C	±0.03°C
	HEBC002-WA10		Water-cooled	140 W	Approx. 3 L	−15 to 60°C	±0.02°C	
	INR-244-696A			280 W	Approx. 5.5 L			

Peltier-Type Thermoelectric Bath Lineup



Specifications	Square type, water-cooled				
Model	INR-244-745	INR-244-733	INR-244-747	INR-244-736	
Cooling method	Peltier, Water-cooled		Peltier, Water-cooled		
Cooling capacity*1	140 W (at 20°C Water)		320 W (at 20°C Water)		
Dimensions (W x D x H)	266 x 376 x 400 mm		266 x 376 x 400 mm		
Tank capacity (W x D x H)	216 x 216 x 250 mm (Approx. 10 L)		216 x 216 x 250 mm (Approx. 10 L)		
Weight	Approx. 15.5 kg		Approx. 16.5 kg		
Power supply voltage range	100 VAC to 240 VAC		100 VAC to 240 VAC		
Rated current (at 100 VAC)	3.5 A		5.5 A		
Liquid temperature range	0 to 60°C		0 to 60°C		
Temperature stability	±0.03°C		±0.03°C		
Communications	RS-232C	RS-485	RS-232C	RS-485	
Safety standards	dards CE/UKCA marking		(NRTL) standard,	RoHS	



Specifications	Square type, water-cooled				
Model	INR-244-746	INR-244-734	INR-244-749	INR-244-748	
Cooling method	Peltier, Water-cooled		Peltier, Water-cooled		
Cooling capacity*1	320 W (at 25°C Water)		320 W (at 25°C Water)		
Dimensions (W x D x H)	350 x 510 x 400 mm		350 x 510 x 550 mm		
Tank capacity (W x D x H)	300 x 350 x 250 mm (Approx. 23 L)		300 x 350 x 400 mm (Approx. 39 L)		
Weight	Approx. 21 kg		Approx. 25 kg		
Power supply voltage range	100 VAC to 240 VAC		100 VAC to 240 VAC		
Rated current (at 100 VAC)	5.5 A		5.5 A		
Liquid temperature range	0 to 60°C		0 to 60°C		
Temperature stability	±0.03°C		±0.03°C		
Communications	RS-232C	RS-485	RS-232C	RS-485	
Safety standards	CE/UKCA marking, UL (NRTL) standard, RoHS				



Specifications	Square type, air-cooled		
Model	INR-244-757		
Cooling method	Peltier, Air-cooled		
Cooling capacity	220 W (at 25°C Water, Ambient temperature 25°C)		
Dimensions (W x D x H)	350 x 460 x 395 mm		
Tank capacity (W x D x H)	300 x 290 x 200 mm (Approx. 17 L)		
Weight	Approx. 22 kg		
Power supply voltage range	100 VAC to 240 VAC		
Rated current (at 100 VAC)	6 A		
Liquid temperature range	0 to 60°C		
Temperature stability	±0.03°C		
Communications	RS-232C		
Safety standards	CE/UKCA marking, RoHS		



Specifications	Round type, water-cooled/Remote controller			
Model	HEBC002-WA10/HEBC002-WB10			
Cooling method	Peltier, Wa	Peltier, Water-cooled		
Cooling capacity*1	140 W (at 25°C Water)			
Dimensions (W x D x H)	Liquid tank 200 x 207 x 332 mm	Controller 250 x 300 x 180 mm		
Tank capacity	ø130 x 188 mm (Approx. 3 L)	_		
Weight	Approx. 8.5 kg	Approx. 6.5 kg		
Power supply voltage range	100 VAC to 240 VAC			
Rated current (at 100 VAC)	4 A			
Liquid temperature range	−15 to 60°C			
Temperature stability	±0.02°C			
Communications	RS-485/RS-232C			
Safety standards	CE/UKCA marking, UL (NRTL) standard, RoHS			



Specifications	Round type, water-cooled/Remote controller			
Model	INR-244-696A			
Cooling method	Peltier, Water-cooled			
Cooling capacity*1	280 W (at 25°C Water)			
Dimensions (W x D x H)	Liquid tank 240 x 240 x 350 mm	Controller 220 x 330 x 123 mm		
Tank capacity	ø170 x 202 mm (Approx. 5.5 L)	_		
Weight	Approx. 12 kg	Approx. 5 kg		
Power supply voltage range	200 VAC to 220 VAC			
Rated current (at 200 VAC)	5 A			
Liquid temperature range	-15 to 60°C			
Temperature stability	±0.02°C			
Communications	RS-485			
Safety standards	RoHS			

^{*1} Conditions: Facility water temperature 20°C, flow rate 5 L/min, ambient temperature 25°C

