Vacuum Ejector Variations

| | ZH□A | | | | | | | ZU□A | | | | |
|--|--------|---|-----|-----|-----|-----|-----|------|---|-----|-----|-----|
| Series | | 0.745 | | | | | | | p. 773 | | | |
| Features | | Can be connected with the combination of a one-touch and a screw-in connection. | | | | | | | Vacuum port and supply port are located collinearly to facilitate piping. | | | |
| Vacuum pump system | | | | | | | | | | | | |
| Nozzle diameter [mm] | | 0.5 | 0.7 | 1.0 | 1.3 | 1.5 | 1.8 | 2.0 | 0.3 | 0.4 | 0.5 | 0.7 |
| Max. suction flow [L/min(ANR)] | Type S | 6 | 12 | 26 | 40 | 58 | 76 | 90 | 1.8 | 3.2 | 7 | 11 |
| | Type L | 13 | 28 | 52 | 78 | 78 | 128 | 155 | 3.4 | 5.8 | 13 | 16 |
| Air consumption [L/min(ANR)] | | 13 | 27 | 52 | 88 | 117 | 165 | 201 | 4.2 | 7.7 | 14 | 28 |
| Guidelines for applicable pad diameter [mm]* | 2 | • | • | • | • | • | • | • | • | • | • | • |
| | 4 | • | • | • | • | • | • | • | • | • | • | • |
| | 6 | • | • | • | • | • | • | • | • | • | • | • |
| | 8 | • | • | • | • | • | • | • | • | • | • | • |
| | 10 | • | • | • | • | • | • | • | | • | • | • |
| | 13 | • | • | • | • | • | • | • | | | • | • |
| | 16 | | • | • | • | • | • | • | | | | • |
| | 20 | | • | • | • | • | • | • | | | | • |
| | 25 | | | • | • | • | • | • | | | | |
| | 32 | | | • | • | • | • | • | | | | |
| | 40 | | | | • | • | • | • | | | | |
| | 50 | | | | • | • | • | • | | | | |
| | 63 | | | | | • | • | • | | | | |
| | 80 | | | | | • | • | • | | | | |
| | 100 | | | | | • | • | • | | | | |
| | 125 | | | | | | • | • | | | | |
| | 150 | | | | | | | • | | | | |
| Silencer | | • | | | | | | | | | | |
| Clamp mount (L-br | • | | | | | | | | | | | |
| Single unit, Width | | 14 to 22 | | | | | | | 8.2 to 10.4 | | | |
| Single unit, Weight [g] | | 5 to 46.2 | | | | | | | 2.4 to 4.3 | | | |