RoHS

Directional Control Valves

Air Cylinders

Rotary Actuators


Grippers

Air


Preparation

For general pneumatic tubing **Flexible** Polyurethane tubing





#### **Burst Pressure Characteristics Curve and Operating pressure**



			-	ubing size			
	Inch size (Series TIUB)			Metri	c size es TU)		
Model	10-TIUB01	10-TU0212	10-TU0425	10-TU0604	10-TU0805	10-TU1065	10-TU1208
O.D. (mm)	3.2	2	4	6	8	10	12
I.D. (mm)	2	1.2	2.5	4	5	6.5	8
Black (B) White (W) Red (R) Blue (BU) Yellow (Y) Green (G) Clear (C)							
Orange (YR)							

# **∧** Precautions

Be sure to read this before handling. Refer to page 1382 for Safety In-I I structions and pages 1237 to 1240 I for Fittings and Tubing Precautions.

### **⚠** Caution

- Applicable for general industrial water.

  Please consult with SMC if using for the other kind of fluid. Also, the surge voltage pressure must be under the maximum operating pressure. If the surge pressure exceeds the maximum operating pressure, it will result in damage to fittings and tubes.
- 2. The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures. Furthermore, abnormal temperature rises caused by adiabatic compression may result in the burst of the tube.
- 3. The value of the minimum bending radius is measured at the temperature of 20°C as shown in the figure on the right.

Specifications							
Fluid	Air, Water						
Max. operating pressure (20°C)	0.8 MPa						
Burst pressure	Refer to the burst pressure characteristics curve.						
Recommended fittings	Clean series fittings 10-KQ2, 10-KF, 10-KDM, 10-KG 10-M, 10-MS, KP, KPQ, KPG						3
Min. bending radius (mm)	10	4	15	20	27	35	5
Operating temperature	-20 to 60°C, Water: 0 to 40°C (No freezing)						
Material	Polyurethane						
Cleanliness class (ISO class)			Clas	s 3			



Bend the tube into U-form at a temperature of 20°C. Fix one end and close loop gradually. Measure 2R when the tube breaks or is crushed.


**ØSMC** 

RoHS

# For flexible tubing Compact piping possible



# **Burst Pressure Characteristics Curve and Operating Pressure**



#### **Specifications**

Model	10-TCU 0425B-1	10-TCU 0425B-2	10-TCU 0425B-3	10-TCU 0604B-1	10-TCU 0604B-2	10-TCU 0604B-3	10-TCU 0805B-	
Number of cores	1	2	3	1	2	3	1	
Tubing O.D. (mm)		4	•		6	•	8	
Tubing I.D. (mm)	2.5 4					5		
Fluid	Air							
Max. operating pressure (20°C)	0.8 MPa							
Burst pressure	Refer to the burst pressure characteristics curve.							
Recommended fittings	Clean series fittings 10-KQ2, 10-KF, 10-KDM, 10-KG 10-M, 10-MS, KP, KPQ, KPG							
Operating temperature			-2	0 to 60	°C			
Material	Polyurethane							
Color				Black				
Cleanliness class (ISO class)	Class 3							


# **⚠** Precautions

Be sure to read this before handling.
Refer to page 1382 for Safety
Instructions and pages 1237 to 1240
for Fittings and Tubing Precautions.

#### 

- 1. Please consult with SMC regarding use with any fluids other than air.
- The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures.
  - Furthermore, abnormal temperature rises caused by adiabatic compression may result in the burst of the tube.
- Please do not cut the coil and insert it into the fitting. This may cause air leakage, or tubing to come out after installation.

#### **Dimensions**




	Specifications	Tubing s	ize (mm)			Number	No. of coil windings per	Max. operating
Model		O.D.	I.D.	L	D	of cores	tubing length	length (m)
10-TCL	J0425B-1			210	18	1	52±2	1.5
10-TCL	J0425B-2	4	2.5	280	28	2	35±1	1.5
10-TCL	J0425B-3			265	20	3	22±1	1
10-TCL	J0604B-1			325	24	1	54±2	2
10-TCL	J0604B-2	6	4	323	37	2	27±1	1.5
10-TCL	J0604B-3		Ī	305	37	3	17±1	1
10-TCL	J0805B-1	8	5	330	31	1	41±2	2

<sup>\*</sup> The number of coil windings per tube length and dimensions are changeable due to material.

Compact piping possible



#### **Burst Pressure Characteristics Curve and Operating Pressure**



# 

Be sure to read this before handling. IRefer to page 1382 for Safety I Instructions and pages 1237 to 1240 for Fittings and Tubing Precautions.

## **⚠**Caution

- 1. Please consult with SMC regarding use with any fluids other than air.
- 2. The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures.
  - Furthermore, abnormal temperature rises caused by adiabatic compression may result in the burst of the tube.
- 3. The value of the minimum bending radius is measured at the temperature of 20°C as shown in the figure on the right.
- 4. As a result of product design characteristics, there are cases of very slight leakage.

#### **Specifications**

Model	10-TFU 0425B-2	10-TFU 0425B-3	10-TFU 0604B-2	10-TFU 0604B-3	10-TCU 0805B-2	10-TCL 0805B-	
Number of cores	2	3	2	3	2	3	
Tubing O.D. (mm)	4	1	6	6	8		
Tubing I.D. (mm)	2.	.5	4	1	5		
Fluid			P	\ir			
Max. operating pressure (20°C)			0.8	MPa			
Burst pressure	Refe	r to the bu	ırst press	ure charac	cteristics o	urve.	
Recommended fittings	Clean	series fitti		02, 10-KF 10-MS, k			
Operating temperature			–20 to	60°C			
Material			Polyur	ethane			
Color	Black						
Min. bending radius (mm)	10 15 20						
Tubing length per roll (m)			1	0			
Cleanliness class (ISO class)			Cla	ss 3			




Bend the tube into U-form at a temperature of 20°C. Fix one end and close loop gradually. Measure 2R when the tube breaks or is crushed.


#### How to Order

RoHS





#### **Burst Pressure Characteristics Curve and Operating Pressure**



#### Model

TPH0604 Model **TPH0425 TPH0806** TPH1075 TPH1209 O.D. (mm) 6 8 10 12 I.D. (mm) 2.5 4 6 7.5 9 White (W) Black (B) Red (R) Blue (BU) Yellow (Y) • Green (G)

Specification	ıs
---------------	----

Fluid	Air, N	Air, Nitrogen gas, Water (Deionized water) Note 1						
Max. operating pressure (20°C)	1.0	1.0 MPa <sup>Note 2)</sup>			0.7 MPa <sup>Note 2)</sup>			
Min. bending radius (mm)	15		25	35	45	55		
Burst pressure	Refer	to the	burst	pressure cl	naracteristi	cs curve.		
Operating temperature	-20	-20 to 80°C, for water 5 to 80°C (No freezing)						
Material		Polyolefin resin						
Cleanliness class (ISO cla	iss)	Class 3						

- Note 1) Please consult with SMC regarding other fluids.
- Note 2) The maximum operating pressure is the value at 20°C. Refer to the burst pressure characteristics curve for other temperatures. Furthermore, an abnormal temperature rise due to adiabatic compression can cause tubing to burst.
- Note 3) The minimum bending radius indicates the value at a temperature of 20°C with an outside diameter change rate of 10% or less. At higher temperatures, the outside diameter change rate may exceed 10% within the minimum bending radius.

### **⚠** Caution

- The TPH series was specially designed for clean blowing and washing lines. Please consult with SMC for use in other applications.
- Materials: The durability of polyolefin resin against mineral oils is inferior. Because of this, it is unsuitable for general pneumatic equipment lines.



 Length per roll Symbol

20

100

Length

20 m roll

100 m reel

TPS0604 B Tubina model Color

60

**Burst Pressure Characteristics Curve and Operating Pressure** 

1 Max. operating pressure

Operating temperature °C

	00101
Symbol	Color
W	White
В	Black
R	Red
BU	Blue
Y	Yellow
G	Green

Model				●–20 m rol	I □-100 m ree
Model	TPS0425	TPS0604	TPS0805	TPS1065	TPS1208
O.D. (mm)	4	6	8	10	12
I.D. (mm)	2.5	4	5	6.5	8
White (W) Black (B) Red (R) Blue (BU) Yellow (Y) Green (G)					

Sp	20	ifir	٦	i۸	ne

Fluid	Air,	Air, Nitrogen gas, Water (Deionized water) Note 1)							
Max. operating pressure (20°C)		0.7 MPa <sup>Note 2)</sup>							
Min. bending radius (mm)	10	20	25	30	40				
Burst pressure	Refer	Refer to the burst pressure characteristics curve.							
Operating temperature	-20	-20 to 80°C, for water 0 to 80°C (No freezing)							
Material		Polyolefin resin							
Cleanliness class (ISO cla	ss)	Class 3							

Note 1) Please consult with SMC regarding other fluids.

Note 2) The maximum operating pressure is the value at 20°C. Refer to the burst pressure characteristics curve for other temperatures. Furthermore, an abnormal temperature rise due to adiabatic compression can cause tubing to burst.

Note 3) The minimum bending radius indicates the value at a temperature of 20°C with an outside diameter change rate of 10% or less. At higher temperatures, the outside diameter change rate may exceed 10% within the minimum bending radius.

## **⚠** Caution

Burst pressure MPa

- The TPS series was specially designed for clean blowing and washing lines. Please consult with SMC for use in other applications.
- Materials: The durability of polyolefin resin against mineral oils is inferior. Because of this, it is unsuitable for general pneumatic equipment lines.