## For 4 Axes

# Simple Controller



## End to end

2-point operation is possible without programming!

- Reduced setting labor
  Only the speed and force need to be set
- Reduced wiring labor
  Only 2 inputs/outputs\*1
  \*1 Per axis




Space saving


63

86


Footprint Reduced by up to approx. 79%

Single-axis controller (LECP6) x 4 controllers






4-axis controller (JXC73/83/93)












#### **Specifications**

Model	JXC□4-X1
Number of axes	4 axes
Compatible motor	Step motor (Servo/24 VDC) □42/□28/□20
Power supply	Power voltage: 24 VDC ±10%
Power consumption	Power consumption depends on the actuator size connected. Refer to the actuator specifications for further details.
Operating temperature range	0 to 55°C (No freezing)
Operating humidity range	90% or less (No condensation)
Enclosure	IP10
Insulation resistance	Between all external terminals and the case 50 $M\Omega$ (500 VDC)
Weight	300 g (DIN rail mounting), 390 g (Screw mounting)
Applicable actuator	LEY Series (Size 16, 25 * Excluding the LEYG)

#### **Dimensions**



↑ Safety Instructions | Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

### **SMC** Corporation

Akihabara UDX 15F

4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362

https://www.smcworld.com

© 2020 SMC Corporation All Rights Reserved