

Direct Operated 2-Port Solenoid Valve

CE UK CULISTED CALUS ROHS







* IP65 for models with

CE marking compliance depends on the voltage and electrical entry. (Refer to page 3 for details.) This product is not compliant with EU drinking water directive 2020/2184 nor regulation (EC) No. 1935/2004 safety requirements



HF3-JSX Series



NSF/ANSI 61 certification



Variations

Model	Port size	Orifice diameter		Flow rate*1 [L/min]		Fluid	Body	Valve	Seal	Electrical entry	Standards
Model	FUIT SIZE	[mmø]	5 1	0 2	90 30		Tulu	material	type	material	Electrical entry	Statituatus
HF3-JSX10 Series	1/8	1.6, 2.4	5	(For orif	ice diameter ø2	:.4)						NSF/ANSI 61
HF3-JSX20	1/8	3.2		4.5			Water	Stainless	N.C.	NBR	Grommet DIN terminal	UK CA
Series	1/4, 3/8	3.2, 4.0, 5.6, 7.1		15 (For orifice diame	ice diameter ø5			steel	N.C.		Conduit M12 connector	C UL US LISTED
HF3-JSX30 Series	1/4, 3/8	4.0, 5.6, 7.1	(For d	orifice diamete	25 ers ø4.0 and ø5	5.6)						c Tus us * Refer to pages 3, 5, and 6 for details.

^{*1} At the max. operating pressure differential (Fluid: Water)




Space saving

Compact
Valve volume:

25% reduction*1

Lightweight
Weight:
30% reduction*1

*1 Compared with the existing model



Full-wave rectifier type

(AC specification: Insulation type Class B)

Improved durability

Extended service life due to the special construction (Compared with the existing shading coil)

Reduced buzzing noise

Due to being rectified to DC by the full-wave rectifier

Reduced apparent power

* Class B, N.C. valve (Compared with the existing model)

 $9.5 \text{ VA} \rightarrow 8 \text{ VA}$ (HF3-JSX20 Series) 12 VA \rightarrow **9.5** VA (HF3-JSX30 Series)

Low-noise construction

Specially constructed to reduce metal noise during operation

Electrical entry variations





DIN terminal

M12 connector



NSF/ANSI 61 certification

Direct Operated 2-Port Solenoid Valve

F3-JSX Series

Body Material Stainless Steel



electrical entry.

For details, refer to the Web Catalog.

*1 This product is not compliant with EU drinking water directive 2020/2184 nor regulation (EC) No. 1935/2004 safety requirements for materials and articles intended to come into contact with food.






For details, refer to pages 5 and 6.





For Water

How to Order





a	Siza
ш) Size

Symbol	Size
1	10
2	20
3	30

2 Valve type

Symbol	Valve type					
1	N.C.	2(OUT) 				

Body material

	ouy material
Symbol	Body material
S	Stainless steel

A Electrical entry

<u> </u>	Electrical entry	<u>/</u>					
Symbol	Electrical e	entry	_	Size	_	CE/UKCA-	UL Standards
		, _	10	20	30	compliant	
G	Grommet*1					24 VDC	
<u> </u>	Grommot					12 VDC	
						100 VAC	
	Grommet with PCB					24 VDC	
GS	(With surge voltage		•	•	•	12 VDC	
	suppressor)*2					48 VAC	
						24 VAC	
cs	Conduit (With surge voltage suppressor)		_	•	•	All voltages	
DS	DIN terminal (With surge voltage suppressor)		•	•	•	All voltages	For details, refer to page 6.
DZ	DIN terminal with light (With surge voltage suppressor)		•	•	•	All voltages	. 0
DN	DIN terminal without connector (With surge voltage suppressor)		•	•	•	All voltages	
WN	M12 connector/Without connector cable (With surge voltage suppressor)*3		•	•	•	All voltages	

4 Seal material

Symbol	Seal material
N	NBR

6 Thread type

Symbol	Thread type
R	Rc
N	NPT
F	G

5 Orifice diameter and port size

Cumbal	Orifice diameter	Port size		Size	
Symbol	[mmø]	Port Size	10	20	30
101	1.6	1/8	•	_	_
201	2.4	1/8	•	_	_
301		1/8	_	•	_
302	3.2	1/4	_	•	_
303		3/8	_	•	_
402	4.0	1/4	_	•	•
403		3/8	_	•	•
502	- 6	1/4	_	•	•
503	5.6	3/8	_	•	•
702	7.1	1/4	_	•	•
703	7.1	3/8	_	•	•

Rated voltage

AC				DC	
Symbol	Rated voltage	Symbol	Rated voltage	Symbol	Rated voltage
1	100 VAC	7	240 VAC	5	24 VDC
2	200 VAC	8	48 VAC	6	12 VDC
3	120 (110) VAC	В	24 VAC		
4	220 VAC	J	230 VAC		

9 Option

Symbol	Option
Nil	None
В	With bracket*1 (Stainless steel)

^{*1} Bracket assembly part nos. (Refer to the Web Catalog.)

- *1 DC voltage only
- *2 Any voltage can be selected, but only the voltages listed in the table are compliant with CE/UKCA.
- *3 A cable for the M12 connector is not included with the product. Refer to "Option" on the Web Catalog to order it separately.

Specifications

Size	10	20	30				
Fluid and fluid temperature	Water:	Water: 1 to 60°C (No freezing)					
Fluid temperature for NSF/ANSI 61 certification compliance		23°C					
Standards		NSF/ANSI 61, CE, UKCA, UL Recognized, UL Listed					
Body material		Stainless steel					
Seal material		NBR					

Specifications not listed are the same as those of the standard product.





Dimensions



Stainless Steel


Body Material

HF3-JSX20 Port Size 1/8


Stainless Steel


Body Material

G: Grommet




G: Grommet





HF3-JSX20, 30 Port Size 1/4, 3/8 Stainless Steel **Body Material**

G: Grommet




									[mm]			
C:	Port						_	Grommet				
Size	size	Α	B	С	D	E	F	J	K			
	1/4	28.1	40	69		12.5		39				
20	3/8		48	69	69	36	36	12.5	12.5	18	39	28.5
	G3/8			72		14		42				
	1/4	28.1	4 40 70	70	78 42	12.5		40	31.1			
30	3/8		40	78			21	40				
	G3/8		48	81		14		43				

* Electrical entries not listed are the same as those of the standard product.





Dimensions: Bracket Options



										[mm]
Size	Port size	A	В	С	D	E	F	G	н	ø J
20	1/8	13	46	7	40	56	1.5	_	_	5.3
20. 20	1/4, 3/8	10	46	4	22	E.C.	1 5	22.2	22.2	F 2
20, 30	G3/8	13	46	4	33	56	1.5	19	20.6	5.3

 Electrical entries not listed are the same as those of the standard product.



NSF/ANSI 61 certification HF3-JSX Series/Specific Product Precautions

Be sure to read this before handling the products. For safety instructions and 2-port solenoid valves for fluid control precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

∧ Caution

- 1. Quality control relating to hygiene is not implemented for this product.
- 2. This product is NSF/ANSI 61-2016 (Drinking Water System Components-Health Effects) certified by UL. Be sure to use the product in accordance with the laws and regulations of the country and region in which it is to be used.
- 3. Please use the product in accordance with the specifications provided in the catalogs/ operation manuals. It is your responsibility to check the suitability for your workpiece and equipment.
- 4. Install filters suitable for the application on the downstream side of the solenoid valve.



HF3-JSX10, 20, 30 Series

Table of UL-compliant Products

Refer to the table below for UL-compliant products



Recognized















JSX11

Carica/Valua tuna
Series/Valve type
HF3-JSX11

	Body material	Seal material	Orifice diameter/Port size	Thread type
-	S	N	101	R
			201	N
				F

Rated voltage	Electrical entry
1	G *1
2	GS
3	DN
4	WN
5	
6	
7	
8	
B	

itry		Op	tion
	_		*

JSX21

Series/Valve typ	oe
HF3-JSX21	П
-	_

	Body material	Seal material	Orifice diameter/Port size	Thread type
_	S	N	301	R
			302	N
			303	F
			402	
			403	
			502	
			503	
			702]
			703	

Rated voltage	Electrical entry
1	G *1
2	GS
3	DN
4	WN
5	
6	
7	
8	
В	
J	



Series/Valve type
HF3-JSX31

	Body material	Seal material	Orifice diameter/Port size	Thread type
_	S	N	402	R
			403	N
			502	F
			503	
			702	
			703	

		l
	Rated voltage	Electrical entry
-	1	G *1
	2	GS
	3	DN
	4	WN
	4 5	
	6	
	7	
	8	
	В	
	J	

Option *

Option

^{*1} Only applicable to rated voltage symbols "5" and "6"



Listed





JSX21

Series/Valve type
HF3-JSX21

Body material	Seal material	Orifice diameter/Port size	Thread type
S	N	301	R
		302	N
		303	F
		402	
		403	
		502	
		503	
		702	
		702	1

	Rated voltage	Electrical entry		Option
_	1	CS	—	*
	2			
	3			
	4			
	5			
	6			
	7			
	8			
	В			
	J			

JSX31

	Series/Valve type
ſ	HF3-JSX31

	Body material	Seal material	Orifice diameter/Port size	Thread type
-	S	N	402	R
			403	N
			502	F
			503	
			702	
			703	

Rated voltage	Electrical entry	Option
1	CS	*
2		
3		
4		
5		
6		
7		
8		
В		
- 1		

⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

⚠ Danger: Danger indicates a hazard with a high level of risk which, If not avoided, will result in death or serious injury.

Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

⚠ Caution: Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

*1) ISO 4414: Pneumatic fluid power - General rules and safety requirements for systems and their components ISO 4413: Hydraulic fluid power - General rules and safety requirements for systems and their components IEC 60204-1: Safety of machinery - Electrical equipment of machines - Part 1: General requirements ISO 10218-1: Robots and robotic devices - Safety requirements for industrial robots - Part 1:Robots

⚠Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
 - 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments. Use under such conditions or environments is not covered.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogs and operation manuals.
 - 3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

⚠ Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing business.

Use in non-manufacturing business is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act.

The new Measurement Act prohibits use of any unit other than SI units in

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
 - *2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

SMC Corporation

Akihabara UDX 15F.

4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362

https://www.smcworld.com

© 2023 SMC Corporation All Rights Reserved