
Longer Life Cylinder



New technology offers at least 4 times better durability



 The maintenance intervals will be extended



 Employs the same specification and dimensions as the existing models, CJ2 Air Cylinder series

High Durability Series

High Durability Series is the series name for the "special specification" that offers superior durability and environmental resistance compared to standard products.

Series Variations

Series	Action	Model	Во	re size [m	nm]	Cushion	Manufacturable stroke		
Selles	Action Model		6 10 16		Custilott	[mm]			
Air cylinder CJ2 series	Double acting, Single rod	CJ2-XB24	•	•	•	Rubber bumper	ø6 : 15 to 200 ø10: 15 to 400 ø16: 15 to 400		



High Durability Series


Longer Life Cylinder Double Acting, Single Rod

CJ2-XB24



ø6, ø10, ø16

How to Order



Mounting

В	Basic						
E	Double-side bossed						
D	Double clevis						
L	Single foot bracket						
M	Double foot bracket						
F	Rod flange						
G	Head flange						

- Foot brackets or flanges are shipped together with the product, but not assembled.
- A double clevis is only available for ø10 and ø16.

6 Rod end bracket

Nil	None						
V	Single knuckle joint						
W	Double knuckle joint						
Т	Rod end cap (Flat type)						
U	Rod end cap (Round type)						

- * A rod end bracket is shipped together with the product, but not assembled.
- Single/Double knuckle joint: ø10 and ø16 only

2 Bore size

6	6 mm
10	10 mm
16	16 mm

Cylinder manufacturable stroke [mm]

Refer to the "Manufacturable Strokes" on page 2.

Auto switch

Nil	Without auto switch
* For ap	plicable auto switches,
refer to	o the table below.

★ Enter the auto switch mounting type (A or B) even when a built-in magnet cylinder without an auto switch is required.

4 Head cover port location

Nil	Perpendicular to axis	
R	Axial	

- For the double clevis, the product is perpendicular to the cylinder axis.
- For the double-side bossed, the product is perpendicular to the cylinder axis.

6 Pivot bracket

	or braonor
Nil	None
N	Pivot bracket is shipped
IN	together with the product.
	rogether with the product.

- * Only for the double clevis type (ø10 and ø16)
- A pivot bracket is shipped together with the product, but not assembled.

8 Number of auto switches

Nil	2
S	1
n	n

Auto switch mounting type

		 •
Α	Rail mounting	_
В	Band mounting	

- For the rail mounting, screws and nuts for 2 auto switches come with the rail.
- Refer to the Web Catalog for
- auto switch mounting brackets.
- ø6: Band mounting only

* Refer to the "Ordering Example of Cylinder Assembly" on page 2.

Applicable Auto Switches / Refer to the Web Catalog for further information on auto switches.


		Electrical	Indicator light	Wiring		Load vo	oltage		Auto swi	ch model		Lea	d wir	e ler	ngth	[m]	Dro wired	Annli	nabla	
Туре	Special function	entry	cator	(Output)			AC	Band mounting Rail mounting		0.5	1	3		None	Pre-wired connector	Applio loa				
		Citiy	ğ	(Output)		DC	ζ)	Perpendicular	In-line	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	(N)	COLLIGECTOL	load		
				3-wire (NPN)		5 V,12 V		M9NV	M9N	M9NV	M9N	•	•		0	_	0	IC circuit		
등		Grommet		3-wire (PNP)		5 V,12 V		M9PV	M9P	M9PV	M9P				0	_	0	IC CIICUII		
switch				2-wire		12 V		M9BV	M9B	M9BV	M9B	•	•		0	_	0			
		Connector		2-wire		12 V		_	H7C	J79C	_	•	-	•		•	_	-		
anto	Diagnostic indication			3-wire (NPN)		5 V,12 V		M9NWV	M9NW	M9NWV	M9NW	•			0	—	0	IC circuit	Dalau	
		Yes	3-wire (PNP)	24 V	3 V, 12 V	_	M9PWV	M9PW	M9PWV	M9PW	•	•	•	0	_	0	IC CIICUIL	Relay, PLC		
state	(2-color indicator)			2-wire		12 V		M9BWV	M9BW	M9BWV	M9BW				0	 —	0	_	1 20	
	Water resistant	Grommet	net 3-wire (NPN)	t		5 V,12 V		M9NAV*1	M9NA*1	M9NAV*1	M9NA*1	0	0	•	0	_	0	IC circuit		
Solid						3-wire (PNP)]	5 V,12 V	I I	M9PAV*1	M9PA*1	M9PAV*1	M9PA*1	0	0		0	_	0	IC CIICUII
တြ	(2-color indicator)			2-wire		12 V 5 V,12 V	_			M9BAV*1	M9BA*1	M9BAV*1	M9BA*1	0	0	•	0	_	0	_
	With diagnostic output (2-color indicator)			4-wire (NPN)]			_	H7NF	_	F79F	•	-	•	0	_	0	IC circuit		
switch			Vaa	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	A96V	A96	•	-	•	_	-	_	IC circuit	-	
Ĭ		Grommet	Yes		1	_	200 V	_	_	A72	A72H	•	_	•	_	_	_			
	anto —						100 V	A93V*2	A93	A93V*2	A93	•	•	•	•	_	_	-		
ΙĦ			No	0		10.1/	100 V or less	A90V	A90	A90V	A90	•	_	•	_	_	_	IC circuit	Relay,	
		Connector	Yes	2-wire	24 V	12 V	_	_	C73C	A73C	_	•	_	•	•	•	_	_	PLĆ	
Reed		Connector	No				24 V or less	_	C80C	A80C	_	•	_	•		•	_	IC circuit		
ш	Diagnostic indication (2-color indicator)	Grommet	Yes			_	_	_	_	A79W	_	•	_	•	_	_	_	_		

- Water-resistant type auto switches can be mounted on the models, but SMC cannot guarantee water resistance. Please contact SMC regarding water-resistant types with the above model numbers.
- *2 The 1 m lead wire is only applicable to the D-A93.
- * Lead wire length symbols: 0.5 m----- Nil (Example) M9NW 1 m----- M (Example) M9NWM 3 m---- L (Example) M9NWL
- 5 m····· Z (Example) M9NWZ
- None N (Example) H7CN
- * Since there are applicable auto switches other than those listed above, refer to the Web Catalog for details.
- Solid state auto switches marked with a "O" are produced upon receipt of order
- The D-A9□/M9□/A7□/A80□/F7□/J7□ auto switches are shipped together, but not assembled. (For the band mounting, only the auto switch mounting brackets are assembled before shipment.)




Symbol

Rubber bumper



Ordering Example of Cylinder Assembly



Mounting D: Double clevis Pivot bracket N: Yes

Rod end bracket W: Double knuckle joint

Auto switch D-M9BW: 2 pcs. Auto switch mounting B: Band mounting

- Pivot brackets, double knuckle joints, and auto switches are shipped together with the product, but not assembled.

Specifications

Bore size [mm]	6	10	16		
Action	Do	uble acting, Single i	rod		
Fluid		Air			
Proof pressure		1 MPa			
Max. operating pressure		0.7 MPa			
Min. operating pressure	0.12 MPa	0.06	MPa		
Ambient and fluid temperatures	Without auto switch: -10°C to 70°C (No freezing) With auto switch: -10°C to 60°C (No freezing)				
Cushion		Rubber bumper			
Lubrication	Not required (Non-lube)				
Piston speed	50 to 750 mm/s				
Allowable kinetic energy	0.012 J	0.035 J	0.090 J		
Stroke length tolerance		+1.0 0			

Manufacturable Strokes

	[mm]
Bore size	Manufacturable stroke
6	15 to 200
10	15 to 400
16	15 to 400

- * The manufacturing of strokes in 1 mm increments is possible. (Spacers are not used.) Produced upon receipt of order.
- * Applicable strokes should be confirmed according to the usage. For details, refer to the "Air Cylinders Model Selection" in the Web Catalog. Note that if the stroke is long, the specifications may not be satisfied due to deflection or other causes.

Mounting and Accessories

lacktriangle ···· Mounted on the product. \bigcirc ··· Can be ordered within the cylinder model. \triangle ··· Order it separately.

	Mounting	Basic	Foot bracket	Flange	Double*1 clevis	Double clevis (including T-bracket)
ard	Mounting nut	•	•	•	_	_
Standard	Rod end nut	•	•	•	•	•
Ste	Clevis pin (including retaining rings)	_	_	_	•	•
	Double clevis (With one-touch connecting pin)	Δ	Δ	Δ	_	_
l _	Single knuckle joint	0	0	0	0	0
Option	Double knuckle joint (including a pin and retaining rings)	0	0	0	0	0
g	Double knuckle joint (With one-touch connecting pin)	Δ	Δ	Δ	Δ	Δ
	Rod end cap (Flat/Round type)	0	0	0	0	0
	Pivot bracket (T-bracket)	_	_	_	0	•

- *1 A double clevis is only available for ø10 and ø16.
- Stainless steel mounting brackets and accessories are also available. Refer to the Web Catalog for details.

Mounting Bracket Part Nos.

Mounting brookst		Bore size [mm]	
Mounting bracket	6	10	16
Foot bracket	CJ-L006C	CJ-L010C	CJ-L016C
Flange	CJ-F006C	CJ-F010C	CJ-F016C
T-bracket*1	_	CJ-T010C	CJ-T016C

*1 A T-bracket is used with double clevis (D).

The mounting pitch and shape of this product with auto switch are the same as those of the Air Cylinder CJ2 series with auto switch. For details, refer to the Web Catalog.

- · Auto Switch Proper Mounting Position (Detection at stroke end) and Mounting Height
- · Min. Stroke for Auto Switch Mounting
- · Operating Range
- · Auto Switch Mounting Brackets/Part Nos.

Moisture Control Tube **IDK Series**

When operating an actuator with a small bore size and a short stroke at a high frequency, dew condensation (water droplets) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.


The operating speed, allowable loads at the rod end, theoretical output, weight, and accessory are equivalent to those of the Air Cylinder CJ2 series. For details, refer to the Web Catalog.






Basic (B)


ø6







Head cover port location Axial location (R)




[mm]

Bore size	Α	В	С	D	F	GA	GB	Н	MM	NA	NB	NC	NDh8	NN	S	SA	Т	Z	ZA
6	15	12	14	3	8	14.5	5	28	M3 x 0.5	16	9.5	7	6_0.018	M6 x 1.0	51.5	49	3	79.5	77
10	15	12	14	4	8	8	5	28	M4 x 0.7	12.5	9.5	_	8_0_0	M8 x 1.0	46	_	_	74	_
16	15	18.3	20	5	8	8	5	28	M5 x 0.8	12.5	9.5	_	10_0.022	M10 x 1.0	47	_	_	75	_




Single foot bracket (L)

ø6



ø10, ø16



Head cover port location Axial location (R)

* The overall cylinder length does not change.

☆ For details of the mounting nut, refer to the **Web Catalog**.


				<u> </u>	, -																					[[mm]
Bore size	Α	В	С	D	F	GA	GB	Н	LB	LC	LH	LT	LX	LY	LZ	MM	NA	NB	NC	NN	S	SA	Т	X	Υ	Z	ZA
6	15	12	14	3	8	14.5	5	28	15	4.5	9	1.6	24	16.5	32	M3 x 0.5	16	9.5	7	M6 x 1.0	51.5	49	3	5	7	79.5	77
10	15	12	14	4	8	8	5	28	15	4.5	9	1.6	24	16.5	32	M4 x 0.7	12.5	9.5	_	M8 x 1.0	46	_	_	5	7	74	_
16	15	18.3	20	5	8	8	5	28	23	5.5	14	2.3	33	25	42	M5 x 0.8	12.5	9.5	_	M10 x 1.0	47	 —	_	6	9	75	_






Double foot bracket (M)

ø6



ø10, ø16




☆ For details of the mounting nut, refer to the Web Catalog.

_	· · · · · · · · · · · · · · · · · · ·			9 .	,	00				э.														[mm]
	Bore size	Α	D	F	GA	GB	Н	LB	LC	LH	LS	LT	LX	LY	LZ	MM	NA	NB	NN	S	Т	X	Υ	Z
	6	15	3	8	14.5	5	28	15	4.5	9	65.5	1.6	24	16.5	32	M3 x 0.5	16	9.5	M6 x 1.0	51.5	3	5	7	91.5
Ī	10	15	4	8	8	5	28	15	4.5	9	60	1.6	24	16.5	32	M4 x 0.7	12.5	9.5	M8 x 1.0	46	_	5	7	86
	16	15	5	8	8	5	28	23	5.5	14	65	2.3	33	25	42	M5 x 0.8	12.5	9.5	M10 x 1.0	47	_	6	9	90




Rod flange (F)

ø6



ø10, ø16



Head cover port location Axial location (R)

* The overall cylinder length does not change.

☆ For details of the mounting nut, refer to the Web Catalog.


A 1 of dotailo c	,	moun	9	ut, 1	0.0.		,	· outo	g.															[mm]
Bore size	Α	В	С	D	F	FB	FC	FT	FX	FY	FZ	GA	GB	Н	MM	NA	NB	NC	NN	S	SA	Т	Z	ZA
6	15	12	14	3	8	13	4.5	1.6	24	14	32	14.5	5	28	M3 x 0.5	16	9.5	7	M6 x 1.0	51.5	49	3	79.5	77
10	15	12	14	4	8	13	4.5	1.6	24	14	32	8	5	28	M4 x 0.7	12.5	9.5	_	M8 x 1.0	46	_	_	74	_
16	15	18.3	20	5	8	19	5.5	2.3	33	20	42	8	5	28	M5 x 0.8	12.5	9.5	_	M10 x 1.0	47	_	_	75	_






Head flange (G)

ø6



ø10, ø16




☆ For details of the mounting nut, refer to the Web Catalog.

	A I OI GOIGIIO C	, uio i	- Touriti	ng na	, 10101	10 1110		Guiai	- J													[mm]
Ī	Bore size	Α	В	С	D	F	FB	FC	FT	FX	FY	FZ	GA	GB	Н	MM	NA	NB	NN	S	Т	Z
	6	15	12	14	3	8	13	4.5	1.6	24	14	32	14.5	5	28	M3 x 0.5	16	9.5	M6 x 1.0	51.5	3	87.5
Ī	10	15	12	14	4	8	13	4.5	1.6	24	14	32	8	5	28	M4 x 0.7	12.5	9.5	M8 x 1.0	46	_	82
	16	15	18.3	20	5	8	19	5.5	2.3	33	20	42	8	5	28	M5 x 0.8	12.5	9.5	M10 x 1.0	47	_	83

Double clevis (D)

ø10, ø16



 $\ast\,$ A clevis pin and retaining rings are included.

[mm]


Bore size	Α	В	С	CD (cd)	СХ	CZ	D	GA	GB	Н	MM	NA	NB	R	S	U	Z	ZZ
10	15	12	14	3.3	3.2	12	4	8	18	28	M4 x 0.7	12.5	22.5	5	46	8	82	87
16	15	18.3	20	5	6.5	18.3	5	8	23	28	M5 x 0.8	12.5	27.5	8	47	10	85	93






Double-side bossed (E)

ø6



ø10, ø16



																[mm]
Bore size	Α	В	С	D	F	GA	GB	Н	MM	NA	NB	NDh8	NN	S	Т	Z
6	15	12	14	3	8	14.5	5	28	M3 x 0.5	16	9.5	6_0.018	M6 x 1.0	51.5	3	87.5
10	15	12	14	4	8	8	5	28	M4 x 0.7	12.5	9.5	8_0_0	M8 x 1.0	46	_	82
16	15	18.3	20	5	8	8	5	28	M5 x 0.8	12.5	9.5	10_0.022	M10 x 1.0	47	_	83



High Durability Series CJ2-XB24

Specific Product Precautions

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products," the "Operation Manual," and air cylinder CJ2 series specific product precautions on the SMC website: https://www.smcworld.com

Handling

. Marning

1. Use within the specified cylinder speed and kinetic energy ranges.

Otherwise, cylinder and seal damage may occur.

2. Do not apply excessive lateral load to the piston rod.

Easy checking method

Min. operating pressure after the cylinder is mounted to the equipment (MPa) = Min. operating pressure of cylinder (MPa) + $\{Load\ mass\ (kg)\ x\ Friction\ coefficient\ of\ guide/Sectional\ area$ of cylinder (mm²) $\}$


If smooth operation is confirmed within the above value, the load on the cylinder is the resistance of the thrust only and it can be judged as having no lateral load.

3. Do not apply any torque to the cover joint.

Both the rod cover and head cover have wrench flats. When mounting the product, be sure to tighten with an appropriate amount of force.

When mounting the cylinder or installing a fitting to the port, perform tightening while holding the cover on the same side as the component being installed with a wrench.

Do not hold the cover on the opposite side. Failure to follow this instruction may cause the cover and tube joint to be broken by torque.





⚠ Caution

1. Tighten retaining screws to an appropriate tightening torque within the range given below.

ø6: 2.1 to 2.5 N·m, ø10: 5.9 to 6.4 N·m ø16: 10.8 to 11.8 N·m

- 2. To remove and install retaining rings for knuckle pins or clevis pins, use an appropriate pair of pliers (tool for installing a type C retaining ring). In particular, use a pair of ultramini pliers for removing and installing retaining rings on the Ø10 cylinder.
- 3. For the auto switch rail mounting type, do not remove the rail that is mounted.
 - Because retaining screws extend into the cylinder, this could lead to an air leak.
- 4. Please contact SMC when the stroke exceeds 100 mm for the axial foot mounting type.

Durability of The Cylinder

The durability of a longer life cylinder has been evaluated by comparison with the existing cylinders under SMC's test conditions.

The durability of a cylinder depends on the customer's operating conditions and operating environment.

Therefore, durability of four times or longer will not be guaranteed under all conditions.



⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

Caution: Caution indicates a hazard with a low level of risk which, If not avoided, could result in minor or moderate injury.

★ Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

Danger indicates a hazard with a high level of risk which, ⚠ Danger: Danger indicates a nazaru wiun a nigin level on the first avoided, will result in death or serious injury.

*1) ISO 4414: Pneumatic fluid power - General rules relating to systems.

ISO 4413: Hydraulic fluid power – General rules relating to systems.

IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

⚠Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.

- 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
- 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
- 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
 - 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
 - 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

⚠ Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.

If anything is unclear, contact your nearest sales branch.

Limited warranty and Disclaimer/ **Compliance Requirements**

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2) Also, the product may have specified durability, running distance or
 - replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
 - 2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered.

Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

⚠ Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

SMC Corporation

Akihabara UDX 15F.

4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362

https://www.smcworld.com

© 2023 SMC Corporation All Rights Reserved