Flat Head Screwdriver AdjustableMetal Speed ControllerNewwith One-touch Fitting

Improved environmental resistance with the all metal exterior

For use in environment with Welding spatter (Option BD type)

Flow adjustable by a **flat head screwdriver** Prevents accidental manual operation

Adjustment needle lock nut feature as standard

Prevents unauthorized adjustment and unwanted operation of the needle from the set position due to vibrations or impacts. Helps improve safety in your machinery.



More compact (For G thread, face seal) Height reduced by 14% 36.8 mm < 42.8 mm 6.0 mm shorter

ASB22□1-G02-□ AS2201F-G02-□W2D

Variations


One-touch	Port	size	Applicable tubing O.D.					
fitting type	FUIL	SIZE	Metric size	Inch size				
	M5 :	k 0.8	4, 6	—				
	10-32	2UNF	—	5/32", 1/4"				
	_	1/8	6, 8	1/4", 5/16"				
	R G	1/4	6, 8, 10	1/4", 5/16", 3/8"				
	NPT	3/8	8, 10	5/16", 3/8"				
		1/2	10, 12	3/8", 1/2"				

* Metric size: R, G only, Inch size: NPT only

ASB- D Series



Made of flexible silicone rubber which conforms to the tube





Flat Head Screwdriver Adjustable Metal Speed Controller with One-touch Fitting **ASB-D D Series** RoHS

Model


One-touch fitting type

<u></u>													
				Applicable tubing O.D.									
Model*2	Port size		Port size Seal method		c size (A	pplicable	e thread:	R, G)	Inch size (Applicable thread: NP				NPT)
				4	6	8	10	12	5/32"	1/4"	5/16"	3/8"	1/2"
ASB12□1-M5-□	M5 :	x 0.8	Gasket seal										
ASB12□1-U10/32-□	10-32	2UNF	Gasket seal							•			
ASB22□1-□01-□	_	1/8											
ASB22□1-□02-□		1/4	Sealant (R/NPT)*1							•			
ASB32□1-□03-□	NPT	3/8	Face seal (G)										
ASB42□1-□04-□		1/2						•					•

*1 "Without sealant" type can be selected as a standard option.

*2 Meter-out and meter-in types can be visually differentiated by the flow direction symbol on the body.

Flow Direction Symbols on Body



Specifications

Fluid	Air
Proof pressure	1.5 MPa
Max. operating pressure	1 MPa
Min. operating pressure	0.1 MPa
Ambient and fluid temperatures	-5 to 60°C (No freezing)
Applicable tubing material*1, *2	FEP, PFA, Nylon, Soft nylon, Polyurethane, Polyolefin

*1 Check the max. operating pressure of the tubing. (Please refer to the Web Catalog for details.)
 *2 Tubing with inner layer of these materials is applicable.

SMC tubing: TRBU (FR double layer), TRTU (FR three-layer), TRS (FR soft nylon), etc.


Flow Rate and Sonic Conductance

		ASB12□1-M5-□	ASB12□1-U10/32-□	ASB2201-001-0	ASB22□1-□02-□	ASB32	1-□03-□	ASB4201-04-0
Model		ø4, ø6	ø5/32". ø1/4"	ø6, ø1/4", ø8,	ø6, ø1/4", ø8,	ø8,	ø10,	ø10, ø3/8", ø12,
		04, 00	05/32,01/4	ø5/16"	ø5/16", ø10, ø3/8"	ø5/16"	ø3/8"	ø1/2"
C values: Sonic conductance	Free flow	0.3	0.3	0.7	1.4	2.7	2.9	4.8
dm ³ /(s·bar)	Controlled flow	0.3	0.3	0.7	1.8	2.8	3.0	4.9
b values: Critical	Free flow	0.2	0.2	0.25	0.3	0.:	25	0.25
pressure ratio	Controlled flow	0.4	0.4	0.2	0.3	0	.2	0.3

* C and b values are for controlled flow with the needle fully open and free flow with the needle fully closed.

▲ Caution


Be sure to read this before handling the products.
Refer to the back cover for safety instructions. For flow I control equipment precautions, refer to the "Handling I Precautions for SMC Products" and the "Operation I Manual" on the SMC website: https://www.smcworld.com




ASB- D Series

Needle Valve: Flow Rate Characteristics


ASB12□1-M5-□




ASB22□1-01-□




ASB2201-02-0










* The flow rate characteristics are representative values.


* The numbers above the flow rate characteristic curves in the charts show the applicable tubing outside diameter as defined by the product number.

Flat Head Screwdriver Adjustable Metal Speed Controller with One-touch Fitting **ASB- D Series**


Construction

ASB-D _{Series} Seal method: Gasket seal For M5, 10-32UNF





Seal method: Face seal For G thread




Component Parts


Comp	onent Parts	5	
No.	Description	Material	Note
1	Body A	Zinc alloy	
2	Body B	Brass	Electroless nickel plating
3	Needle	Brass	Electroless nickel plating
4	O-ring	FKM	
5	Lock nut	Brass	Electroless nickel plating
6	C-ring	Stainless steel	
7	Seat ring	Brass	Electroless nickel plating
8	O-ring	NBR	
9	U-seal	HNBR	
10	O-ring	NBR	
11	Seal	FKM	
12	Cover	Stainless steel	
13	Cassette	Stainless steel	
14	Gasket	Stainless steel/NBR	M5, U10/32 type
15	Seal	NBR	G thread type

ASB-D Series


Construction

ASB-BD _{Series} Seal method: Gasket seal For M5, 10-32UNF





Seal method: Face seal For G thread



Component Parts


	Description	Material	Mata
4		material	Note
1 E	Body A	Zinc alloy	
2 E	Body B	Brass	
3 N	leedle	Brass	
4 L	.ock nut	Aluminum alloy	Trivalent chromated
5 C	C-ring	Stainless steel	
6 S	Seat ring	Brass	Electroless nickel plating
7 C	D-ring	NBR	
8 U	J-seal	HNBR	
9 C	D-ring	NBR	
10 S	Seal	FKM	
11 C	Cover	Stainless steel	
12 C	Cassette	Stainless steel	
13 G	Gasket	Stainless steel/NBR	M5, U10/32 type
14 S	Seal	NBR	G thread type

SMC


ASB- D Series For M5, 10-32UNF, R, NPT Thread

Dimensions

Seal method: Gasket seal For M5, 10-32UNF



Applicable tubing O.D. ød




Metric Size


Metric Size												[mm]
Model	d	т	Hı	H2	D1	Α	14	L2	L3	L4	м	Weight
Woder		п	ПZ		Max.	L1			Max.	IVI	[g]	
ASB12□1-M5-04D	4	M5 x 0.8	0	7	10.4	24.8	17.1	22.8	15.4	27.7	12.6	14
ASB12□1-M5-06D	6	IVIS X 0.0	VIS X U.0 9	1	13.1	13.1 24.8	20.8	26.5	14.2	27.7	13.6	17

Inch Size

Model	Ь	т	Hı	H2	D1	Α	L1	L2	L3	L4	м	Weight
inio do.	-	-				Max.				Max.		[g]
ASB12□1-U10/32-03D	5/32	10/32	0	7	10.4	04.0	17.1	22.8	15.4	07.7	12.6	14
ASB12□1-U10/32-07D	1/4	UNF	9	/	13.1	24.8	20.8	26.5	14.2	27.7	13.5	17

Seal method: Sealant For R, NPT thread







[mm]

[mm]

Metric Size

												[]
Model	d	т	H1	H2	D1	A Max.	L1	L2	Lз	L4 Max.	м	Weight [g]
ASB22 1-01-06D	6	B1/8	13	9	13.1	29.1	22.5	29.6	18.3	32.2	13.6	25
ASB22 1-01-08D	8	n1/0	13	9	15.1	29.1	25.4	32.5	10.5	32.2	16.1	28
ASB22 1-02-06D	6				13.1		24.7	34			13.6	44
ASB22 1-02-08D	8	R1/4	17	12	15.1	32.5	28.4	37.7	23.2	38	16.1	46
ASB22 1-02-10D	10				18		30.8	40.1]		17.0	51
ASB32□1-03-08D	8	R3/8	22	14	15.1	38.4	30	41.9	26.9	43.6	16.1	76
ASB32□1-03-10D	10	n3/0	22	14	18	30.4	32.1	44	20.9	43.0	17.0	82
ASB42 1-04-10D	10	R1/2	27	17	18	45.1	34.4	48.8	33.5	52.2	17.0	135
ASB42□1-04-12D	6	n1/2	27	17	21	45.1	36.3	50.7	33.5	52.2	18.6	145

Inch Size												[mm]
Model	d	т	H1	H2	D1	A Max.	L1	L2	L3	L4 Max.	м	Weight [g]
ASB22□1-N01-07D	1/4	NPT1/8	10.7	0	13.1	00.1	22.5	29.6	10.0	00.0	13.5	25
ASB22 1-N01-09D	5/16	INPII/8	12.7	9	15.1	29.1	25.4	32.5	18.3	32.2	16.1	28
ASB22 1-N02-07D	1/4				13.1		24.7	34.1			13.5	45
ASB22 1-N02-09D	5/16	NPT1/4	17.46	12	15.1	32.5	28.4	37.8	23.2	38	16.1	48
ASB22 1-N02-11D	3/8				18		30.8	40.2			16.6	53
ASB32□1-N03-09D	5/16	NPT3/8	22.23	14	15.1	38.4	30	41.9	26.9	43.6	16.1	78
ASB32□1-N03-11D	3/8	INF 13/0	22.23	14	18	30.4	32.1	44	20.9	43.0	16.6	84
ASB42□1-N04-11D	3/8	NPT1/2	27	17	18	45.1	34.4	48.8	33.5	52.2	16.6	138
ASB42□1-N04-13D	1/2		21	17	21	40.1	36.3	50.7	33.5	52.2	18.5	145




Flat Head Screwdriver Adjustable Metal Speed Controller with One-touch Fitting **ASB- D Series**

For G Thread

[mm]

Dimensions

Seal method: Face seal For G thread



Metric Size

												[]
Model	b	т	H1	H2	D1	Α	L1	L2	L3	L4	м	Weight
Model	ŭ	•	•••	112		Max.	L 1	62	L 3	Max.	IVI	[g]
ASB22□1-G01-06D	6	G1/8	13	9	13.1	26.7	22.5	29.6	18.3	32.2	13.6	26
ASB22□1-G01-08D	8	GI/6	13	9	15.1	20.7	25.4	32.5	10.3	52.2	16.1	28
ASB22 1-G02-06D	6				13.1		24.7	34			13.6	42
ASB22 1-G02-08D	8	G1/4	17	12	15.1	28.8	28.4	37.7	22	36.8	16.1	45
ASB22 1-G02-10D	10				18		30.8	40.1]		17.0	49
ASB32□1-G03-08D	8	G3/8	22	14	15.1	36.1	30	41.9	26.9	43.6	16.1	79
ASB32□1-G03-10D	10	G3/6	22	14	18	30.1	32.1	44	20.9	43.0	17.0	85
ASB42 1-G04-10D	10	G1/2	27	17	18	43.2	34.4	48.8	33.5	52.2	17.0	143
ASB42 1-G04-12D	12	G1/2	21	17	21	43.2	36.3	50.7	33.5	52.2	18.6	153


Related Equipment

Spatter Cover

Applicable tubing: FR soft nylon/TRS, FR double layer/TRB/TRBU, FR three-layer/TRTU



Model	Applicable tubing O.D.	L1	L2	ø D 1	ø D 2
KQB2-06C-X1124	6	24.6	16.6	13.5	11.6
KQB2-08C-X1124	8	30.2	20.6	16.4	14.2
KQB2-10C-X1124	10	34.4	24.6	19.3	16.2



Sales unit: 10 pcs./bag

Since the spatter cover is designed for multi-layer (double layer, three-layer) tubing, sufficient effects cannot be obtained in foreign matter flow-in or followability for single-layer tubing.

* The cover can be attached regardless of the single-layer/multi-layer tubing.



*





One-touch Fittings KQG2 Series





ASB- D Series Specific Product Precautions 1

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For flow control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

Design and Selection

A Warning

1. Confirm the specifications.

The products in this catalog are designed to be used in compressed air systems (including vacuum) only.

If the products are used in an environment where pressure or temperature is out of the specified range, damage and/or malfunction may result. Do not use under such conditions. (Refer to the specifications.)

Please contact SMC when using a fluid other than compressed air (including vacuum).

We do not guarantee against any damage if the product is used outside of the specification range.

2. Products mentioned in this catalog are not designed for use as stop valves with zero air leakage.

A certain amount of leakage is allowed in the product's specifications.

Tightening the needle to reduce leakage to zero may result in equipment damage.

3. Do not disassemble the product or make any modifications, including additional machining.

Doing so may cause human injury and/or an accident.

4. The flow rate characteristics for each product are representative values.

The flow rate characteristics are characteristics of each individual product. Actual values may differ depending on the piping, circuitry, pressure conditions, etc.

Also, depending on product specifications, there may be variations in the zero needle rotations position of the flow rate characteristics.

- Sonic conductance (C) and critical pressure ratio (b) values for products are representative values.
 For controlled flow direction values the needle is fully open. For free flow direction values the needle is fully closed.
- 6. Check if PTFE can be used in the application. PTFE powder (Polytetrafluoroethylene resin) is included in the seal material of the male thread type piping taper thread. Confirm that the use of it will not cause any adverse effects on the system.

Please contact SMC if the Safety Data Sheet (SDS) is required.

7. Speed controllers are designed to control the speed of the actuator.

Mounting

\land Warning

1. Operation manual

Install the product and operate it only after reading the operation manual carefully and understanding its contents.

Also, keep the manual where it can be referred to as necessary.


- 2. Ensure sufficient space for maintenance activities. When installing the products, allow access for maintenance and inspection.
- **3. Tighten threads with the proper tightening torque.** When installing the products, follow the listed torque specifications.
- 4. Use R external threads with Rc internal threads and NPT external threads with NPT internal threads.
- 5. Confirm that the lock nut is tightened. A loose lock nut may cause speed changes in the actuator.
- 6. Check the degree of rotation of the needle valve. The products in this catalog are retainer type so that the needle is not removed completely. Over rotation will cause damage.

7. Refer to the table below for the proper adjusting torque of the needle and recommended screwdrivers.

Connection thread size	Proper adjusting torque [N·m]	Recommended screwdriver*1
M5, 10-32UNF	0.05	Nominal thickness $\mathbf{a} = 0.4$ Nominal width $\mathbf{b} = 2.5$ ($\mathbf{t} = 0.7$)
1/8	0.17	Nominal thickness $\mathbf{a} = 0.5$ Nominal width $\mathbf{b} = 3$ ($\mathbf{t} = 0.9$)
1/4	0.23	Nominal thickness $\mathbf{a} = 0.6$ Nominal width $\mathbf{b} = 3.5$ $(\mathbf{t} = 1.1)$
3/8	0.25	Nominal thickness $\mathbf{a} = 1$ Nominal width $\mathbf{b} = 5.5$ ($\mathbf{t} = 1.8$)
1/2	0.40	Nominal thickness $\mathbf{a} = 1.2$ Nominal width $\mathbf{b} = 8$ ($\mathbf{t} = 2.2$)

*1 Tip shape of a usable screwdriver conforms to JIS B 4609-1998 Type B (see Annex, figure 3 and table 2).

Screwdriver tip shape







ASB-D Series Specific Product Precautions 2

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For flow control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

\land Warning

8. Confirm the air flow direction.

Mounting backward is dangerous because the speed adjustment needle will not work, and the actuator may lurch suddenly.

9. Adjust the needle by opening the needle slowly after having closed it completely.

Loose needle valves may cause unexpected sudden actuator extension.

When a needle valve is turned clockwise, it is closed and cylinder speed decreases. When a needle valve is turned counterclockwise, it is open and cylinder speed increases.

Flow Direction Symbols on Body



10. Do not apply excessive force or shock to the body or fittings with an impact tool.

It can cause damage or air leakage.

11. To install/remove the product, use an appropriate wrench to tighten/loosen at the supplied nut on body B.

Do not apply torque at other points, as the product may be damaged. Rotate body A manually for positioning after installation.


▲ Caution



Body B

1. When performing the piping work, turn the tightening tool in the horizontal direction to the hexagon across flats of body B so that any moment is not applied to the body.

If the tool is in contact with the body, this may cause the body to come off.



2. Body A can be slightly rotated for positioning, but it cannot be used as a rotating part.

This will cause metal debris by wearing, which may enter the operating fluid or cause fitting damage.

3. If the connection tube oscillates or turns, do not use this product.

Failure to do so may result in fitting breakage or detachment of the body.

Mounting

▲ Caution

For M5, 10-32UNF

Tightening method


First, tighten it by hand, then give it an additional 1/6 turn to 1/4 turn with a wrench. The reference value for the tightening torque is 1 to $1.5 \text{ N}\cdot\text{m}$.

* Excessive tightening may damage the thread portion or deform the gasket and cause air leakage.

If the screw is too shallowly screwed in, it may come loose or air may leak.

Chamfered area for female thread

1. In compliance with ISO 16030 Standards (air pressure fluid dynamics – connection – ports and stud ends), the chamfered thread sizes shown below are recommended.



For R, NPT Thread (With sealant)

Tightening method

1. The proper tightening torques of the fittings are as shown in the table below.


As a guide, tighten it by hand, then turn it two or three turns with a wrench.

Check the dimensions of each product for the hexagon width across flats.

Connection thread size	Proper tightening torque [N·m]
NPT, R1/8	3 to 5
NPT, R1/4	8 to 12
NPT, R3/8	15 to 20
NPT, R1/2	20 to 25

Chamfered area for female thread

By chamfering as shown in the following table, machining of threads is easier and effective for burr prevention.



Connection thread size	Chamfer dimension ø D (Recommended value)	
111000 3120	Rc	NPT, NPTF
1/8	10.2 to 10.4	10.5 to 10.7
1/4	13.6 to 13.8	14.1 to 14.3
3/8	17.1 to 17.3	17.4 to 17.6
1/2	21.4 to 21.6	21.7 to 21.9

 For Uni thread, Rz 12.5 is necessary for sealing at the chamfered part.



ASB-D Series Specific Product Precautions 3

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For flow control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

Mounting

For G Thread (Face seal)

Tightening method

First, tighten the threaded portion by hand, then use a proper wrench, which could be suitable for the width across flats of the hexagon body, to tighten it further at a wrench tightening angle shown in the table below. For a tightening torque guide, refer to the table below. Check the dimensions of each product for the hexagon width across flats.

1) The proper tightening torques of the fittings are as shown in the table below.

Connection thread size	Proper tightening torque [N·m]
G1/8	3 to 5
G1/4	8 to 12
G3/8	15 to 20
G1/2	20 to 25

- Insufficient tightening may loosen the threads, or cause air leakage.
- 3) Reuse
 - (1) Normally, fittings with a sealant can be reused up to 6 to 10 times.
 - (2) The seal ring cannot be replaced.

Chamfered area for female thread


(Recommended value)

1. Conforming to ISO 16030-2001, the chamfered dimensions shown in the table below are recommended. By chamfering as shown in the table below, machining of threads is easier and effective for burr prevention.

	Nominal	Chamfered dimension øD	
	thread size	Min.	Max.
	1/8	9.8	10.2
	1/4	13.3	13.7
	3/8	16.8	17.2
	1/2	21.0	21.4
Rz12.5			

2. Use G external threads with G internal threads.

How to distinguish between G, R, and NPT threads



The proper tightening torques for hexagon lock nuts are shown in the table below.

For standard installation, turn 15 to 30° using a tool, after fastening by hand. Pay attention not to over tighten the product. Check the dimensions for each product for the width across flats.

Body size	Proper tightening torque [N·m]	Lock nut width across flats
M5	0.17	7
1/8	0.3	9
1/4	1	12
3/8	1.5	14
1/2	2	17

Piping Threads with Sealant

▲ Caution

- 1. If the fitting is tightened with excessive torque, a large amount of sealant will seep out. Remove the excess sealant.
- 2. Insufficient tightening may loosen the threads or cause air leakage.

3. For reuse

- 1) Normally, fittings with a sealant can be reused up to 2 to 3 times.
- To prevent air leakage through the sealant, remove any loose sealant stuck to the fitting by blowing air over the threaded portion.
- 3) If the sealant no longer provides effective sealing, wind sealant tape over the sealant before reusing. Do not use any form other than the tape type of sealant.
- 4. Once the fitting has been tightened, backing it out to its original position often causes the sealant to become defective. Air leakage will occur.
- 5. Use R external threads with Rc internal threads and NPT external threads with NPT internal threads.

Piping

▲ Caution

1. Refer to the Fittings and Tubing Precautions in the **Web Catalog** for handling One-touch fittings.

2. Preparation before piping

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil, and other debris from inside the pipe.

3. Winding of sealant tape

When screwing piping or fittings into ports, ensure that chips from the pipe threads or sealing material do not enter the piping. Also, if sealant tape is used, leave 1 thread ridge exposed at the end of the threads.



▲ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "**Caution**," "**Warning**" or "**Danger**." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)^{*1}, and other safety regulations.

- Caution: indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
- Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

AWarning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
 - The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

- 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
- 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
- 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

- *1) ISO 4414: Pneumatic fluid power General rules relating to systems.
 - ISO 4413: Hydraulic fluid power General rules relating to systems. IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)
 - ISO 10218-1: Manipulating industrial robots Safety. etc.

 The product is provided for use in manufacturing industries. The product herein described is basically provided for peaceful use in manufacturing industries. If considering using the product in other industries, consult SMC beforehand

and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.

*2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

A Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

SMC Corporation

Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362 https://www.smcworld.com © 2021 SMC Corporation All Rights Reserved