Air Tank AT Series



⚠ Precautions

- Be sure to read this before handling I the products.
- I Refer to page 9 for safety instruc-I tions and pages 10 to 12 for air preparation equipment precautions.

Precautions

- 1. Use outside Japan is not allowed. The AT series air tank is in compliance with the requlations in Japan (Pressure Vessel Structure), but is not
- in compliance with related regulations outside Japan. 2. Do not lose the Class 2 Pressure Vessel Certificate. The AT series is in compliance with the regulations in Japan (Class 2 Pressure Vessel). The Class 2 Pres-
- sure Vessel Certificate will be sent in 2 to 4 weeks after the product is shipped. Please keep it in a safe place. In addition, be sure to conduct annual independent inspections and keep copies of the results for 3 years. 3. About the anchor bolts for securing the product
- The calculation results for post-installed anchors will change depending on the state of the installation surface, so be sure to conduct your own calculations taking the actual installation conditions into consideration.
- 4. The inner surface of the air tank is not coated. Install a filter on the outlet side if needed.

There is a stainless steel specification, an inner surface anti-corrosive treatment type, and other special order options available.

In addition, products with a change in coating, products with a change in the port size of each socket, products with a change in mounting position, and a horizontal type product are also available as special orders. Please contact SMC separately for details.

- 5. The air tank is an indoor specification. It cannot be used outdoors.
- 6. Use the pressure gauge within the 0 to 45°C range. The max. operating temperature of the pressure gauge that comes with the standard model is 45°C. If the temperature of the air tank exceeds 45°C, provide a heat radiator such as a pipe siphon, etc., between the air tank and the pressure gauge.

Model/Standard Specifications

Model		AT6C	AT11D	AT22D	AT37D	AT55D	AT75D	AT125D	AT150C (1)	AT220C(1)		
Fluid	Ė	Compressed air										
Tank	capacity (L)	100	200	400	500	700	1000	1500	2000	3000		
Max. o	perating pressure (MPa)	0.97										
Port	size	Rc 1/2	Rc 3/4	Rc	1 1/2	2B flange (2)		3B flange (2)	4B flange (2)			
Set pres	ssure for safety valve (MPa)					0.97						
Proof pre	ssure (Under water pressure) (MPa)	1.46										
Fluid	temperature (°C)	0 to 100 (For the type with auto drain: 0 to 60°C)										
Mate	erial	Steel plate (SS400) Steel plate (SS400, SM490)										
Weig	ght (kg)	55	115	180	205	275 395		505	775	965		
Coat	ting color	Surface: Munsell N-5.5, Inner surface: Non coated										
© S	Safety valve (1 pc.)	R 1/2	R 3/4	R 1	1/4	R 1	1/2		R 2			
sory	alve for drainage (1 pc.)	Rc 1/2										
	Pressure gauge (1 pc.)	R3/8 D2 shape										
A L	type anchor bolt (4 pcs.)	M	116 x L25	0	M	16 x L30	10	M16 x L500	M24 x	L500		

Note 1) Manufactured upon receipt of order Note 2) JISB2220 (JIS 10K FF flange)

Note 4) This product is for indoor use only and not to be used outdoors. Note 5) As this product is a Class 2 Pressure Vessel, conduct an annual Note 3) The accessories should be mounted by user. self inspection and safely store the inspection results for 3 years.

Option Note 1) (Accessory)

Replacement Part Note 2)

Model	Auto drain	Companion flange		Model	Pressure gauge	Gasket for cleaning hole	Gasket for manhole	
AT6C		_		AT6C		_		
AT11D		_		AT11D				
AT22D		_		AT22D				
AT37D	AD402-04	_		AT37D		411419	!	
AT55D		2 ^B JIS 10K FF flange		AT55D	AT-SA001	411419		
AT75D				AT75D				
AT125D		3 ^B JIS 10K FF flange		AT125D				
AT150C		4 ^B JIS 10K FF flange		AT150C			412013	
AT220C		4º JIS TUK FF flange		AT220C		_	412013	

Note 1) The accessories should be mounted by user. (Order with the part number.) Note 2) Parts other than the replacement parts cannot be shipped individually.

How to Order

rank	capacity •——				
Symbol	Applicable compressor	Capacity			
Syllibol	(kW)	(L)			
6C	5.5	100			
11D	11	200			
22D	22	400			
37D	37	500			
55D	55	700			
75D	75	1000			
125D	125	1500			
150C	150	2000			
2200	220	2000			

22D

Option (Accessory)

Symbol	Description
Nil	_
D	With auto drain
F	Companion flange
DF	With auto drain, companion flange

Note) For F and DF, only AT55D to AT220C can be selected.

Port size

Symbol	Size	Applicable model					
04	Rc 1/2	AT6C					
06	Rc 3/4	AT11D					
14	Rc 1 1/2	AT22D, 37D					
20	2 ^B JIS 10K FF flange	AT55D, 75D					
30	3 ^B JIS 10K FF flange	AT125D					
40	4 ^B JIS 10K FF flange	AT150C, 220C					

Related Product

Refer to page 1288 for details.

This is a small capacity air tank to which a booster valve can be connected directly in a compact manner. It is not compatible with the Class 2 Pressure Vessel requirement. The air tank can be used as a single unit.

Model	VBAT05A	VBAT10A	VBAT20A	VBAT38A		
Tank capacity (L)	5	10	20	38		






When used as a single unit and pressurized at over 1 MPa at normal temperatures (the booster valve is not connected), the air tank falls under the scope of the "High Pressure Gas Safety Act" in Japan.




AT Series


Dimensions




ORIENTATION (Nozzle direction) AT6C to 220C




AT55D to 125D





AT150C/220C



Andrioi	(mm)													
Model	Air connection		øΑ	В	øС	≈D	Е	_	G	≈H	øJ	к		Anchor bolt
	Socket	Flange	DA.	- P	, oc	-≈0	_	"	G	211	90	_ ^	-	Alichol bolt
AT6C	Rc 1/2	_	408.4	361	440	1268	1000	550	6	528	19	Rc 1/2	80	M16 x L250
AT11D	Rc 3/4	_	611	510	650	1266	945	645	9	751	19	Rc 3/4	110	M16 x L250
AT22D	Rc 11/2	_	611	510	650	1986	1340	740	9	812	19	Rc 11/4	110	M16 x L250
AT37D	Rc 11/2	_	611	510	650	2286	1340	740	9	812	19	Rc 11/4	110	M16 x L300
AT55D	_	2 ^B JIS 10K FF flange	964	824	1080	1557	1100	750	12	1215	19	Rc 11/2	180	M16 x L300
AT75D	_	2 ^B JIS 10K FF flange	964	824	1080	2167	1550	750	12	1215	19	Rc 11/2	180	M16 x L300
AT125D	_	3 ^B JIS 10K FF flange	964	824	1080	2777	1650	750	12	1240	19	Rc 2	180	M16 x L500
AT150C	_	4 ^B JIS 10K FF flange	1218	1019	1300	2558	1700	850	16	1495	27	Rc 2	260	M24 x L500
AT220C	_	4 ^B JIS 10K FF flange	1218	1019	1300	3288	1700	850	16	1495	27	Bc 2	260	M24 x I 500