# **Grippers for Collaborative Robots**

Compliant with the Dual-Arm SCARA Robot [duAro 1, 2] Kawasaki Heavy Industries, Ltd.



Vacuum Gripper ZXP7□-X1□-KA



Air Gripper JMHZ2-X7500-KA





# **Grippers for Collaborative Robots**

# Kawasaki Heavy Industries, Ltd.

Dual-Arm SCARA Robot [duAro 1, 2] compliant A K-AddOn registered product

# For Adsorption

# Vacuum Gripper **■** *ZXP7*□-*X1*□-*KA*

- A compact, lightweight all-in-one vacuum gripper
- Integrated vacuum ejector, pressure switch, and cups
- A wide variety of cup variations are available to support a wide range of workpieces.
- Standards: Conforming to ISO9409-1-31.5-4-M5

Max. work load [kg]	7
Max. vacuum pressure [kPa]	-84
Suction flow rate [L/min (ANR)]	17
Weight [g]	427*1

<sup>\*1</sup> Without cup mounting flange







# **For Gripping**

# Air Gripper D JMHZ2-X7500-KA

- Compact, lightweight product with high gripping force due to air operation
- With high-precision linear guide: Repeatability: ±0.01 mm
- Integrated speed adjustment mechanism
- Selectable attachment, protective cover, and auto switch
- Standards: Conforming to ISO9409-1-31.5-4-M5

Gripping force	External	32.7
Effective value per finger [N]	Internal	43.5
Opening/Closing stroke (Both sides) [mm]		10
Weight [g]		280





# CONTENTS

# **Grippers for Collaborative Robots**

Kawasaki Heavy Industries, Ltd.

Dual-Arm SCARA Robot [duAro 1, 2] compliant

A K-AddOn registered product





# Vacuum Gripper for Collaborative Robots


Kawasaki Heavy Industries, Ltd. Dual-Arm SCARA Robot

# [duAro 1, 2] compliant

# A compact, lightweight all-in-one vacuum gripper

- Integrated vacuum ejector, pressure switch, and cups
- A wide variety of cup variations are available to support a wide range of workpieces.
- Standards: Conforming to ISO9409-1-31.5-4-M5





## ■ Specifications

	Standards	Conforming to ISO9409-1-31.5-4-M5		
Common	Applicable fluid	Air		
	Operating temperature range [°C]	5 to 50		
	Weight [g]*4	659 (427)		
	Max. work load [kg]*5	7		
	Air pressure supply (P) port	One-touch fitting (ø4)		
	Max. vacuum pressure [kPa]*6	-84		
.,	Suction flow rate [L/min (ANR)]*6	17		
Vacuum ejector	Air consumption [L/min (ANR)]*6	57		
ojootoi	Supply pressure range [MPa]	0.3 to 0.55		
	Standard supply pressure [MPa]*7	0.5		
	Rated pressure range [kPa]	0 to -101		
Pressure switch	Power supply voltage [V]	12 to 24 VDC ±10%, Ripple (p-p) 10% or less		
	Display accuracy	±2% F.S. ±1 digit (Ambient temperature of 25 ±3°C)		
	Repeatability	±0.2% F.S. ±1 digit		
	Temperature characteristics	±2% F.S. (25°C conversion)		

■Included parts: Robot mounting flange, Parallel pin, Mounting bolt, Cups with adapter\*1, Plug\*2, Binding band\*3

- \*1 Included only with cups
- \*2 Included only for the ZXP7A
- \*3 When release pressure is to be supplied, it is used to bind and secure the switch cable and the ø4 tube to be connected to the release pressure supply (PD) port.
- \*4 The weight in brackets refers to the weight of the product without a cup mounting flange. Add the weight of the suction cups with adapter for the weight with cups. (Refer to the "Suction Cup Part Numbers and Weight" on page 6.)
- \*5 May be restricted depending on the cup diameter, mounting orientation, or workpiece. Please use within the max. work load. Suction and transfer exceeding the max. work load may result in reduced vacuum pressure due to air leakage.
- Values are at the standard supply pressure and based on SMC's measurement standards. They depend on atmospheric pressure (weather, altitude, etc.) and the measurement method.
- \*7 This value indicates the pressure right before the air pressure supply (P) port when vacuum is generated. The pressure right before the P port of the vacuum gripper when vacuum is generated may fall below 0.5 MPa due to the air supply capacity, piping size, and the amount of air being consumed by other devices being operated simultaneously.



# **Cup Variations**

The number of cups can be changed. (Refer to the operation manual for details on changing the quantity.)







1 cup

2 cups

4 cups

# The cup type can be changed. (For details on selectable cups, refer to "How to Order.")











Flat (ø8), Silicone rubber

Bellows (ø20), NBR

Thin flat (ø16), NBR

Flat (ø32), Silicone rubber Flat (ø32), Urethane rubber







ø25, 5.5-stage, Silicone rubber




ø25, 5.5-stage, Silicone rubber With vacuum saving valve



Vacuum saving valve ZP2V Series (To be ordered separately) Applicable part no.: ZP2V-B6-05

\* The silicone material is compliant with the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.

## ■The cup pitch can be changed.



\*1 Operating range: 25 to 35 (When a cup is mounted in the center) As interference between cups may occur depending on the cup diameter, select the cup diameter according to the pitch to be used.




\*1 Refer to the table below for the applicable cups. For models with cups, 4 cups with adapters are included in the package.

-KA







For Kawasaki Heavy Industries, Ltd.

16

### Dual-Arm SCARA Robot duAro 1 and 2 compatible

## Cup series

Cup series				
Symbol	Cup series			
ZP	Basic			
ZP3P	Bellows type for film			
ZP3P	packaging workpieces			
Nil	Without cup			

Cup diameter					
Symbol	Cup diameter	Symbol	Cup diameter		
08	ø8	25	ø25		
10	ø10	B25	ø25		
13	ø13	B30	ø30		

32

Nil

ø32

Without cup

# Body size

Symbol	Size
7	75 mm

# Cup mounting flange shape

Symbol	Flange shape	
Α	With flange	
A	(42 mm x 42 mm)	
N	Without flange*2	



2 Customers selecting the product without a cup mounting flange will be required to produce a flange that matches the mounting dimensions on their own.

# Cup form

Symbol	Cup form		
U	Flat		
С	Flat with rib		
В	Bellows		
UT	Thin flat		
J	Multistage bellows		
JT2	2.5-stage bellows		
JT5	5.5-stage bellows		
Nil	Without cup		

## 6 Cup material

With flange Without flange

Symbol	Material			
N	NBR			
S	Silicone rubber (White)*3			
U	Urethane rubber			
F	FKM			
SF	Silicone rubber (Blue)*3			
Nil	Without cup			

\*3 The silicone material is compliant with the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.

### Attachment\*4

Attachment		
With (guide)		
attachment		
With mesh		
attachment		

\*4 Only applicable to the cup form "JT ..." Note that "M" applies only to cup form:

## 8 Pressure switch output specifications/Unit

ø16

Symbol	Output/Unit			
Nil	NPN/With unit switching function*5			
Α	NPN/SI unit only*6			
В	NPN/With unit switching			
Ь	function (Initial value psi)*5			
С	PNP/With unit switching function*5			
D	PNP/SI unit only*6			
E	PNP/With unit switching			
_ E	function (Initial value psi)*5			

- \*5 Under the New Measurement Act, switches with the unit switching function are not permitted for use in Japan.
- \*6 Fixed unit: kPa, MPa

# ■ Suction Cup Part Numbers and Weight

Part No. <b>ZXP7(A,N)</b> -						-X1□-KA
	3	4	5	6	7	

#### Applicable cups

#### **Cup part numbers**

* Ref	fer to the	Web Catalo	<b>g</b> for de	tails on	suction	cups.


Applicable cups					oup part numbers			the web Catalog for details on suction cups.						
3	4	5	6	7	Cup w	ith ada	oter	A dontor unit						
						Weight	by cup i	material	(g/cup)	Adapter unit / Vacuum inlet: \ Cup unit				
Cup	Cup	Cup	Cup	Attachment	Part no.	N	S/SF	U	F	Male thread M6 x 1	Cup unit			
series	diameter	form	material			(NBR)	(Silicone)	(Urethane)	(FKM)	(Male lifead Mo X 1)				
ZP	80	U			ZPT08U□-A6	4	4	4	4		ZP08U□			
ZP	08	В			ZPT08B□-A6	4	4	4	4		ZP08B□			
ZP	10	UT			ZPT10UT□-A6	4	4	4	4	ZPT1-A6	ZP10UT□			
ZP	13	UT			ZPT13UT□-A6	4	4	4	4		ZP13UT□			
ZP	16	UT			ZPT16UT□-A6	4	4	4	4		ZP16UT□			
ZP	10	U			ZPT10U□-AS6	7	7	7	7		ZP10U□			
ZP	13	U			ZPT13U□-AS6	7	7	7	8	ZPT2-AS6	ZP13U□			
ZP	16	U			ZPT16U□-AS6	7	7	7	8		ZP16U□			
ZP	20	U			ZPT20U□-AS6	9	10	10	10		ZP20U□			
ZP	25	U			ZPT25U□-AS6	10	10	10	11	ZPT3-AS6	ZP25U□			
ZP	32	U			ZPT32U□-AS6	10	11	11	12		ZP32U□			
ZP	10	С		-	ZPT10C□-AS6	7	7	7	7		ZP10C□			
ZP	13	С			ZPT13C□-AS6	7	7	7	7	ZPT2-AS6	ZP13C□			
ZP	16	С		-	ZPT16C□-AS6	7	7	7	8		ZP16C□			
ZP	20	C			ZPT20C□-AS6	9	10	10	11		ZP20C□			
ZP	25	С		_	ZPT25C□-AS6	10	10	10	11	ZPT3-AS6	ZP25C□			
ZP	32	С			ZPT32C□-AS6	10	11	11	12		ZP32C□			
ZP	10	В			ZPT10B□-AS6	7	7	7	8		ZP10B□			
ZP	13	В		-	ZPT13B□-AS6	7	8	8	8	ZPT2-AS6	ZP13B□			
ZP	16	В			ZPT16B□-AS6	8	8	8	9		ZP16B□			
ZP	20	В		-	ZPT20B□-AS6	11	11	11	13		ZP20B□			
ZP	25	В			ZPT25B□-AS6	11	12	12	14	ZPT3-AS6	ZP25B□			
ZP	32	B			ZPT32B□-AS6	14	15	15	18		ZP32B□			
ZP	20	UT			ZPG20UT□-7A-X2	4	4	4	4	ZPT1-A6	ZP2-20UT			
ZP	16	J_			ZPG16J□-7A-X2	8	8	8	9	ZPT2-AS6	ZP2-16J□			
ZP	B25	J		-	ZPGB25J□-7A-X2	14	15	15	18	ZPT3-AS6	ZP2-B25J			
ZP	B30	J			ZPGB30J□-7A-X2	18	19	19	25		ZP2-B30J□			
ZP3P	20	JT2	SF		ZP3PG20JT2SF-7A-X2	_	21		_	ZP3PA-T1JT-7A-X2	ZP3P-20JT2SF-W			
ZP3P	20	JT2	SF	M	ZP3PG20JT2SF-M-7A-X2		21	<u> </u>	_	- '	ZP3P-20JT2SF-WM			
ZP3P	32	JT2	SF	8.4	ZP3PG32JT2SF-7A-X2		48		_	ZP3PA-T2JT-7A-X2	ZP3P-32JT2SF-W			
ZP3P	32	JT2	SF	M	ZP3PG32JT2SF-M-7A-X2		48	_	_		ZP3P-32JT2SF-WM			
ZP3P	20	JT5	SF		ZP3PG20JT5SF-7A-X2		23		_	ZP3PA-T1JT-7A-X2	ZP3P-20JT5SF-WG			
ZP3P	25	JT5	SF		ZP3PG25JT5SF-7A-X2		25	_	_		ZP3P-25JT5SF-WG			
ZP3P	32	JT5	SF		ZP3PG32JT5SF-7A-X2		54		_	ZP3PA-T2JT-7A-X2	ZP3P-32JT5SF-WG			

Input the material symbol ("N," "S," "U," or "F") into the  $\square$  in the part number.




### **Model Selection**

## Exhaust Characteristics\*1




\*1 The exhaust characteristics are different when the vacuum-saving valve (ZP2V-B6-05) is mounted. For details, refer to "8.3 Suction cup precautions" in the operation manual.

### **Flow Rate Characteristics**







## Dimensions




Circuit diagram Silencer exhaust EXH. Digital pressure switch ZSE20-□-□-M5-LA2

pressure supply (PD) port





### Without cup mounting flange



\*2 Operating range: 25 to 35 (When a cup is mounted in the center)

As interference between cups may occur depending on the cup diameter, select the cup diameter according to the pitch to be used.

# **ZXP7**□-X1□-KA Specific Product Precautions

Be sure to read this before handling the products. For safety instructions and vacuum equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

#### Handling

# **∧** Caution

- Strictly observe the precautions on vacuum equipment and safety when using the product. Additionally, select a cup size and material suitable to both the workpiece to be adsorbed and the atmosphere. Take safety measures so that any accident, such as the dropping of a workpiece, does not occur during adsorption transfer. For details, refer to the Web Catalog.
- Use the product within the specification range. Use exceeding the compressed air pressure or voltage may result in serious damage due to reduced product performance.
- 3. Exhaust air is released from the opening in the product. Therefore, this exhaust air opening must not be blocked or restricted.

#### Mounting

# **⚠** Caution

- 1. For details on the mounting method, refer to the Operation Manual.
- Tighten to the specified tightening torque. If the tightening torque is exceeded, the body and the mounting screws may break. However, insufficient torque may cause displacement of the body and loosening of the mounting screws.
- 3. Do not drop, strike, or apply excessive impact to this product.
  - Doing so may result in damage to the internal parts of the body or pressure switch. In some cases, this damage may result in a malfunction.
- 4. Hold the body when handling the product. Do not pull excessively on the switch cable or pinch the cable when lifting the body. Failure to do so may result in damage to the pressure sensor. In some cases, this damage may result in a failure or malfunction.
- The bolts may loosen due to the operating conditions and environment. Be sure to conduct maintenance such as tightening the bolts periodically.

#### Wiring

# **∧** Caution

- 1. Avoid repeatedly bending or stretching the switch cable as well as applying force to it.
- Do not wire while energizing the product. Doing so may result in damage to the internal parts of the pressure switch. In some cases, this damage may result in a malfunction.
- Do not disassemble the switch cable or make any modifications, including additional machining. Doing so may cause human injury and/or an accident.

## **Piping**

# **A** Caution

#### 1. Flushing of the inside of the pipes

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil, and other debris from inside the pipe.

#### 2. Tube attachment

- · Take a tube having no flaws on its periphery and cut it off at a right angle. When cutting the tube, use tube cutters TK-1, 2, 3, 5, or 6. Do not use pliers, nippers, scissors, etc. If cutting is done with tools other than tube cutters, the tube may be cut diagonally or become flattened, etc., making a secure installation impossible, and causing problems such as the tube pulling out after installation or air leakage. Allow some extra length in the tube.
- · Grasp the tube and push it in slowly, inserting it securely all the way into the fitting.
- After inserting the tube, pull on it lightly to confirm that it will not come out. If it is not installed securely all the way into the fitting, this can cause problems such as air leakage or the tube pulling out.

#### 3. Tube detachment

- · Push in the release button sufficiently, pushing its collar equally around the circumference.
- · Pull out the tube while holding down the release button so that it does not come out. If the release button is not pressed down sufficiently, there will be increased bite on the tube and it will become more difficult to pull it out.
- When the removed tube is to be used again, cut off the portion which has been chewed before reusing it. If the chewed portion of the tube is used as is, this can cause trouble such as air leakage or difficulty in removing the tube.

#### 4. Other Tube Brands

When using other than SMC brand tube, confirm that the following specifications are satisfied with respect to the tube outside diameter tolerance.

 $\begin{array}{ll} \cdot \mbox{ Nylon tube} & \mbox{ within } \pm 0.1 \mbox{ mm} \\ \cdot \mbox{ Soft nylon tube} & \mbox{ within } \pm 0.1 \mbox{ mm} \end{array}$ 

· Polyurethane tube within +0.15 mm, within -0.2 mm

Do not use tube which do not meet these outside diameter tolerances. It may not be possible to connect them, or they may cause other trouble, such as air leakage or the tube pulling out after connection.

## 5. Piping

- Do not apply unnecessary forces, such as twisting, pulling, moment loads, vibration, impact, etc., on fittings or tubing.
   This will cause damage to fittings and will crush, burst, or release tubing.
- Do not lift the product by the piping after the tube is connected.
   Doing so may result in damage to the One-touch fitting.
   For details, refer to the "Handling Precautions for SMC Products" on the SMC website: https://www.smcworld.com



# Air Gripper for Collaborative Robots

Kawasaki Heavy Industries, Ltd. Dual-Arm SCARA Robot


# [duAro 1, 2] compliant

- Compact, lightweight product with high gripping force due to air operation
- An air gripper that realizes high rigidity and high precision due to its guide-integrated construction

With high-precision linear guide

Repeatability:  $\pm 0.01$  mm

- Integrated speed adjustment mechanism
- A split protective cover for easy air gripper maintenance
  Allows you to maintain the air gripper without removing the user-specific attachment
- Selectable attachment, protective cover, and number of auto switches
- Standards: Conforming to ISO9409-1-31.5-4-M5





# **Specifications**

Bore size [mm]	16
Fluid	Air
Operating pressure [MPa]	0.1 to 0.7
Ambient and fluid temperatures [°C]	-10 to 60
Repeatability [mm]	±0.01
Max. operating frequency [c.p.m]	120

Lubrication	Non-lube				
Action	Double acting				
Gripping force	External	32.7			
Effective value per finger [N]	Internal	43.5			
Opening/Closing stroke (Both	10				
Weight [g]	280*1				


<sup>\*1</sup> Includes 2 attachments (30 g) and 2 protective covers (20 g)

# **How to Order**



D-M9NW

D-M9PW



Number of fingers

Bore size 16 16 mm

Action Double acting

4 Auto switch Symbol Specifications Model Without auto switch Nil (Built-in magnet) М9В D-M9B Solid state auto M9N D-M9N switch М9Р D-M9P M9BW D-M9BW 2-color indicator

solid state auto

switch

M9NW

0

\*1 Auto switches marked with a "O" are produced upon receipt of order.

 $\bigcirc$ 

Number of auto switches

Nil	2
S	1
N	n

Options "S" and "N" are shipped with the product. 6 Attachment

Nil	Without attachment						
Α	With attachment						

Applicable Auto Switches/Refer to the Web Catalog and the Best Pneumatics Catalog for further information on auto switches.

12 V

Protective cover

M9BW

Nil	Without protective cover						
С	With protective cover						

M9PW

Type Special function	Electrical entry								Load voltage			Auto switch model	Lead v	vire ler	gth [m	1]*1							
			Indicator light					Wiring (Output)		DC	AC	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applicab	le load				
0				3-wire (NPN)		5 V, 12 V		M9N	•			0	0	IC circuit									
tch — — — — — — — — — — — — — — — — — — —	_	-	Grommet									3-wire (PNP)		5 V, 12 V		М9Р	•	•		0	0	IC Circuit	
	Crommat			\/	2-wire	04.1/	12 V		M9B	•	•		0	0	_	Relay,							
switch	Diagnostic	Grommet		Grommet	Grommet	et Yes	3-wire (NPN)	24 V	5 \/ 40 \/	_	M9NW	•	•		0	0	10 -:	PLC					
indication			3-wire (PNP)		5 V, 12 V		M9PW	•			0	0	IC circuit										

(2-color indicator) \* Lead wire length symbols:

Sol

0.5 m ...... 1 m ..... (Example) M9NW (Example) M9NWM ... М (Example) M9NWL 3 m ..... 5 m ..... (Example) M9NWZ

\* When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper.

2-wire

Product mounting bolts are included in the package.




# **Characteristics**


## **Gripping force**

#### • Indication of effective gripping force


The gripping force shown in the graphs below represents the gripping force of one finger when all fingers and attachments are in contact with the workpiece. F = One finger thrust


#### **External gripping force**





### Internal gripping force







## **Gripping point**


- The air gripper should be operated so that the workpiece gripping point "L" and the amount of overhang "H" stay within the range shown for each operating pressure given in the graphs below.
- If the workpiece gripping point goes beyond the range limits, this will have an adverse effect on the life of the air gripper.


## **External grip**








## Internal grip


















# JMHZ2-X7500-KA Specific Product Precautions

Be sure to read this before handling the products. For safety instructions, air gripper precautions, air gripper specific product precautions, and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

#### Handling

# **∧** Caution

- Martensitic stainless steel is used for the finger guide. However, the anti-corrosiveness of this steel is inferior to that of austenitic stainless steel. In particular, rust may be generated in environments where waterdrops are likely to adhere to the product due to condensation, etc.
- 2. Finite orbit type guide is used in the actuator finger part. By using this, when there are inertial force which cause by movements or rotation to the actuator, steel ball will move to one side and this will cause a large resistance and degrade the accuracy. When there are inertial force which cause by movements or rotation to the actuator, operate the finger to full stroke.
- 3. When mounting or removing the attachment, use the following tightening torque: 0.59 N. The weight of the attachment is generally about 70 g per side of a finger.

#### Mounting

# **A** Caution

- 1. For details on the mounting method, refer to the Operation Manual.
- Tighten to the specified tightening torque. If the tightening torque is exceeded, the body and the mounting screws may break. However, insufficient torque may cause displacement of the body and loosening of the mounting screws.
- 3. Do not drop, strike, or apply excessive impact to this product. Doing so may result in damage to the internal parts of the body or auto switch. In some cases, this damage may result in a malfunction.
- 4. Hold the body when handling the product. Do not pull excessively on the auto switch cable or pinch the cable when lifting the body. Failure to do so may result in damage to the auto switch. In some cases, this damage may result in a failure or malfunction.
- 5. The bolts may loosen due to the operating conditions and environment. Be sure to conduct maintenance such as tightening the bolts periodically.

#### Wiring

# **∧** Caution

- 1. Avoid repeatedly bending or stretching the auto switch cable as well as applying force to it.
- Do not wire while energizing the product. Doing so may result in damage to the internal parts of the auto switch. In some cases, this damage may result in a malfunction.
- Do not disassemble the product or make any modifications, including additional machining. Doing so may cause human injury and/or an accident.

## **Piping**

# **⚠** Caution

### 1. Flushing of the inside of the pipes

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil, and other debris from inside the pipe.

#### 2. Tube attachment

- · Take a tube having no flaws on its periphery and cut it off at a right angle. When cutting the tube, use tube cutters TK-1, 2, 3, 5, or 6. Do not use pliers, nippers, scissors, etc. If cutting is done with tools other than tube cutters, the tube may be cut diagonally or become flattened, etc., making a secure installation impossible, and causing problems such as the tube pulling out after installation or air leakage. Allow some extra length in the tube.
- · Grasp the tube and push it in slowly, inserting it securely all the way into the fitting.
- After inserting the tube, pull on it lightly to confirm that it will not come out. If it is not installed securely all the way into the fitting, this can cause problems such as air leakage or the tube pulling out.

#### 3. Tube detachment

- · Push in the release button sufficiently, pushing its collar equally around the circumference.
- Pull out the tube while holding down the release button so that it does not come out. If the release button is not pressed down sufficiently, there will be increased bite on the tube and it will become more difficult to pull it out.
- · When the removed tube is to be used again, cut off the portion which has been chewed before reusing it. If the chewed portion of the tube is used as is, this can cause trouble such as air leakage or difficulty in removing the tube.

#### 4. Other Tube Brands

When using other than SMC brand tube, confirm that the following specifications are satisfied with respect to the tube outside diameter tolerance.

 $\begin{array}{ll} \cdot \mbox{ Nylon tube} & \mbox{ within $\pm 0.1$ mm} \\ \cdot \mbox{ Soft nylon tube} & \mbox{ within $\pm 0.1$ mm} \end{array}$ 

· Polyurethane tube within +0.15 mm, within -0.2 mm

Do not use tube which do not meet these outside diameter tolerances. It may not be possible to connect them, or they may cause other trouble, such as air leakage or the tube pulling out after connection.

#### 5. Piping

- Do not apply unnecessary forces, such as twisting, pulling, moment loads, vibration, impact, etc., on fittings or tubing.
   This will cause damage to fittings and will crush, burst, or release tubing.
- Do not lift the product by the piping after the tube is connected.
   Doing so may result in damage to the One-touch fitting.
   For details, refer to the "Handling Precautions for SMC Products" on the SMC website: https://www.smcworld.com



# **⚠** Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)\*1), and other safety regulations.

Caution: Caution indicates a hazard with a low level of risk which, If not avoided, could result in minor or moderate injury.

-----

Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

⚠ Danger: Danger indicates a nazaru wiun a nigin level on the first avoided, will result in death or serious injury. **Danger** indicates a hazard with a high level of risk which, \*1) ISO 4414: Pneumatic fluid power - General rules relating to systems.

ISO 4413: Hydraulic fluid power – General rules relating to systems.

IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

# **⚠Warning**

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.

- 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
- 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
- 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

- 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
- 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
- 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

## **⚠** Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.

If anything is unclear, contact your nearest sales branch.

## Limited warranty and Disclaimer/ **Compliance Requirements**

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

### **Limited warranty and Disclaimer**

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.\*2) Also, the product may have specified durability, running distance or
  - replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
  - 2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered.

Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

#### Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

## **⚠** Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.