Differential Pressure Gauge GD40-2-01 Series RoHS

The pressure differential at the inlet and the outlet of compressed air equipment can be viewed at a glance on the differential pressure gauge. It is ideal for the maintenance control of filters.

Can be installed easily by merely providing a bypass circuit. Provided with a protective cover to prevent hazards.



Model/Specifications

Model	GD40-2-01
Fluid	Compressed air
Max. operating pressure	1 MPa
Proof pressure	1.5 MPa
Ambient and fluid temperature	5 to 60°C
Port size	Hight pressure : R1/8 Low pressure : Rc1/8
Scale range	0 to 0.2 MPa
Accuracy	±3% F.S. (Full span)
Weight (g)	300

Accessory

Main Parts Material

		//////////////////////////////////////
Case	Zinc alloy	Nylon tube
Internal part	Brass, Phosphor bronze	Male connector
Window	Resin	Male elbow
Scale plate	Stainless steel	

Stanless steel

▲ Specific Product Precautions

Be sure to read this before handling the products.
 Refer to page 9 for safety instructions and pages 10 to 12 for air

Refer to page 9 for safety instructions and pages 10 to 12 for air preparation equipment precautions.

Design

▲ Caution

L

Symbol

1. Install the product where a pulsation is not likely to be generated.

Mounting

A Caution

1. Mounting

1) The HIGH and LOW marks on the back of the differential pressure gauge indicate the high pressure and low pressure sides respectively. Connect the HIGH side to the inlet side of the filter or other devices and the LOW side to their outlet side. Do not use a stop valve to prevent damage to the differential pressure gauge if the valve is inadvertently left closed.
2) Install the differential pressure gauge vertically.

3) The piping of the differential pressure gauge

T0425 B (0.5 m) H04-01 (1 pc.)

DL04-01 (1 pc.)

Piping Example









