Water Resistant Cylinder (Pneumatic/Hydraulic)

Pneumatic: CM2/CG1/MB/MB1/CQ2/CA2/MGP/MGG/MK/RSQ Series Hydraulic: CHDKB/CH2F Series

Compatible with an operating environment with coolants.



Anti-coolant performance has been improved compared to the standard cylinders. Applicable for an operating

environment where water splashes.




Water Resistant Air Cylinders (Pneumatic/Hydraulic)

Suitable for using under the atmosphere having coolant in the machine tools.

Also, compatible with environments where water is splashed on the food machinery, or car washing machines, etc

Special scraper

 Dramatically improved water resistance compared to standard cylinders



Mounting brackets, accessories, and nut material: Stainless steel

The following accessories need to be prepared separately. (Please order separately.) Refer to the "Accessories" page of each series for details.

Series	Bore size (mm)	Foot	Flange	Single knuckle joint	Double knuckle joint	Mounting nut	Rod end nut	Accessories page
CM2	20, 25, 32, 40	0	0	0	0	0	0	p. 254
CG1	20, 25, 32, 40, 50, 63, 80, 100	0*	0*	0	0	-	0	p. 396
	20, 25, 32, 40, 50, 63, 80, 100		_	0	0	-	0	p. 899

Applicable Cylinder

* Except bore size 20 and 25.



6 SMC

Model	Applicable cylinder	Lead wire
D-F7BA(V)L/ Rail mounting	CQ2 (ø20 to ø100) MK (ø16 to ø63) RSQ (ø32 to ø50)	Oilproof vinyl cabtire cord: ø3.4 0.2 mm ² , 2 cores (Brown, Blue), 3 m (standard)
D-F5BAL/Tie-rod mounting	MB (ø32 to ø100) CA2 (ø40 to ø100) CH2F (ø32 to ø100)	Oilproof vinyl cabtire cord: ø4, 0.3 mm² 2 cores (Brown, Blue), 3 m (standard)
D-H7BAL/ Band mounting	CM2 (Ø20 to Ø40) CG1 (Ø32 to Ø63) MGG (Ø32 to Ø63)	Oilproof vinyl cabtire cord: ø3.4 0.2 mm², 2 cores (Brown, Blue), 3 m (standard)
D-G5BAL/ Band mounting	CG1(ø80, ø100) MGG(ø80, ø100)	Oilproof vinyl cabtire cord: ø4, 0.3 mm ² 2 cores (Brown, Blue), 3 m (standard)
D-Y7BAL/ Direct mounting Note 1)	MB (ø32 to ø100) MB1 (ø32 to ø100) CA2 (ø40 to ø100) CHKDB (ø32 to ø100)	Oilproof vinyl cabtire cord: ø3.4 0.15mm ² , 2 cores (Brown, Blue), 3 m (standard)
D-M9□A(V)L/Direct mounting Note 1)	$\begin{array}{l} CM2 \ (o20 \ to \ o40) \\ CG1 \ (o32 \ to \ o100) \\ MB \ (o32 \ to \ o100) \\ MB1 \ (o32 \ to \ o100) \\ CA2 \ (o40 \ to \ o100) \\ CQ2 \ (o20 \ to \ o100) \\ MGP \ (o20 \ to \ o100) \\ MK \ (o16 \ to \ o50) \\ RSQ \ (o32 \ to \ o50) \\ CHKDB \ (o20 \ to \ o100) \\ \end{array}$	Oilproof vinyl cabtire cord: 2.7 x 3.2 Elliptical shape, 0.15 mm², 2 cores (D-M9BA(V 3 cores (D-M9NA(V),D-M9PA(V))

Water resistant 2-color indicator solid state auto switch

Note 1) Tie-rod mounting for CA2 and MB Note 2) This product is not made to be used in water.

Refer to pages 1271 to 1365 for the detailed specifications of auto switches.




Hydraulic Cylinders







How to Order



specifications

/ Caution


Rod seals and scrapers are not replaceable. The above parts cannot be replaced since the scraper is press-fit in the rod cover.

Specifications

Action	Double acting, Single rod		
Bore size (mm)	20, 25, 32, 40		
Cushion	Rubber bumper, Air cushion		
Auto switch mounting	Band mounting		
Made to Order	Made of stainless steel (-XC6)		

* Specifications other than above are the same as standard, basic type.

Dimensions



٦H	
<u>н</u>	
ZZ	+ Stroke

				(mm)
Bore size (mm)	E1	NN1	Н	ZZ
20	22_0.033	M22 x 1.5	24	99
25	*26_0.033	*M26 x 1.5	24	99
32	*26_0.033	*M26 x 1.5	24	101
40	*32_0.039	*M32 x 2	26	130

* Other specifications are the same as the double acting, single rod standard type. (An asterisk means it is the same as the standard type.)

Mounting Bracket*: Part No.

Mounting bracket	Min. order qty.	Bore size (mm) 20	Description (At min. order qty.)
Axial foot type**	2	CM-L020C	2 foots, 1 mounting nut
Flange	1	CM-F020C	1 flange
Trunnion (with nuts)	1	CM-T020C	1 trunnion, 1 trunnion nut


* The brackets for ø25 to ø40 are the same for the standard type.

** Order 2 foot brackets for each cylinder unit.





How to Order




Specifications


Action	Double acting, Single rod
Bore size (mm)	32, 40, 50, 63, 80, 100
Cushion	Rubber bumper, Air cushion
Auto switch mounting	Band mounting
Made to Order	Made of stainless steel (-XC6)

* Specifications other than above are the same as standard, basic type.

Dimensions








WA


(mm)

Bore size (mm)	(E1)	E*	(F1)	F*	GA	S	TA	WA	ZZ
32	17	18	2	2	18	77 (85)	17	22	119 (127)
40	21	25	2	2	19	84 (93)	18	23	136 (145)
50	26	30	2	2	21	97 (109)	20	25	157 (169)
63	26	32	2	2	21	97 (109)	20	25	157 (169)
80	32	40	3	3	28	116 (130)	_	32	190 (204)
100	37	50	3	3	29	117 (131)	_	33	191 (205)

* Other specifications are the same as the double acting, single rod standard type. (An asterisk means it is the same as the standard type.)

* (): For the long stroke type






Water resistant 2-color indicator solid state auto switch

> Made to Order specifications



How to Order




Specifications

Action	Double acting, Single rod		
Bore size (mm)	ø32, 40, 50, 63, 80, 100		
Cushion	Air cushion, Rubber bumper		
Auto switch mounting	Tie rod mounting		
Made to Order	Made of stainless steel (-XC68)		

* Specifications other than above are the same as standard, basic type.

Dimensions



		(mm)
Bore size (mm)	Н	ZZ
32	47	135 (141)
40	58	146 (152)
50	67	165 (173)
63	67	165 (173)
80	81	199 (209)
100	81	199 (209)

* Other specifications are the same as the double acting, single rod standard type.


* (): For the type without a rubber bumper

Specifications

Action	Double acting, Single rod				
Bore size (mm)	ø32, 40, 50, 63, 80, 100				
Cushion	Air cushion, Rubber bumper				
Auto switch mounting	Direct mounting				
Made to Order	Made of stainless steel (Piston rod is hard chrome plated) (-XC68)				

* Specifications other than above are the same as standard, basic type.


Dimensions




		(mm)
Bore size (mm)	H	ZZ
32	47	135 (141)
40	58	146 (152)
50	67	165 (173)
63	67	165 (173)
80	81	199 (209)
100	81	199 (209)

* Other specifications are the same as the double acting, single rod standard type.

* (): For the type without a rubber bumper





V FKM seals (Fluororubber)

Water resistant 2-color ● indicator solid state auto switch

> Made to Order specifications

> > Suffix

 Nil
 Retaining ring, piston rod, rod end nut material: Stainless steel

 A
 Piston rod, rod end nut, cover holding bolt material: Stainless steel

 Note) -XC6A: ø20 to ø32 only

Specifications


Action	Double acting, Single rod						
Bore size (mm)	20, 25, 32, 40, 50, 63, 80, 100						
Mounting	Ø20 to Ø32 ······B (through-hole) only Ø40 to Ø100 ·····B (through-hole), F (rod side flange) A (both ends tapped), G (head side flange) L (foot), D (double clevis)						
Cushion	None						
Minimum operating pressure	0.08 MPa						
Auto switch mounting	Rail mounting (D-F7BAL/F7BAVL)/Direct mounting (D-M9□A(V)L) Use auto switch brackets for rail mounting.						
Made to Order	Retaining ring, piston rod, rod end nut material: Stainless steel (-XC6						

* Specifications other than above are the same as standard, basic type.

Refer to page 972 for details.



How to Order




Specifications

Action	Double acting, Single rod
Bore size (mm)	40, 50, 63, 80, 100
Cushion	Air cushion
Auto switch mounting	Tie-rod mounting type
Made to Order	Made of stainless steel (Piston rod is hard chrome plated) (-XC68)

* Specifications other than above are the same as standard, basic type. Note 1) Air-hydro type, rod boot specifications are excluded. Note 2) Combination of auto switches and steel tube is not available.

Dimensions

* Other specifications are the same as the double acting, single rod standard type.




* Piston rod and guide rod are made of stainless steel.

Specifications

Applicable series		MGPM							
Bearing type		Slide bearing							
Bore size	(mm)	20, 25, 32, 40, 50, 63, 80, 100							
Cushion	MGPM□□R	Rubber bumper							
Cusilion	MGPM□□V	Without cushion							
Auto swit	ch mounting	Direct mounting							
Minimum operating pressure		0.13 MPa							
Made to Order -XC6A		Specified parts made of stainless steel							

* Specifications other than above are the same as standard, basic type. Note) Refer to the Web Catalog for details.

Dimensions



					(
Dana sina		Α				
Bore size (mm)	50 st or less	Over 50 st 200 st or less	Over 200 st	В	DA	
20	66	90.5	66	(10)		
25	67.5	7.5 91.5 123.5		67.5	(10)	
32	87	87 105.5		71.5	(14)	
40	87	105.5 141.5		78	(14)	
50	99.5	120.5 161.5		83	20	
63	99.5	120.5	161.5	88	20	
80	110.5	137.5	186.5	102.5	25	
100	130.5	155.5	194.5	120	30	


Bore size		E		XC6A		
(mm)	50 st or less	Over 50 st 200 st or less	Over 200 st	FB	FB	
20	(0)	(24.5)	(57)	21	20	
25	25 (0)		(56)	(56) 21		
32	(15.5)	(34)	(70)	24	22	
40	(9)	(27.5)	(63.5)	24	22	
50	(16.5)	(37.5)	(78.5)	27	23	
63	(11.5)	(32.5)	(73.5)	27	23	
80	(8)	(35)	(84)	30	27	
100	(10.5)	(35.5)	(74.5)	35	32	

* The dimensions in () are the same as standard type.

* The FB dimensions change for the XC6A.



How to Order



* A scraper is installed on piston rod parts only.

Specifications

Action		Double acting						
Bore size (mm)		32, 40, 50, 63, 80, 100						
Bearing type		Slide bearing						
Cushion		Built-in rubber bumper and shock absorber						
Auto switch mounting		Band mounting						
	-XC6	Made of stainless steel (Piston rod, rod end nut)						
Made to Order	-XC6A	Stainless steel used on all iron parts						
Made to Order	-XC6B	Stainless steel rod end moving parts						
	-XC6C	Stainless steel rods						

* Specifications other than above are the same as standard, basic type. Refer to the Web Catalog for details.

Front mounting flange

Note) RBL (anti-coolant) type is used for shock absorbers.

Dimensions (Dimensions other than the below are the same as the standard type.)

ø32 to ø50

(mm)

Q
X Y + Stroke

ø63 to ø100

-

Ø100	Front mounting flange

- II •	
X Y + Stroke	


			(mm)
Bore size (mm)	Q	X	Y
32	16	48	77 (85)
40	17	58	84 (93)
50	19	69	97 (109)
63	34	56	112 (124)
80	46	68	137 (151)
100	47	68	138 (152)

* (): For the long stroke type.



ø16 to ø63

How to Order



Dimensions


Specifications

Bore size (mm)	16	20	25	32	40	50	63	
Action	Double acting							
Cushion	Rubber bumper							
Minimum operating pressure	ng pressure 0.15 MPa (0)	
Auto switch mounting	Direct mounting							


Specifications other than above are the same as standard, basic type.

Excludes bore sizes ø16 to ø25 of the rod flange type


* The dimensions in () are the same as standard type.




ø20. ø25



ø32 to ø63



I	Bore	Ded		Clamp stroke												
	size	Rod state	10 mm		20 mm		30 mm		50 mm			J	ĸ	L	AB	ØAC
	(mm) state	Q	R	Q	R	Q	R	Q	R							
ĺ	32	Retracted	118.5	81.5	138.5	91.5	158.5		198.5	121.5	9	7	M6 x 1.0	10	1	5.5
I	32	Extended	143.5	01.5	173.5	91.0	203.5		263.5							5.5
ĺ	40	Retracted	119	75	139	85	159	95	199	115	9	7	M6 x 1.0	10	1	5.5
	40	Extended	144		174	00	204		264							
ĺ	50	Retracted	137	00 F	157	00.5	5 177 226 10	1106 5	217	126.5	11	8	M8 x 1.25	4.4		6.6
l	50	Extended	166	86.5	196	96.5			286	120.5		0	NIO X 1.20	14	1	0.0
Ì	63	Retracted	140	90	160	100	180	110	220	130	14	10.5	M10 x 1.5	10		9
l	03	Extended	169	90	199	100	229	110	289	130	14	10.5	INITU X 1.5	118	1.4	9




Specifications

Action	Double acting
Bore size (mm)	ø32, ø40, ø50
Cushion	Rubber bumper
Rod end configuration	Round bar
Auto switch mounting	Direct mounting

* Specifications other than the above are the same as the standard type.


Dimensions



				(mm)
Bore size	A	н	V	VA
32	80	32	24	8
40	89.5	37	29	0
50	91	37	29	0

* Other specifications are the same as the double acting.

Hydraulic Cylinders



V FKM seals (Fluororubber)


Piston seal is made of NBR for both R and V.

Specifications

Action	Double acting, Single rod		
Bore size (mm)	20, 25, 32, 40, 50, 63, 80, 100		
Cushion	None		
Auto switch mounting	Direct mounting		

* Specifications other than above are the same as standard, basic type.

Dimensions



					(mm
Bore size (mm)	A	в	с	N	s
20	61	43	18	26.5	6
25	63	45	18	30	6
32	71	51	20	38	7
40	75	55	20	45	7
50	81	60	21	55	7
63	90	67	23	66	7
80	105	78	27	86	7
100	132	96	36	104	7

steel piston rods are available

as made to order.

* Other specifications are the same as the double acting, single rod standard type.




Rod end male thread

		(mm)
Bore size (mm)	g	h
20	33	76
25	36	81
32	45	96
40	50	105
50	56	116
63	68	135
80	87	165
100	111	207

* Other specifications are the same as the double acting, single rod standard type.

Piston seal is made of NBR for both



	(mm)
Bore size	B type rod
(mm)	А
32	_
40	—
50	_
63	—
80	13.5
100	14.5

* Other specifications are the same as the double acting, single rod standard type.

Action

R and V.

Specifications

Bore size (mm)	32, 40, 50, 63, 80, 100		
Cushion	Cushion seal type		
Auto switch mounting	Tie-rod mounting		
* Specifications other than above are the same as standard, basic type.			

Water resistant 2-color

* Stainless steel piston rods are available as made to order

Double acting, Single rod

indicator solid state auto switch

Dimensions





Water Resistant Air Cylinder/Water Resistant Hydraulic Cylinder Specific Product Precautions

Be sure to read this before handling the products. Refer to page 20 for safety instructions and pages 21 to 30 for actuator and auto switch precautions.

Handling Precautions

- Before installing a cylinder, thoroughly flush out the piping to prevent dust or cutting chips from entering the cylinder. For the hydraulic cylinder, use the air bleed valve to bleed the air inside the cylinder.
- Eccentric loads applied to the piston rod dramatically shorten the service life. Use the piston rod by always applying a load in an axial direction.
- 3.Make sure not to scratch or gouge the sliding portion of the piston rod, as this could damage the seals and lead to leaks. Attach a cover or other protection in locations where the cylinder is exposed to grinding sludge or machining chips.
- 4. When the cylinder is used in a place where the liquid from the piston rod is lightly splashed, and exposed to dust or sand, use a heavy duty scraper (-XC4).
- 5.If there is a possibility that liquid splashes on cylinder fittings when using an air cylinder, use insert fittings, self-align fittings, piping, etc. Consider the compatibility of liquid components and piping materials before using.
- 6. When selecting seals, generally use NBR (nitrile rubber) seals with liquids that do not contain chlorine and sulfur, and use FKM (fluororubber) seals with liquids that contain chlorine and sulfur. However, depending on the type and the brand of liquid that splashes on the cylinder, the operating life of seals may be reduced dramatically (such as coolant liquid). In cases where special additives are used, or where liquid caused trouble with the current nitrile or fluororubber seals in the past, request an investigation or set up a test period for the use of the seals.

Examples of coolants

Shimiron, PA-O-5	(Daido Chemical Industry Co., Ltd.)	(NBR seals)
Noritake Cool, AFG-S	(Noritake Co., Ltd.)	(NBR seals)
Yushiroken, S-46S	(Yushiro Chemical Industry Co., Ltd.)	(NBR seals)
Yushiroken, EC-50-T3	(Yushiro Chemical Industry Co., Ltd.)	(NBR seals)
Yushiron Oil, No. 23	(Yushiro Chemical Industry Co., Ltd.)	(FKM seals)
Daphne Cut, Hs-1	(Idemitsu Kosan Co., Ltd.)	(FKM seals)

Please consult with SMC separately when liquid contains sulfur, which is used for cylinders with a guide (MGP, MGG).