Refrigerated Air Dryer

IDFA Series

For Use in Europe, Asia and Oceania

(€ 2%

Applicable for the high-temperature environments

Ambient temperature: Max. 45°C Inlet air temperature: Max. 65°C

Air flow capacity * IDFA90-23, Dew point of 3°C

810 m³/h

(23% increase compared to the existing model)





Refrigerated Air Dryer IDFA Series

Applicable for the hightemperature environments



Increased air flow capacity





Series Variations

Model	Rated inlet	Rated ambient	Air fl	ow capacity [m³/h]	Port size
Wodel	condition	temperature	Dew point 3°C	Dew point 7°C	Dew point 10°C	POIT SIZE
IDFA60			204 300 312 408	360	R1	
IDFA70	35°C	25°C		408	480	R1 1/2
IDFA80	0.7 MPa	25 0	552	654	720	R2
IDFA90			810	900	960	n2

Options

· Cool compressed air output

· Anti-corrosive treatment for copper tube

· With Chinese labels and a Chinese operation manual

· With a heavy-duty auto drain

· With an earth leakage breaker

With a terminal block for operating, error, and remote operation signals
 With a timer controlled solenoid valve type auto drain

Optional accessories

p. 151

· Foundation bolt set


- Piping adapter
- Bypass piping set



Auto Drain Valve Longer life, Higher resistance to foreign matter

Non-sliding part reduces the catching of foreign matter

Diaphragm type -



Shape prevents condensate accumulation

Condensate and foreign matter are discharged completely.

Easier maintenance


• One-touch mounting and removal of the bowl is possible without using any tools.

Release the lock by sliding the lock button down while holding the body. Then, rotate the bowl guard and pull down for removal.

Transparent bowl guard

- Allows you to visually check the condensate condition in the bowl
- Improved environmental durability due to 2-layer construction

Drain tube holder (Accessory)







Protect Pneumatic Equipment from Moisture!

An air dryer removes the vapor from the moist compressed air delivered by the compressor and prevents it from causing the pneumatic equipment to fail.


Effects of moisture on equipment

- Malfunctioning of valves and actuators caused by dripping grease
- Generation of water droplets
- Decomposition of auto drain caused by rusting inside pipes



@ SIVIC

AIR DRYER



IDFA Series Model Selection

Air dryers should be selected based on the corrected air flow capacity while taking operating environment and facility into account. Select the air dryer model in accordance with the following procedure.

1 Read the correction factors.

Read the correction factors A to C suitable to the operating conditions.

IDFA Selection Example								
Cond	ition	Data symbol	Correction factor*1					
Inlet air temperature	40°C	(A)	0.71					
Ambient temperature	30°C	B	0.85					
Inlet air pressure	0.6 MPa	©	0.89					
Air flow rate	250 m³/h (ANR)	_	_					
Outlet air pressure dew point	3°C	_	_					

2 Calculate the corrected air flow capacity.

Obtain the corrected air flow capacity from the following formula.

Corrected air flow capacity from the following formula:

Corrected air flow capacity = Air flow rate ÷ (Correction factor (A) x (B) x (C))

Corrected air flow capacity

= 250 m3/h (ANR) ÷ (0.71 x 0.85 x 0.89)

*1 Values obtained from the table below

= 465 m3/h (ANR)

3 Select the model.

Select the model with air flow capacity exceeding the calculated corrected air flow from data ① of the table below.

The model which exceeds the correct air flow capacity of $465 \, m^3/h$ (ANR) is IDFA80.

Data A: Inlet Air Temperature

°C	5 to 25	30	35	40	45	50	55	60	65
Correction factor	1.42	1.15	1.00	0.71	0.62	0.50	0.40	0.33	0.21

Data B: Ambient Temperature

°C	2 to 25	30	35	40	45
Correction factor	1.00	0.85	0.80	0.73	0.62

Data ©: Inlet Air Pressure

MPa	0.3	0.4	0.5	0.6	0.7 to 1.6
Correction factor	0.71	0.75	0.82	0.89	1.00

Data D: Air Flow Capacity

			A : (1	it 3/In (ANID)				
Mod	Model		Air flow capacity m³/h (ANR)					
IVIOC	161	IDFA60	IDFA70	IDFA80	IDFA90			
Outlet	3°C	204	312	552	810			
air pressure	7°C	300	408	654	900			
dew point	10°C	360	480	720	960			

^{*} The outlet air pressure dew point varies depending on the operating conditions. Particularly when the outlet air pressure dew point is 3°C or 7°C, though this depends on the operating conditions, freeze protection functions may be activated, resulting in the dew point rising and becoming unstable.

If a stable low dew point is required, consider an IDG series membrane air dryer.

- * Refer to pages 152 and 153 for options.
- * Refer to page 151 for optional accessories.




Refrigerated Air Dryer

IDFA60/70/80/90 Series

(Max. inlet air temperature: 65°C, Max. ambient temperature: 45°C)


How to Order



- * When multiple options are combined, indicate symbols in alphabetical order.
- The combination of L and V is not available.

Replacement Parts

Auto drain



Auto Drain Replacement Part Nos.

Description	Part no.	Qty.
Element	AD402P-040S	1
Bowl O-ring	KA00463	1
Bowl assembly*1	AD52-A	1


*1 A bowl O-ring is included.

A One-touch fitting for connecting the drain tube is not included.





Dustproof filter



Dustproof Filter Replacement Part Nos.

ſ	Part no.	Qty.	Dimension [mm]	Applicable model		
	IDF-S0530	1	H370 x W440	For IDFA60		
	IDF-S0531	1	H614 x W440	For IDFA70		
	IDF-S0535	1	H614 x W556	For IDFA80, IDFA90		

Standard Specifications

Spe	cification	ıs		Model	IDFA60	IDFA70	IDFA80	IDFA90	
50	Fluid				Compressed air				
ati 🧸	Inlet ai	r tempe	rature	[°C]	5 to 65				
Operating range *1	Inlet ai	r pressu	ire	[MPa]		0.15 to	1.0* ⁹		
0 -	Ambie	nt tempe	rature (Humidity) [°C]	2 to 45	(Relative hu	midity: 85%	or less)	
			Outlet air pressure dew point	3°C	204	312	552	810	
		condition (ANR)*2	Outlet air pressure dew point	7°C	300	408	654	900	
S **	Air flow	(ANN) -	Outlet air pressure dew point	10°C	360	480	720	960	
Rated conditions*4	inta	Compressor intake condition*3	Outlet air pressure dew point	3°C	216	331	585	859	
conc			Outlet air pressure dew point	7°C	318	432	693	954	
ated		conducti	Outlet air pressure dew point	10°C	382	509	763	1018	
Œ	Inlet air pressure [MPa]					0	.7		
	Inlet ai	r tempe	rature	[°C]	35				
	Ambie	Ambient temperature [°C]			25				
	Power	Power supply voltage (Frequency)			Single-phase 230 VAC (50 Hz) Allowable voltage range ±10%*5				
Max	cimum a					city calculated			
Electric spec.	Power	consum		[W]	820	1300	1950	2220	
			mption*6	[A]	4.9	7.2	12.0	13.0	
			e breaker capacity	¹⁷ [A]	10	15	20	30	
	oling me						efrigeration		
	rigerant					410A (HFC)			
Ref	rigerant	charge		[g]	390 ±10	530 ±10	630 ±10	780 ±10	
	o drain					en, Min. ope			
	t size				R1	R1 1/2	-	12	
	ght			[kg]	49	68	95	110	
Acc	essorie	s			Drain tube (ø1	2: 3.5 m), Drain	tube holder, Op	eration manual	
*1 T	he opera	ting rand	e does not quara	antee use	with normal	air flow cap	acity.		

- Symbol
- Refrigerated i air drver Auto drain

- The operating range does not guarantee use with normal air flow capacity.
- *2 Air flow capacity under the standard condition (ANR) [atmospheric pressure 20°C, relative humidity 65%]
- *3 Air flow capacity converted by the compressor intake condition
- [32°C, Atmospheric pressure, and 75% relative humidity] *4 When the operating conditions are different from the rated values, select a model in accordance
- with Model Selection (page 147) or calculate the air flow capacity suitable to the operating conditions based on the Correction of Air Flow Capacity.
- *5 Do not use this product with continuous voltage fluctuations
- *6 These values are reference values under rated conditions and are not guaranteed. Do not use these values for the thermal relay set values, etc.
- *7 Products other than Option R are not equipped with an earth leakage breaker. Purchase an appropriate earth leakage breaker separately. Use an earth leakage breaker with a leak current sensitivity of 30 mA.
- *8 This is the value specified by IPCC4 AR4. The value specified by the Revised Fluorocarbons Recovery and Destruction Law (Japanese law) is R410A GWP: 2090.
- *9 The maximum operating pressure is 1.0 MPa as standard, but it is possible to achieve 1.6 MPa when selecting Option L or Option V.

Correction of Air Flow Capacity

Inlet air	Inlet air temperature [°C]									
°C	5 to 25	30	35	40	45	50	55	60	65	
Correction factors	1.42	1.15	1.00	0.71	0.62	0.50	0.40	0.33	0.21	

Ambient temperature [°C]									
°C	2 to 25	30	35	40	45				
Correction factors	1.00	0.85	0.80	0.73	0.62				

Inlet air pressure [MPa]

MPa	0.3	0.4 0.5		0.6	0.7 to 1.6	
Correction factors	0.71	0.75	0.82	0.89	1.00	


Calculation example: The air flow capacity when the dew point of the IDFA60 is set to 10°C under the following conditions is calculated. [Operating conditions: Inlet air temperature: 35°C, Ambient temperature: 35°C, Inlet air pressure: 0.6 MPa] $360 \text{ m}^3/\text{h}$ (ANR) x $1.00 \times 0.80 \times 0.89 = 256 \text{ m}^3/\text{h}$ (ANR)




IDFA Series

Construction (Air/Refrigerant Circuit)

Humid, hot air coming into the air dryer will be cooled down by a cooler re-heater (heat exchanger). Water condensed at this time will be removed from the air by an auto drain and drained out automatically. Air separated from the water will be heated by a cooler reheater (heat exchanger) to obtain the dried air, which goes through to the outlet side.



Dimensions




															[]
Model	Port size	Α	В	С	D	E	F	G	Н	J	K	L	M	N	0
IDFA60	R1	307	745	605	161	405	681	94	71	46	12.5 330 365 11 463	330	20	704	355
IDFA70	R1 1/2	342	890	825	176		905	94	68	46		365		849	390
IDFA80	R2	438	957	863	169	480	958	219	78	100		20	916	485	
IDFA90	nz	436	957	003	169		956	219	/ °	100	''	463		916	465

IDFA Series


Optional Accessories

Foundation Bolt Set



				[mm]
Part no.	Nominal thread size	Material	Number of 1 set	Α
IDF-AB500	M10	Stainless steel	4	50

Piping Adapter



Part no.	Thread type	_	D	Е	Material	Number of		
	Male thread A side	Female thread B side					1 set	
IDF-AP604	NPT1	Rc1	50	27	46			
IDF-AP606	NPT1 1/2	Rc1 1/2	55	31	54	Brass	2	
IDF-AP607	NPT2	Rc2	65	30	70			

Bypass Piping Set




, .PP	ouble un un joi
Symbol	Applicable dryer
339	IDFA60
340	IDFA70
341	IDFA80
341	IDFA90

Max. operating pressure: 1.0 MPa

* Not applicable to the moderate pressure specification Prepare a bypass piping set suitable for the specification.

For IDFA60: IDF-BP339


Weight: 5 kg



For IDFA70: IDF-BP340

[mm]


Weight: 10 kg



For IDFA80, IDFA90: IDF-BP341

[mm]

[mm]



IDFA Series Options

Option symbol

Cool compressed air output

Cool outlet air (10°C) can be supplied.

The air flow with this option is smaller than that of the standard air dryer. (Refer to the table below.)

If the air dryer is used out of the scope of the rated specifications or conditions, select a model according to page 147 and apply the air flow capacity shown in the table below to the data (0).

* Perform thermal insulation treatment for pipings and equipment installed after the dryer to prevent the formation of condensation.

Air Flow Capacity

Model		Air flow capacity m ³ /h (ANR)					
		IDFA60-23-A	IDFA70-23-A	IDFA80-23-A	IDFA90-23-A		
Outlet air pressure dew point	10°C	186	300	462	576		

Rated conditions: Inlet air pressure: 0.7 MPa, Inlet air temperature: 35°C, Outlet air temperature: 10°C



This minimizes the corrosion of the copper and copper alloy parts when the air dryer is used in an atmosphere containing hydrogen sulfide or sulfurous acid gas. (Corrosion cannot be completely prevented.) Special epoxy coating: Copper tube and copper alloy parts. The coating is not applied on the heat exchanger or around electrical parts, where

* Failure due to corrosion is not covered under warranty.

operation may be affected by the coating




In addition, Chinese labels are put on the external panels.

A Chinese operation manual is also included.

Option symbol With a heavy-duty auto drain (applicable to moderate pressure)

The float type auto drain used in the standard air dryer is replaced with a heavy-duty auto drain (ADH4000-04) which enables the condensate to discharge more efficiently. The product can be used for moderate pressure with this option.

Max. operating pressure: 1.6 MPa




 The heavy-duty auto drain and piping materials (nipple, elbow) are shipped together with the main body of the air dryer. Customers are required to mount the parts to the air dryer.

Replacement Parts: Heavy-Duty Auto Drain

Replacement part no. (Description)	Configuration
ADH4000-04 (Heavy-duty auto drain)	Heavy-duty auto drain
ADH-E400 (Replacement kit for exhaust mechanism)	Replacement kit for exhaust mechanism Housing (Use existing equipment.)

Option symbol With an earth leakage breaker

The air dryer is equipped with an earth leakage breaker, reducing the electrical wiring required during installation.







With a terminal block for operating, error, and remote operation signals

In addition to power supply connection, terminal blocks for operating, error, and remote operation signals are available.

. The operating and error signals are no-voltage contact style.


Operating signal...During operation: contact "close", During stop: contact "open"

Error signal...During error: contact "close", During stop: contact "open" Contact capacity...Rated load voltage: 240 VAC or less/24 VDC or less

Max. load current: 5 A (Resistance load)/2 A (Induction load)

Min. applicable load: 20 VDC, 3 mA

 Power supply voltage is applied to the remote operation contact. The external switch is to be prepared by customers. Position holding switch (alternate type switch) or automatic return switch (momentary switch) can be used.





Option symbol

With a timer controlled solenoid valve type auto drain (applicable to moderate pressure)


Drainage is discharged by controlling a solenoid valve with a timer.

A strainer for solenoid valve protection and a stop valve are also included.

Max. operating pressure: 1.6 MPa

Replacement Parts

Part no.	Note
IDF-S0534	200 to 230 VAC





IDFA Series Specific Product Precautions 1

Be sure to read this before handling the products. For safety instructions and air preparation equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

Installation


⚠ Caution

- Avoid locations where the air dryer will be in direct contact with wind or rain. (Avoid locations where relative humidity is 85% or more.)
- Avoid locations where water, water vapor, salt water, or oil may splash on the product.
- · Avoid locations where dust or other particles are present.
- · Avoid locations where flammable or explosive gases are present.
- Avoid locations where corrosive gases, solvents, or combustible gases are present
- · Avoid locations which receive direct sunlight or radiated heat.
- Avoid locations where the ambient temperature exceeds the limits as mentioned below.

During operation: 2 to 45°C

During storage: 0 to 50°C (when there is no drain water inside of the piping)

- Avoid locations where temperature substantially changes.
- Avoid locations where strong magnetic noise occurs. (Avoid locations where strong electric fields, strong magnetic fields, or surge voltages occur.)
- Avoid locations where static electricity occurs or conditions which make the product discharge static electricity.
- · Avoid locations where high frequencies occur.
- · Avoid locations where damage is likely to occur due to lightning.
- Avoid installation on machines used for transporting, such as vehicles, ships, etc.
- · Avoid locations at altitudes of 2000 meters or higher.
- · Avoid locations where strong impacts or vibrations occur.
- Avoid conditions where a massive force strong enough to deform the product is applied or the weight from a heavy object is applied.
- Avoid locations with insufficient space for maintenance.
- · Avoid locations where the ventilation grille is obstructed.
- Avoid locations where the air dryer will draw in high-temperature air discharged from an air compressor or other dryer.



Confirm that the exhaust air does not flow into the neighboring equipment.

- Avoid pneumatic circuits where rapid pressure fluctuations or flow speed changes are generated.
- When installing in locations where the dripping of condensation is a problem
 Depending on the operating conditions, the product and its downstream
 pipes could drip water due to condensation formed by supercooling. If this
 is a problem, install a drain receiver below this product or the condensation points and empty it regularly. Alternatively, wind additional insulation
 around the condensation points.

Drain Tube

⚠ Caution

- A tube with an outside diameter of 12 mm is attached as a drain tube. Use this tube to discharge condensate to a drain tank, etc.
- Do not use the drain tube in an upward direction. Do not bend or crush the drain tube. If it is unavoidable that the tube goes upward, make sure it only goes as far as the position of the auto drain outlet. The drain tube to be prepared should have an O.D. of 12 mm, an I.D. of 8 mm or more, and be 5 m or less in length. Otherwise, the auto drain will not operate correctly, which may cause air to be blown constantly or moisture not to be exhausted.

Power Supply


⚠ Caution

- Connect the power supply to the terminal block.
- Install an earth leakage breaker*1 suitable to each model for the power supply.
- Maintain a voltage range within ±10% of the rated voltage. (Do not use this product with continuous voltage fluctuations.)
- *1 Select an earth leakage breaker with a leak current sensitivity of 30 mA.
 - Regarding the rated current, refer to the Applicable Earth Leakage Breaker Capacity.
- When a short-term interruption of the power supply (including momentary interruptions) occurs in this equipment, the restarting of normal operations may require some time or may be impossible due to the operation of protective devices even after the supply of power returns.

Air Piping

⚠ Caution

- Be careful to avoid any errors in connecting the air piping at the compressed air inlet (IN) and outlet (OUT).
- Flush the piping sufficiently in order to avoid any foreign matter such as dust, sealant tape, liquid gasket, etc., before connecting piping. Foreign matter in the piping can cause cooling failure or drainage failure.
- Inlet and outlet compressed air connections should be made removable by using a union, etc.
- Provide bypass piping to make it possible to do maintenance without stopping the air compressor.
- When tightening the inlet/outlet air piping, firmly hold the port on the air dryer with a pipe wrench, etc.
- Use pipes and fittings that can endure the operating pressure and temperature. Connect them firmly to prevent air leakage.
- Do not allow the load of the piping to lie directly on the air dryer.
 When mounting any part, such as an air filter, on the fitting at the compressed air inlet or outlet port, support the part to prevent excessive force from being applied to the product.
- Be careful not to let the vibrations of the air compressor transmit.
- If a metallic flexible tubing is used for the inlet/outlet air piping, abnormal noise might be generated in the piping. In such cases, please use steel tubing instead.
- If the temperature of the compressed air on the inlet side is over 65°C, place an aftercooler after the air compressor. Or, lower the temperature of the place where the air compressor is installed to below 65°C.
- If the air supply generates high pressure fluctuations (pulsations), take appropriate countermeasures, such as installing an air tank.
- If rapid pressure fluctuations or flow changes occur, install a filter on the dryer outlet to prevent condensate from splashing.
- Variations in operating conditions may cause condensation to form on the surface of the outlet piping. Apply thermal insulation around the piping to prevent condensation from forming.







IDFA Series Specific Product Precautions 2

Be sure to read this before handling the products. For safety instructions and air preparation equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

Protection Circuit

When the air dryer is operated in the following cases, the protection circuit will activate, the light will turn off and the air dryer will come to stop.

- The compressed air temperature is too high.
- . The compressed air flow rate is too high.
- The ambient temperature is too high. (45°C or higher)
- The fluctuation of the power supply voltage is beyond ±10% of the rated voltage.
- The air dryer is drawing in high temperature air exhausted from an air compressor or other dryer.
- The ventilation grille is obstructed by a wall or clogged with dust.

Transportation and Installation

⚠ Warning

Be sure to follow the instructions below for transporting the product.

- The product is filled with refrigerant. Transport it (by land, sea or air) in accordance with laws and regulations specified.
- When carrying the product, be careful not to let it drop or fall over, and use a forklift.
- . Do not lift the product by holding the panel, fittings or piping.
- Never lay the product down for transportation. This may lead to damage to the product.
- The product is heavy and has potential dangers in transportation. Be sure to follow the instructions above.
- Be sure to use a forklift for transporting the product. Weight of each model with packaging: IDFA60: 57 kg, IDFA70: 78 kg, IDFA80: 106 kg, IDFA90: 122 kg

Compressor Air Delivery

⚠ Caution

Since the auto drain is designed in such a way that the valve remains open unless the air pressure rises to 0.1 MPa or higher, air will blow out from the drain outlet at the time of air compressor start up until the pressure increases. Therefore, if an air compressor has a small air delivery, the pressure may not be sufficient.

Auto Drain

⚠ Caution

The auto drain may not function properly, depending on the quality of the compressed air. Check the operation once a day.

Cleaning of Ventilation Area

If the dustproof filter becomes clogged with dust or debris, a decline in cooling performance can result.

In order to avoid deforming or damaging the dustproof filter, clean it with a long-haired brush or air gun once a month.

Time Delay for Restarting

Allow at least three minutes before restarting the air dryer. Otherwise, the protection circuit will activate, the light will turn off and the air dryer will not start up.

Modifying the Standard Specifications

Do not modify the standard product using any of the optional specifications once the product has been supplied to a customer. Check the specifications carefully before selecting an air dryer. In addition, do not disassemble or modify the product. Products which have been disassembled and/or modified cannot be quaranteed.

■ Refrigerant with GWP Reference

	Global Warming Potential (GWP)						
Refrigerant	Regulation (EU)	Fluorocarbon Emissions Control Act (Japan)					
nelliyelalli	No 51 //2014	GWP value labeled on	GWP value to be used for reporting				
	(Based on the IPCC AR4)	products	the calculated amount of leakage				
R134a	1430	1430	1300				
R404A	3922	3920	3940				
R407C	1774	1770	1620				
R410A	2088	2090	1920				

- This product is hermetically sealed and contains fluorinated greenhouse gases (HFC). When this product is sold on the market in the EU after January 1, 2017, it needs to be compliant with the quota system of the F-Gas Regulation in the EU.
- * See specification table for refrigerant used in the product.