
Compact Cylinder/Plate type

CQU Series

Size: 20, 25, 32, 40



● Total length: Reduced by up to 15%

Volume: Reduced by up to 18%


Weight: Reduced by up to 36%

Light and compact!



A Dimension Comparison

| COI | прап | SOII | (mm) | | | | | | |
|------|------|------|----------------|--|--|--|--|--|--|
| Size | A | | | | | | | | |
| Size | CQU | CQ2 | Reduction rate | | | | | | |
| 20 | 22 | 36 | 39% | | | | | | |
| 25 | 24 | 40 | 40% | | | | | | |
| 32 | 28 | 45 | 38% | | | | | | |
| 40 | 32 | 52 | 38% | | | | | | |



B/C Dimensions Comparison


| | | | | | | (111111) | | |
|------|-----|----|----------------|------|----|----------------|--|--|
| Size | | В | | С | | | | |
| Size | CQU | MU | Reduction rate | CQU | MU | Reduction rate | | |
| 20 | 47 | _ | _ | 72.5 | _ | _ | | |
| 25 | 53 | 54 | 2% | 72.5 | 85 | 15% | | |
| 32 | 62 | 68 | 9% | 79.5 | 88 | 10% | | |
| 40 | 80 | 86 | 7% | 79.5 | 90 | 12% | | |
| | | | | | | | | |

* Compared with 30 stroke.

| • | Weight |
|---|-----------|
| | Compariso |


| | | | (9) |
|------|-----|--------|----------------|
| Size | | Weight | |
| Size | CQU | MU | Reduction rate |
| 20 | 153 | | _ |
| 25 | 180 | 252 | 29% |
| 32 | 272 | 376 | 28% |
| 40 | 351 | 552 | 36 % |
| | | | |

* Compared with 30 stroke.




Seals can be replaced easily just by removing the retaining rings.

 A small type of auto switch can be mounted from 4 directions.
 No protrusion of auto switch from the mounting slot



 Auto switch can be mounted without removing a support bracket.





specified. Refer to page 1086.

Through-hole/Both ends tapped common

Through-hole/Both ends tapped common (Standard)

Through-hole/Both ends tapped common (Standard)

Vertical foot

Double clevis

Variations


| Model | 0: | | Stroke | | | | | | | | | | | O his | Mounting | Rod end |
|-------|------|---|--------|----|----|----|----|----|----|----|----|----|-----|---------|--|---------|
| Model | Size | 5 | 10 | 15 | 20 | 25 | 30 | 35 | 40 | 45 | 50 | 75 | 100 | Cushion | | Hou enu |
| | 20 | • | • | • | • | • | • | • | • | • | • | _ | _ | | Through-hole/Both ends tapped common (Standard) Vertical foot Lateral foot Double clevis | Male |
| CQU | 25 | • | • | • | • | • | • | • | • | • | • | _ | _ | Rubber | | thread |
| CQU | 32 | • | • | • | • | • | • | • | • | • | • | • | • | bumper | | Female |
| | 40 | • | • | • | • | • | • | • | • | • | • | • | • | | | thread |

Compact Cylinder: Plate Type Double Acting, Single Rod

CQU Series

Size: 20, 25, 32, 40

How to Order



Applicable Auto Switches/Refer to pages 1271 through to 1365 for further information on auto switches

| | | Floridad | igh | 10/5-5 | L | oad volta | ge | Auto swit | ch model | Lead | wire | lengtl | h (m) | Data seriand | | | | | | | | | | | | | | | | | | |
|---------------------|--|---------------------|-----------------|----------------------------|------|-----------------|---------------|---------------|------------|--------------|------------|----------|----------|---------------------|-----------------|------------|----------|----------|------------|---------|----------|---------|--|-------|------|---|---|---|---|---|------------|-----|
| Туре | Special function | Electrical entry | Indicator light | Wiring (Output) | D | C | AC | Perpendicular | In-line | 0.5 (Nil) | 1 (M) | 3 (L) | 5 | Pre-wired connector | Applicable load | | | | | | | | | | | | | | | | | |
| _ | | | | 3-wire (NPN) | | 51/ 401/ | | M9NV | M9N | • | • | • | 0 | 0 | IC circuit | | | | | | | | | | | | | | | | | |
| switch | _ | | | 3-wire (PNP) | | 5 V, 12 V | | M9PV | M9P | • | • | • | 0 | 0 | IC circuit | | | | | | | | | | | | | | | | | |
| | | | | 2-wire | | 12 V | | M9BV | M9B | • | • | • | 0 | 0 | _ | | | | | | | | | | | | | | | | | |
| anto | B | | | 3-wire (NPN) | | 4 V 5 V, 12 V _ | 5 V 40 V | EV 10 V | E 1/ 10 1/ | E V 40 V | E 1/ 10 1/ | 5 V 40 V | 51/ 401/ | 51/ 401/ | E 1/ 10 1/ | EV 10 V | 5 V 40 V | 5 V 40 V | E 1/ 10 1/ | EV 40 V | 51/ 101/ | EV 10 V | | M9NWV | M9NW | • | • | • | 0 | 0 | IC circuit | D-1 |
| | Diagnostic indication (2-color indicator) | Grommet | Yes | 3-wire (PNP) | 24 V | | M9PWV | M9PW | • | • | • | 0 | 0 | IC circuit | Relay, PLC | | | | | | | | | | | | | | | | | |
| state | (2-color indicator) | | | 2-wire | | 12 V | 1 | M9BWV | M9BW | • | • | • | 0 | 0 | _ |] [| | | | | | | | | | | | | | | | |
| | | | | 3-wire (NPN) | | EV 10 V | 5 V. 12 V | | M9NAV*1 | M9NA*1 | 0 | 0 | • | 0 | 0 | IC circuit | | | | | | | | | | | | | | | | |
| Solid | Water resistant (2-color indicator) | | | 3-wire (PNP) | | 3 V, 12 V | | M9PAV*1 | M9PA*1 | 0 | 0 | • | 0 | 0 | IC circuit | | | | | | | | | | | | | | | | | |
| | (2-color indicator) | | | 2-wire | | 12 V | | M9BAV*1 | M9BA*1 | 0 | 0 | • | 0 | 0 | _ | | | | | | | | | | | | | | | | | |
| Reed auto switch | | Grommet | Yes | 3-wire (NPN equivalent) | _ | 5 V | - | A96V | A96 | • | - | • | - | _ | IC circuit | _ | | | | | | | | | | | | | | | | |
| Be to s | _ | Grommet | | 2-wire | 24 V | 12 V | 100 V | A93V*2 | A93 | • | • | • | • | _ | _ | Relay, | | | | | | | | | | | | | | | | |
| an | | | No | 2-wire | 24 V | 12 0 | 100 V or less | A90V | A90 | • | - | • | 1- | _ | IC circuit | PLC | | | | | | | | | | | | | | | | |

^{*1} The water resistant improved D-M9

A and M9

Vype can be mounted, but cylinders are not designed to be water resistant improved construction.

(Example) M9NWZ

^{*2 1} m type lead wire is only applicable to D-A93

^{*} Lead wire length symbols: 0.5 m Nil (Example) M9NW 1 m M (Example) M9NWM 3 m ----- L 5 m ---- Z (Example) M9NWL

^{*} Solid state switches marked with "O" are produced upon receipt of order.

^{*} For details about the auto switch with pre-wired connector, refer to pages 1340 and 1341.

^{*} Auto switches are shipped together, (but not assembled).

Note) The D-M9□V, M9□WV, M9□AV, and A9□V type cannot be mounted on the port surface depending on the cylinder's stroke and the fitting size for piping. Please confirm SMC separately

CQU Series



Symbol

Rubber bumper (Non-circular piston)



Specifications

| Equivalent bore size (mm) | 20 | 25 | 32 40 | | | | | |
|-----------------------------|--|------------------|-----------------|--------|--|--|--|--|
| Action | | Double actin | g, Single rod | • | | | | |
| Fluid | | А | ir | | | | | |
| Proof pressure | | 1.0 l | MРа | | | | | |
| Maximum operating pressure | | 0.7 I | MРа | | | | | |
| Minimum operating pressure | 0.08 MPa 0.05 MPa | | | | | | | |
| Ambient and fluid | Without auto switch: -10 to 70°C (No freezing) | | | | | | | |
| temperature | With a | auto switch: -10 | to 60°C (No fre | ezing) | | | | |
| Cushion | | Rubber | bumper | | | | | |
| Rod end thread | | Female threa | d, Male thread | | | | | |
| Stroke length tolerance | | +1 | | | | | | |
| Mounting | Thro | ugh-hole/Both e | nds tapped con | nmon | | | | |
| Piston speed 50 to 500 mm/s | | | | | | | | |

^{*} The stroke length tolerance does not include the changed amount of the rubber bumper due to compression.

Theoretical Output

| | | | | → OUT | <u></u> ⊢IN | Unit (N) |
|------|----------|-----------|-------------|--------|--------------|----------|
| Size | Rod size | Operating | Piston area | Operat | ing pressure | (MPa) |
| Size | (mm) | direction | (mm²) | 0.3 | 0.5 | 0.7 |
| 20 | 10 | IN | 236 | 71 | 118 | 165 |
| 20 | 10 | OUT | 314 | 94 | 157 | 220 |
| 25 | 10 | IN | 412 | 124 | 206 | 288 |
| 23 | 10 | OUT | 491 | 147 | 246 | 344 |
| 32 | 14 | IN | 650 | 195 | 325 | 455 |
| 32 | 14 | OUT | 804 | 241 | 402 | 563 |
| 40 | 14 | IN | 1103 | 331 | 552 | 772 |
| 40 | 14 | OUT | 1256 | 377 | 628 | 879 |

Standard Stroke

| | Unit (mm) |
|--------|--|
| Size | Standard stroke |
| 20, 25 | 5, 10, 15, 20, 25, 30, 35, 40, 45, 50 |
| 32, 40 | 5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100 |

^{*} Other intermediate strokes can be manufactured upon receipt of order. Please contact SMC.

Support Bracket Part No.

| Size | Vertical f | oot Note 1) | Latera | Double clevis | | |
|------|------------|-------------|----------|---------------|---------------|--|
| Size | Rod end | Head end | Rod end | Head end | Double clevis | |
| 20 | CQU-LR20 | CQU-LH20 | CQU-MR20 | CQU-MH20 | CQU-D20 | |
| 25 | CQU | -L25 | CQU | CQU-D25 | | |
| 32 | CQU | I-L32 | CQU | CQU-D32 | | |
| 40 | CQU | l-L40 | CQU | CQU-D40 | | |

Note 1) When ordering a foot bracket of size 20, check which end, rod end or head end, it will be on. For other sizes, the part number is common to both ends.

Note 2) Parts belonging to each bracket are as follows.

Vertical foot, Lateral foot: Body mounting bolt

Double clevis: Clevis pin, C-type retaining ring for shaft, Body mounting bolt



Compact Cylinder: Plate Type CQU Series Double Acting, Single Rod

Weight

| Size | | | | | | Cylinde | er strok | e (mm) | | | | |
|------|-----|-----|-----|-----|-----|---------|----------|--------|-----|-----|-----|-----|
| Size | 5 | 10 | 15 | 20 | 25 | 30 | 35 | 40 | 45 | 50 | 75 | 100 |
| 20 | 105 | 115 | 125 | 134 | 144 | 153 | 163 | 173 | 182 | 192 | _ | _ |
| 25 | 127 | 138 | 148 | 159 | 169 | 180 | 190 | 201 | 211 | 222 | _ | _ |
| 32 | 199 | 214 | 228 | 243 | 257 | 272 | 286 | 301 | 315 | 330 | 402 | 475 |
| 40 | 264 | 282 | 299 | 316 | 333 | 351 | 368 | 385 | 403 | 420 | 506 | 593 |

| Additional Weight | | | | | Unit (g) |
|---|----------------------|-----|-----|-----|----------|
| Size | | 20 | 25 | 32 | 40 |
| Ded and male three ed | Male thread | 19 | 19 | 32 | 32 |
| Rod end male thread | Nut | 4 | 4 | 10 | 10 |
| Vertical foot (Including mounting | bolt) | 84 | 91 | 122 | 162 |
| Lateral foot (Including mounting | bolt) | 105 | 113 | 145 | 203 |
| Double clevis (Including pin, retaining | ring, mounting bolt) | 60 | 76 | 149 | 266 |

How to Calculate

Unit (g)

(Example) CQUD32-50M


 Basic weight: CQUB32-50-----330 g Additional weight: Rod end male thread------ 42 g Double clevis ······ 149 g

Mounting Bolt for CQU

How to Mount: Use this bolt for mounting into a through-hole. Refer to the following for ordering procedures.

Order the actual number of bolts that will be used.

Example) CQ-M5 x 55L 2 pcs.



| 1 | r | ٠ | ٦ | ۰ | Y | ١ |
|---|---|---|---|---|---|---|
| | | | | | | |

| | | | (11111) |
|----------------|-----|-----|------------------------|
| Cylinder model | С | D | Mounting bolt part no. |
| CQUB20-5 | | 55 | CQ-M5 x 55L |
| -10 | | 60 | x 60L |
| -15 | | 65 | x 65L |
| -20 | | 70 | x 70L |
| -25 | 7.5 | 75 | x 75L |
| -30 | 7.5 | 80 | x 80L |
| -35 | | 85 | x 85L |
| -40 | | 90 | x 90L |
| -45 | | 95 | x 95L |
| -50 | | 100 | x 100L |

| (| m | ın | n) |
|---|---|----|----|

| Cylinder model | С | D | Mounting bolt part no. |
|----------------|------|-----|------------------------|
| CQUB32-5 | | 65 | CQ-M5 x 65L |
| -10 | | 70 | x 70L |
| -15 | | 75 | x 75L |
| -20 | | 80 | x 80L |
| -25 | | 85 | x 85L |
| -30 | 10.5 | 90 | x 90L |
| -35 | 10.5 | 95 | x 95L |
| -40 | | 100 | x 100L |
| -45 | | 105 | x 105L |
| -50 | | 110 | x 110L |
| -75 | | 135 | x 135L |
| -100 | | 160 | x 160L |

| | | | (mm |
|----------------|-----|-----|------------------------|
| Cylinder model | С | D | Mounting bolt part no. |
| CQUB25-5 | | 55 | CQ-M5 x 55L |
| -10 | | 60 | x 60L |
| -15 | | 65 | x 65L |
| -20 | | 70 | x 70L |
| -25 | 7.5 | 75 | x 75L |
| -30 | 7.5 | 80 | x 80L |
| -35 | | 85 | x 85L |
| -40 | | 90 | x 90L |
| -45 | | 95 | x 95L |
| -50 | | 100 | x 100L |


| | | | (11111) |
|----------------|------|-----|------------------------|
| Cylinder model | С | D | Mounting bolt part no. |
| CQUB40-5 | | 65 | CQ-M5 x 65L |
| -10 | | 70 | x 70L |
| -15 | | 75 | x 75L |
| -20 | | 80 | x 80L |
| -25 |] | 85 | x 85L |
| -30 | 10.5 | 90 | x 90L |
| -35 | 10.5 | 95 | x 95L |
| -40 | | 100 | x 100L |
| -45 | | 105 | x 105L |
| -50 | | 110 | x 110L |
| -75 | | 135 | x 135L |
| -100 | | 160 | x 160L |

Material: Chromium molybdenum steel Surface treatment: Zinc chromated







Allowable Kinetic Energy





Allowable Rod End Lateral Load





Allowable rod end lateral load can be found from the above graph. Do not apply a load beyond the line on the graph.





Rod end male thread

Component Parts

| Description | Material | Note |
|-----------------------|--|--|
| Rod cover | Aluminum die-casted | Chromated |
| Head cover | Aluminum die-casted | Chromated |
| Cylinder tube | Aluminum alloy | Hard anodized |
| Piston | Aluminum die-casted | Chromated |
| Dieton rod | Stainless steel | ø20, ø25 |
| Pistoli Tou | Carbon steel | ø32, ø40, Hard chrome plated |
| Bushing | Bearing alloy | |
| Wear ring | Fluoropolymer | |
| N-type retaining ring | Carbon tool steel | Phosphate treatment |
| Bumper | Urethane | |
| Magnet | _ | |
| Rod seal | NBR | |
| Piston seal | NBR | |
| O-ring | NBR | |
| Rod end nut | Carbon steel | Chromated |
| | Rod cover Head cover Cylinder tube Piston Piston rod Bushing Wear ring N-type retaining ring Bumper Magnet Rod seal Piston seal O-ring | Rod cover Aluminum die-casted Head cover Aluminum die-casted Cylinder tube Aluminum die-casted Piston Aluminum die-casted Piston rod Stainless steel Carbon steel Bearing alloy Wear ring Fluoropolymer N-type retaining ring Carbon tool steel Bumper Urethane Magnet — Rod seal NBR Piston seal NBR O-ring NBR |

Replacement Parts: Seal Kit

| Size | Kit no. | Contents | | | | |
|------|-----------|----------------------------|--|--|--|--|
| 20 | CQUB20-PS | | | | | |
| 25 | CQUB25-PS | Set of component | | | | |
| 32 | CQUB32-PS | parts (8), (1), (12), (13) | | | | |
| 40 | CQUB40-PS | | | | | |

- * Seal kit includes ®, 11, 12, 13. Order the seal kit, based on each size.
- * Seal kit does not include a grease package. Order it separately.
 * Grease package part number: GR-S-010 (10 g)


SMC



Dimensions

* For auto switch mounting position and its mounting height, refer to page 1085.

Basic (Through-hole/Both ends tapped common): CQUB



Basic (mm) Stroke range В ΕX ΕY F н ΚA L NX NY Size Α D Κ Q Υ (mm) 20 5 to 50 42.5 22 M5 x 0.8 depth 8 5 5.5 3 49 10 47 11.5 8 6.5 36 15 25 5 to 50 49 42.5 10 24 53 11 M5 x 0.8 depth 8 5 8 41 4 32 5 to 100 49.5 14 28 12 M8 x 1.25 depth 13 6 12 6.5 15 3 40 5 to 100 49.5 14 31 12 M8 x 1.25 depth 13 6 6.5 15 3

| Rod End Male Thread (r | | | | | | | | | | | | |
|------------------------|----|----------------|----------------|------|------------|--|--|--|--|--|--|--|
| Size | х | C ₁ | B ₁ | L1 | H1 | | | | | | | |
| 20 | 18 | 15.5 | 13 | 24.5 | M8 x 1.25 | | | | | | | |
| 25 | 18 | 15.5 | 13 | 24.5 | M8 x 1.25 | | | | | | | |
| 32 | 26 | 23.5 | 19 | 32.5 | M12 x 1.25 | | | | | | | |
| 40 | 26 | 23.5 | 19 | 32.5 | M12 x 1.25 | | | | | | | |


^{*} For details about the rod end nut, refer to page 1084.


Dimensions


Vertical foot: CQUL












Vertical Foot

| 10.11041.1001 | | | | | | | | | | | | (111111) | | |
|---------------|--------------|------|------|------|----------------|----|------|------|-----|----|------|----------|------|---|
| Size | Stroke range | Α | В | L | L ₁ | LD | LH | LS | LT | LX | LY | LZ | Х | Υ |
| 20 | 5 to 50 | 82.5 | 42.5 | 21.5 | 39.5 | 6 | 30 | 67.5 | 3.2 | 11 | 53.5 | 21 | 12.5 | 6 |
| 25 | 5 to 50 | 82.5 | 42.5 | 21.5 | 39.5 | 6 | 32.5 | 67.5 | 3.2 | 11 | 59 | 23 | 12.5 | 6 |
| 32 | 5 to 100 | 90.5 | 49.5 | 21.5 | 47.5 | 7 | 37.5 | 76.5 | 3.2 | 12 | 68.5 | 27 | 13.5 | 6 |
| 40 | 5 to 100 | 99 | 49.5 | 26.5 | 52.5 | 9 | 46.5 | 79.5 | 3.2 | 15 | 86.5 | 30 | 15 | 8 |


Lateral foot: CQUM


Vertical foot bracket material: Carbon steel Surface treatment: Nickel plated



Rod end male thread








CQUM20

Lateral Foot


| Eutorui i Got | | | | | | | | | | | | | (111111) | |
|---------------|--------------|------|------|------|----------------|----|------|------|-----|----|------|----|----------|---|
| Size | Stroke range | Α | В | L | L ₁ | MD | МН | MS | MT | MX | MY | MZ | Х | Υ |
| 20 | 5 to 50 | 82.5 | 42.5 | 21.5 | 39.5 | 6 | 15 | 67.5 | 3.2 | 36 | 26 | 47 | 12.5 | 6 |
| 25 | 5 to 50 | 82.5 | 42.5 | 21.5 | 39.5 | 6 | 14.5 | 67.5 | 3.2 | 42 | 26.5 | 53 | 12.5 | 6 |
| 32 | 5 to 100 | 90.5 | 49.5 | 21.5 | 47.5 | 7 | 15.5 | 76.5 | 3.2 | 48 | 29.5 | 62 | 13.5 | 6 |
| 40 | 5 to 100 | 99 | 49.5 | 26.5 | 52.5 | 9 | 16.5 | 79.5 | 3.2 | 63 | 32 | 80 | 15 | 8 |


Lateral foot bracket material: Carbon steel

Surface treatment: Nickel plated



Rod end male thread





Double Clevis

| Double Cle | Double Clevis | | | | | | | | | | | | |
|------------|---------------|----|------|----|----|----|----|----|----|----|-----|----------------|----|
| Size | Stroke range | Α | В | CD | CL | СТ | CU | CW | СХ | CZ | L | L ₁ | RR |
| 20 | 5 to 50 | 72 | 42.5 | 8 | 64 | 4 | 9 | 15 | 8 | 16 | 6.5 | 24.5 | 8 |
| 25 | 5 to 50 | 74 | 42.5 | 8 | 66 | 4 | 11 | 17 | 9 | 18 | 6.5 | 24.5 | 8 |
| 32 | 5 to 100 | 88 | 49.5 | 10 | 78 | 7 | 13 | 22 | 11 | 22 | 6.5 | 32.5 | 10 |
| 40 | 5 to 100 | 93 | 49.5 | 10 | 83 | 10 | 13 | 27 | 13 | 26 | 6.5 | 32.5 | 10 |

^{*} For details about the rod end nut and accessory brackets, refer to page 1084.


Double clevis bracket material: Carbon steel Surface treatment: Metallic painted



CQU Series

Accessory Brackets


Single Knuckle Joint



| | | | | | | (mm) |
|----------|----------------------|------------|------|----------------|----------------|----------------|
| Part no. | Size | A 1 | E1 | L ₁ | М | M |
| I-G02 | 20, 25 | 8.5 | 16 | 25 | M8 x | 1.25 |
| I-MU03 | 32, 40 | 12 | 18 | 31 | M12 | c 1.25 |
| | | | | | | |
| Part no. | NDH10 | NL | NO | NX | R ₁ | U ₁ |
| I-G02 | 8+0.058 | 9 | 20.5 | 8 | 10.3 | 11.5 |
| I-MU03 | 10 ^{+0.058} | 10 | 24 | 11 | 10 | 14 |

Single knuckle joint material: Rolled steel


Double Knuckle Joint



| Y-G02 | 20, 25 | 8.5 | _ | 25 | M8 x 1.25 | 8+0.058 |
|-------------------|----------------|------------|-----------|-----------|----------------|----------------|
| Y-MU03 | 32, 40 | 12 | 18 | 31 | M12 x 1.25 | 10+0.058 |
| | | | | | | |
| | | | | | | |
| Part no. | NL | NO | NX | NZ | R ₁ | U ₁ |
| Part no. Y-G02 | NL 9 | NO 20.5 | NX | NZ | R ₁ | U ₁ |

Part no Size A1 F1 I1 MM


Knuckle Pin (Common with Double Clevis Pin)



| Part no. | m | t | Applicable retaining ring |
|----------|------|------|---------------------------|
| IY-G02 | 1.5 | 0.9 | C-type 8 for shaft |
| CD-MU02 | 1.5 | 0.9 | C-type 8 for shaft |
| CD-MU03 | 1.25 | 1.15 | C-type 10 for shaft |
| CD-MU04 | 1.25 | 1.15 | C-type 10 for shaft |

- * Knuckle pin is included in the double clevis and double knuckle joint as standard.
- * C-type retaining ring for shaft is included.

Rod End Nut




| Part no. | Size | MM | Н | В | С | D |
|---------------------|----------------|------------|----------|-----------|----------|---------|
| NT-02 | 20, 25 | M8 x 1.25 | 5 | 13 | 15.0 | 12.5 |
| NT-MU03 | 32, 40 | M12 x 1.25 | 7 | 19 | 21.9 | 18 |
| * A nut is included | in the rod end | Roo | d end nu | ıt materi | al: Carb | on stee |

male thread as standard.

Rod end nut material: Carbon steel Surface treatment: Chromated

Pin material: Carbon steel

Double Clevis Socket



| | | | | | | | | | (mm) |
|----------|------|----|----|----------------------|-----|----|----|----|------|
| Part no. | Size | CA | СВ | CD _{H10} | CE | CF | СН | CI | CJ |
| MU-C02 | 25 | 53 | 23 | 8+0.058 | 3.5 | 4 | 11 | 17 | 7 |
| MU-C03 | 32 | 67 | 27 | 10+0.058 | 3.5 | 7 | 13 | 22 | 10 |
| MU-C04 | 40 | 85 | 31 | 10 ^{+0.058} | 3.5 | 10 | 13 | 27 | 10 |


| Part no. | CL | CR | СТ | СХ | CZ | |
|----------|----|-----|-----|----|----|--------------------------------|
| MU-C02 | 26 | 5.3 | 9.5 | 9 | 8 | Double clevis socket material: |
| MU-C03 | 42 | 6.4 | 11 | 11 | 10 | Cast iron |
| MU-C04 | 54 | 8.4 | 14 | 13 | 10 | Surface treatment: Painted |

Note) Double clevis socket is available for sizes from 25 to 40.

^{*} Knuckle pin and retaining ring are included. Double knuckle joint material: Rolled steel Chromated (Y-MU03)

CQU Series Auto Switch Mounting

Auto Switch Proper Mounting Position (Stroke End Detection) and Its Mounting Height



| Size | D-M9□ D-M9□W D-M9□A | | | D-M9□V D-M9□WV D-M9□AV | | | | D-A9□ | | | | D-A | 9□V | (11111) |
|------|---------------------------|------|-----|------------------------------|------|------|------|-------|-----|---------|------|-----|------|---------|
| | Α | В | С | Α | В | Hs | Hv | Α | В | С | Α | В | Hs | Hv |
| 20 | 19 | 11.5 | 1.5 | 19 | 11.5 | 14 | 23 | 15 | 7.5 | 5.5 (3) | 15 | 7.5 | 12.5 | 20.5 |
| 25 | 19 | 11.5 | 1.5 | 19 | 11.5 | 15.5 | 25 | 15 | 7.5 | 5.5 (3) | 15 | 7.5 | 14 | 23 |
| 32 | 22 | 15 | 5 | 22 | 15 | 17 | 30 | 18.5 | 11 | 9 (6.5) | 18.5 | 11 | 15.5 | 27.5 |
| 40 | 22 | 15 | 5 | 22 | 15 | 17.5 | 37.5 | 18.5 | 11 | 9 (6.5) | 18.5 | 11 | 16.5 | 35 |

^{():} D-A93

Minimum Stroke for Auto Switch Mounting


| | | (mm) |
|-------------------------|------------------------------------|--|
| Number of auto switches | D-M9□ D-M9□V D-A9□ D-A9□V | D-M9□W D-M9□WV D-M9□A D-M9□AV |
| 1 pc. | 5 | 10 |
| 2 pcs. | 10 | 15 |

Operating Range

| | | | | (mm) |
|------------------------------|-----|----|-----|------|
| Auto switch model | | Si | ze | |
| Auto switch model | 20 | 25 | 32 | 40 |
| D-M9□/M9□V Note) | 2 | 2 | 2 | 2 |
| D-M9□W/M9□WV D-M9□A/M9□AV | 3 | 3 | 3.5 | 3 |
| D-A9□/A9□V | 6.5 | 6 | 6 | 5.5 |

^{*} Since this is a guideline including hysteresis, not meant to be guaranteed. (Assuming approximately ±30% dispersion) Value may greatly change depending on the surrounding environment.

Auto Switch Mounting



Use a watchmaker's screwdriver with a grip diameter of 5 to 6 mm to tighten the auto switch mounting screw.

| Tightening torque for auto switch | mounting screw (N·r |
|-----------------------------------|---------------------|
| Auto switch model | Tightening torque |
| D-M9□(V) D-M9□W(V) D-A93 | 0.05 to 0.15 |
| D-M9□A(V) | 0.05 to 0.10 |
| D-A9□(V) (Excludes the D-A93) | 0.10 to 0.20 |



^{*} For actual setting, check the operation of the auto switch and adjust as necessary.

Note) In products delivered from August 2008 onwards, the value will be the same as the D-M9□W, M9□WV, M9□A, and M9□AV.



CQU Series Specific Product Precautions

Be sure to read this before handling the products.


Refer to page 20 for safety instructions and pages 21 to 30 for actuator and auto switch precautions.

Precautions

⚠ Caution

- All loads to piston rod must be applied in axial direction only.
 - When a lateral load is applied unavoidably, ensure that it should not exceed the allowable lateral load to the rod end as specified on page 1080.
 - When installing a cylinder, centering should be required accurately.
 - Adoption of guide mechanism is strongly recommended for the case when the CQU is used as stopper to prevent nonrotating piston rod from side loads.
- When securing a workpiece to the end of the piston rod, ensure that the piston rod is retracted entirely, and tighten using the width across flats on the rod end, making sure to avoid the application of rotational torque on the piston rod.





 Operating the cylinder by connecting the piping directly to the cylinder can cause the piston speed to exceed the maximum operating speed of 500 mm/s. Therefore, to operate the cylinder, make sure to use an SMC speed controller and adjust the piston speed to 500 mm/s or less.

Retaining Ring Installation/Removal

⚠ Caution

- For installation and removal, use an appropriate pair of pliers (tool for installing a C-type retaining ring).
- 2. Even if a proper plier (tool for installing a C-type retaining ring) is used, it is likely to inflict damage to a human body or peripheral equipment, as a retaining ring may be flown out of the tip of a plier (tool for installing a C-type retaining ring). Be much careful with the popping of a retaining ring. Besides, be certain that a retaining ring is placed firmly into the groove of rod cover before supplying air at the time of installment.
- Do not reuse the retaining ring once it has been removed. (The retaining ring is included in the seal kit.)

SMC Logo


↑ Caution

 The direction of the SMC logo on the end face of the head cover is not specified in relation to the port position.

Handing of Auto Switches


⚠ Warning

 If multiple cylinders are operated adjacent to each other, the magnets that are enclosed in the adjacent cylinders could affect the operation of the auto switches, causing the switches to malfunction. Therefore, make sure that the mounting pitch of the cylinders is at least that indicated in the table below.



| | | | | (mm) |
|------|-----|----|----|------|
| Size | 20 | 25 | 32 | 40 |
| L | 30 | 29 | 33 | 36 |
| Ч | g g | 5 | 5 | - 5 |

2. If the cylinder is used in an application in which a magnetic material is placed in close contact around the cylinder as shown in the graph below (including cases in which even one of the sides is in close contact) the operation of auto switches could become unstable. Therefore, please check with SMC for this type of application.



When multiple cylinders are installed close together and an auto switch with perpendicular entry for lead wire is used, the auto switch will protrude from the end of the tube, so take care to avoid interference. (Refer to page 1085.)

