Hand Valve **VH Series**



Specifications

	Fluid		Air			
	Proof pressure		1.5 MPa			
	Max. operating pressure	VH200/300/400	1.0 MPa			
		VH600	0.7 MPa			
	Ambient temperature and	operating fluid temperature	-5 to 60°C (No freezing)			
	Operating angle		90°			
	Lubrication		Not required (Use turbine oil Class 1 ISO VG32, if lubricated			


Model

The value in brackets refers to the port size.

	Port size	Number of positions	Piping direction	Model		Flow rate characteristic				Mariela			
Series				Body	Panel	` ` ` `	P)→2(A)/4(B)		2(A)/4(B)→3(Weight (kg)	
				mount	mount	C[dm3/(s-bar)]	b	Cv	C[dm3/(s-bar)]	b	Cv		
		3 (Closed center)	A)	VH200-02	VH210-02	1.5	0.25	0.38	1.5	0.25	0.38	0.42	
		3 (Exhaust center)	1 3 2	VH201-02	VH211-02								
		2 (Position)		VH202-02	VH212-02								
		3 (Closed center)	4 3 3 1 2	VH240-02	VH250-02								
VH2	1/4	3 (Exhaust center)		VH241-02	VH251-02								
		2 (Position)		VH242-02	VH252-02								
		3 (Closed center)	4 12 3	VH220-02	VH230-02		1.1 0.2	0.28	1.1	0.2	0.28		
		3 (Exhaust center)		VH221-02	VH231-02	1.1 0.2							
		2 (Position)		VH222-02	VH232-02								
		3 (Closed center)	4 3 3 4 1 2 2 3 3	VH300-02/03	VH310-02/03								
		3 (Exhaust center)		VH301-02/03	VH311-02/03	5.4(1/4) 6.4(3/8) 0.25	1.25(1/4)	5.4(1/4)	0.25	1.25(1/4)	0.71		
VH3	1/4, 3/8	2 (Position)		VH302-02/03	VH312-02/03		1.5(3/8)	6.4(3/8)		1.5(3/8)			
VIII		3 (Closed center)		VH320-02/03	VH330-02/03	4.5(4/4)	0.2		. = (4 (4)	0.2		0.71	
		3 (Exhaust center)		VH321-02/03	VH331-02/03	4.5(1/4)		1.1(1/4)	4.5(1/4)		1.1(1/4)		
		2 (Position)		VH322-02/03	VH332-02/03	5.3(3/8)		1.3(3/8)	5.3(3/8)		1.3(3/8)		
		3 (Closed center)		VH400-02 to 06	VH410-02 to 06	14.3(1/4)	0.25	3.4(1/4)	14.3(1/4)	0.25	3.4(1/4)		
		3 (Exhaust center)	4 33	VH401-02 to 06	VH411-02 to 06	15.6(3/8)		3.8(3/8)	15.6(3/8)		3.8(3/8)	. 1.28	
		2 (Position)	100	VH402-02 to 06	VH412-02 to 06	17.5(1/2) 18.4(3/4)		4.3(1/2) 4.5(3/4)	17.5(1/2) 18.4(3/4)		4.3(1/2) 4.5(3/4)		
VH4	1/4 to 3/4	3 (Closed center)	-6D	VH420-02 to 06	VH430-02 to 06	11.9(1/4)	3.0(3/8) 0.2 0.2	2.9(1/4)	11.9(1/4)	0.2	2.9(1/4)		
		3 (Exhaust center)		VH421-02 to 06	VH431-02 to 06	13.0(3/8)		3.1(3/8)	13.0(3/8)		3.1(3/8)		
		2 (Position)		VH422-02 to 06	VH432-02 to 06	14.6(1/2) 15.4(3/4)		3.5(1/2) 3.7(3/4)	14.6(1/2) 15.4(3/4)		3.5(1/2) 3.7(3/4)		
	3/4, 1	3 (Closed center)	s in the same	VH600-06/10		37(3/4) 38.8(1)		3.7(3/4)	10.4(0/4)	*/	0.7 (0/4)	+	
VH6		3 (Exhaust center)	201	VH601-06/10	_		37(3/4) 0.25	0.25	10.2(3/4)	37(3/4)	0.25	10.2(3/4)	9.7
		2 (Position)	3 4	VH602-06/10	-			10.5(1)	38.8(1)		10.5(1)	"	
			~ •						I			1511	

VH Series

How to Order



Symbol










Handle Operation Angle and Air Flow Direction


(Refer to the figures of piping direction to the right.)




Flow Rate Characteristics














Construction


VH200







VH300/400





VH600





Component Parts

No.	Description	Material				
INO.	Description	VH200/300/400	VH600			
1	Cover	Zinc die-casted				
2	Body	Aluminium die-casted	Cast iron			

Replacement Parts

Danasiation	No.	Component parts	Material	Part no.			
Description				VH200	VH300	VH400	
Maintenance	3	Slide ring	Resin				
and repair kit*	4 Slide ring spring		Piano wire	KT-VH2□□-N	KT-VH3□□-N	KT-VH4□□-N	
ана геран ки	5	O-ring	NBR				
	6	Handle head	Zinc alloy	24403A	24413A	24413A	
Handle head	7	Spring	Piano wire				
assembly *	8	Pin	Structural steel				
	9	Steel ball	SUJ				
	6	Handle head	Zinc alloy		244125A	244125A	
Handle head	7	Spring	Piano wire				
assembly *	8	Pin	Structural steel	244036A			
u000	9	Steel ball	SUJ				
	10	Handle	_				
		Standard		244032	244032	244032	
Handle	10	10 Long type	-	_	244127	244223	
		Red]	244035	244035	244035	

Part No. of Lock Nut for Panel Mount

Series	Part no.					
VH200	244010					
VH300	24418					
VH400	240258					

Note) Not applicable to the VH600 series.




Note) Replacement parts for the VH600 series are not available.


^{*} Including grease.


VH Series

Dimensions


VH20□/21□-02









VH24□/25□-02





VH22□/23□-02 (Bottom ported) 2(A) 3(R) 4(B) 4x 1/4

Panel cut dimension




Max. panel thickness D


				(mm)
	Α	В	С	D
VH200	3.2	40	35	3.5
VH300	3.2	51	41	6
VH400	3.2	64	51	8




VH30□/31□-02 to 03

(): Long handle type





VH32□/33□-02 to 03 (Bottom ported)




Refer to page 1514 for the panel cut dimension.


VH Series

Dimensions


VH40□/41□-02 to 04

(): Long handle type







VH42□/43□-02 to 04 (Bottom ported)




VH40□/41□-06

(): Long handle type







VH42□/43□-06 (Bottom ported)




Refer to page 1514 for the panel cut dimension.

VH600-06/10









VH Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 15 for 3/4/5 port solenoid valve precautions.

Design

⚠ Warning

 Not suitable for use as a selector valve or a divider valve.

The valve can malfunction due to air leakage.

2. Not suitable for negative pressure.

The valve can malfunction due to air leakage

Do not supply air pressure from other ports than 1(P) port.

Air leakage may occur when the pressure is supplied from other ports.

Selection

⚠ Warning

1. Intermediate stop

When stopping the cylinder piston in the middle using the 3 position closed center valve, it is not possible to stop it correctly and precisely as the hydraulic equipment due to the air compressibility. Do not use this valve because it has slight air leakage and can not hold a stopping position. When it is necessary to hold a stopping position, select an equipment to prevent displacement and design the circuit.

∴ Caution

1. Use in low temperature environments

The valve can be used at a temperature down to -5° C. Take appropriate measures to avoid freezing of drainage, moisture, etc.

2. Operation method

The valve must be switched to each position instantly and securely. Stopping the handle halfway between the extreme positions may cause malfunction.

3. Switch the valve by hand

If a hammer or other tools are used, or it is operated mechanically through the use of a cylinder or the like, damage could result.

Piping

⚠ Caution

 Ensure connection so that air is supplied to the port "1(P)" port.

Air leakage may occur when the pressure is supplied from other ports.

Environment

Marning

 When the valve is exposed to a large amount of dust, install a silencer into the port "3(R)". When dust enters the valve from the port "3(R)", it may cause air leakage.



