
Self-seal Fittings **KC Series**





One-touch fitting (built-in self-seal mechanism) to prevent air exhaust when removing tube.

Best for multiple use areas when pressure cannot be shut down.

10 types are available.

Brass parts are electroless nickel plated.

Sealant is standard.



Applicable Tubing

Tubing material	Nylon, Soft nylon, Polyurethane
Tubing O.D.	ø4, ø6, ø8, ø10, ø12

Specifications

Fluid		Air
Maximum operating pre	essure	1 MPa
Proof pressure		3 MPa
Ambient and fluid temp	erature	-5 to 60°C (No freezing)
	Mounting section	JIS B 0203 (Taper thread for piping)
Thread	Mounting section	JIS B 0205 (Metric fine thread)
	Nut section	JIS B 0205 (Metric fine thread)
Seal on the threads (Sta	andard)	With thread seal
Brass parts surface trea	atment (Standard)	Electroless nickel plated


Principal Parts Material

Body	C3604, PBT
Stud	C3604 (Thread portion)
Chuck, Spring	Stainless steel 304
Guide	Stainless steel 304, PBT
Collet, Release button	POM
Valve, Retainer	POM
Stopper	C3604, POM
Seal, O-ring	NBR
Gasket	Stainless steel 304, NBR



KC Series

Model




Male Connector: KCH

<M5>



Applicable tubing O.D. (mm)	Connection thread R	Model	H (width across	L	A *	м	Effectiv (mi		Weight (g)	
0.D. (IIIII)	M		flats)				invion	Uretnane		
4	M5 x 0.8	KCH04-M5	9.8	30.8	27.3	18	2.1	2.1	8	
4	1/8	KCH04-01S	10	26.1	22.1	10	2.6	2.6	0	
	M5 x 0.8	KCH06-M5	11.8	32.4	28.9	19.5	2.4	2.4	10	
6	1⁄8	KCH06-01S	12	37.4	33.4	19	6.8	6.8	16	
	1/4	KCH06-02S	14	28.9	22.9	19	0.0	0.0	14	
	1⁄8	KCH08-01S	14	42.4	38.4				20	
8	1⁄4	KCH08-02S	14	45.7	39.7	21.5	16.2	13.1	27	
	3⁄8	KCH08-03S	17	34	27.5				25	
10	1/4	KCH10-02S	17	50.5	44.5	24	25.6	20.4	34	
10	3/8	KCH10-03S		51.5	45	24	25.0	20.4	43	
12	3⁄8	KCH12-03S	19	54.2	47.7	25.5	35.4	30.4	48	
12	1/2	KCH12-04S	22	41.6	33.6	20.0	33.4	30.4	41	
		*	Reference	ce dim	ension	s after	R threa	ad insta	llation.	


H



Male Elbow: KCL



tubing	R	Model	(width across	øD1	øD2	2 L1 L2		A *	м	(mi	m²)	(a)	
O.D. (mm)	M		flats)							Nylon	Urethane	(g)	
4	M5 x 0.8	KCL04-M5	8	10.4	8	25.3	16.7	18.4	18	1.9	1.9	6	
4	1/8	KCL04-01S	10	10.4	10	20.0	22.1	24.2	10	2.3	2.3	11	
	M5 x 0.8	KCL06-M5	8		8	26.8	17.4	20.3	19.5	2.2	2.2	7	
6	1⁄8	KCL06-01S	12	12.8	12	28	24.2	27.5	19	6.2	6.2	13	_
	1/4	KCL06-02S	14		12	20	28.6	29.5	19	0.2	0.2	21	1
	1⁄8	KCL08-01S	14				26.2	30.7				16	Ŧ
8	1/4	KCL08-02S	14	15.2	14	34.1	30.6	32.7	21.5	13.0	10.5	24	
	3/8	KCL08-03S	17				30	34.2				37	8 N
10	1/4	KCL10-02S	17	18.5	17	38	33.4	37.2	24	19.5	16.5	29	
10	3/8	KCL10-03S	17	10.5	17	30	34.8	38.7	24	19.5	10.5	38	
12	3/8	KCL12-03S	22	20.9	20.9	40.7	39.2	44.3	25.5	04.0	01.0	63	1
12	1/2	KCL12-04S	22	20.9	20.9	40.7	42.3	45.7	25.5	24.8	21.3	81	



Connection thread (With sealant)


* Reference dimensions after R thread installation.

Effective area

Union Tee: KCT



Applicable tubing	Model	øD	L	Q	м	(m		Weight
O.D. (mm)						Nylon	Urethane	(g)
4	KCT04-00	10.4	28.6	5.3	18	2.8	2.8	8
6	KCT06-00	12.8	32.7	6.1	19	7.6	7.6	15
8	KCT08-00	15.2	39.2	7.1	21.5	13.7	11.1	23
10	KCT10-00	18.5	45.5	7.9	24	21.1	19.0	39
12	KCT12-00	20.9	49.2	8.6	25.5	28.3	24.3	52



Click here for applicable color caps.

KC Series

Union "Y": KCU

5 5	Applicable tubing O.D. (mm)	Model	øD	L1	L2	Ρ	Q	M1	M2		<i>)</i>	Weight			
	4	KCU04-00	10.4	43.1	27.3	10.4	10.6	18	16	3.7	3.7	8		11	
	6	KCU06-00	12.8	48	31.2	12.8	12.5	19	17	10.0	10.0	14		Ξ	
OHT	8	KCU08-00	15.2	57.6	38.9	15.2	14.7	21.5	18.5	21.7	15.1	22		y 2	
	10	KCU10-00	18.5	65.2	44.9	18.5	17.1	24	21	33.3	25.6	37		1	
	12	KCU12-00	20.9	70.1	48.8	20.9	19.1	25.5	22	48.9	38.7	49	-	<u>ø8</u>	
														<u>ø4.2</u>	Q 3 x applicable tubing


Check Adaptor: KCJ

L

Applicable tubing		Applicable fitting size	øD	L	A	м	Effectiv (mr		Weight
O.D. (mm)		ød					Nylon	Urethane	(g)
4	KCJ04-99	4	9.8	49.5	33.5	18	2.6	2.6	9
6	KCJ06-99	6	11.8	54	37	19	6.8	6.8	13
8	KCJ08-99	8	14	61	42.5	21.5	16.2	13.1	20
10	KCJ10-99	10	17	70.4	49.4	24	25.6	20.4	33
12	KCJ12-99	12	19	74.4	52.4	25.5	35.4	30.4	43

Connecting products with metal rods

Products with metal rods cannot be connected to Series KQ2 One-touch fittings. If connected, the metal rod cannot be retained by the chuck of the One-touch fitting and products with metal rods may project during pressurization, causing serious personal injury or accident.




øD

Bulkhead Union: KCE

	tubing O.D. (mm)	
MIN NO R	4	
	6	
Annua Annua -	8	
	10	


	Applicable tubing O.D. (mm)	Model	т (М)	H (width across flats)	L	Mounting hole	M1	M2	(m	ve area m²) Urethane	Weight
ATM NO.	4	KCE04-00	M12 x 1	14	42	13	18	16	2.6	2.6	21
-04	6	KCE06-00	M14 x 1	17	45.5	15	19	17	6.8	6.8	30
	8	KCE08-00	M16 x 1	19	52.5	17	21.5	18.5	16.2	13.1	39
	10	KCE10-00	M20 x 1	24	59.5	21	24	21	25.6	20.4	84
	12	KCE12-00	M22 x 1	27	63.2	23	25.5	22	35.4	30.4	115



Bulkhead Connector: KCE




Applicable tubing O.D. (mm)	Connection thread RC	Model	т (М)	(width across flats)	H2 (width across flats)	L1	L2	Mounting hole	м	Effectiv (m Nylon	m²)	We
4	1/4	KCE04-02	M12 x 1	17	14	40.5	14.7	13	18	2.6	2.6	3
6	1/4	KCE06-02	M14 x 1	17	17	42.7	14.7	15	19	6.8	6.8	3
8	3/8	KCE08-03	M16 x 1	19	19	49.4	15	17	21.5	16.2	13.1	4
10	3/8	KCE10-03	M20 x 1	22	24	53.9	14.2	21	24	25.6	20.4	7
12	3/8	KCE12-03	M22 x 1	24	27	56.1	13.7	23	25.5	35.4	30.4	10



Click here for applicable color caps.


Straight Union: KCH

1




Straight Plug for Frequent Use:KCH

Applicable tubing	Model	Applicable fitting size	øD	L	A	м	Effectiv (m	/e area m²)	Weight
O.D. (mm)		ød					Nylon	Urethane	(g)
4	KCH04-99	4	9.8	40.6	22.6	16	5.6	4	5
6	KCH06-99	6	11.8	43.1	24.1	17	13.1	10.4	8
8	KCH08-99	8	14	46.7	25.2	18.5	26.1	18.0	11
10	KCH10-99	10	17	52.6	28.6	21	41.5	29.5	18
12	KCH12-99	12	19	54.9	29.4	22	58.3	46.1	24



Elbow Plug for Frequent Use: KCL

-	Applicable tubing O.D. (mm)		Applicable fitting size ø d		ø D2	L1	L2	A	IVI	Effectiv (m Nylon	11)	Weight (g)
	4	KCL04-99	4	10.4	10	18	34.3	22.6	16	4.2	4.2	7
	6	KCL06-99	6	12.8	10	20	36.5	24.1	17	11.4	9.0	8
	8	KCL08-99	8	15.2	12	23	40.3	25.2	18.5	21.6	14.9	12
	10	KCL10-99	10	18.5	17	26.5	44.3	28.6	21	35.2	25.0	25
	12	KCL12-99	12	20.9	17	28.5	46.8	29.4	22	50.2	39.7	30



Click here for applicable color caps.



KC Series/Specific Product Precautions

Be sure to read this before handling the products. Refer to page 11 for safety instructions and pages 14 to 18 for fittings and tubing precautions.

No. of Insertions and Removals from Self-seal Fittings

- 1. The number of insertions and removals as a rough guide is as follows.

 - Metal stem 1000 times

Self-seal fittings that have once been attached to connecting plugs cannot be used for tube connection.

It cannot be secured and the fittings will be lurched.

Mounting/Piping

▲Caution

1. When mounting tubes, resin plugs, reducers, etc., do not press the release button. This may cause those parts to come off.

In particular, be aware that when products, such as plug-in elbows or reducers, etc. are mounted, the release button of the fitting on the connection side may be pressed easily due to product handling during piping work.

Distinction of Plug and Applicable Fittings

Caution

- 1. The applicable fitting should be chosen depending on the type of plug.
- Check Adaptor

How to use: Use it for addition of self-seal mechanism to a standard One-touch fitting. Self-seal fittings with check adaptor are not available. It causes air leakage.




 Elbow plug for frequent use, straight plug for frequent use. How to use: For use in the case of frequent tube installation and removal, tube cutting labor can be saved.

These plugs cannot be connected to One-touch fittings other than self-seal fittings KC series.

If connected, the metal rod cannot be retained by the chuck of the One-touch fitting and elbow plug for frequent use/straight plug for frequent use may project during pressurization, causing serious personal injury or accident.

Note the exclusive marking for self-seal fittings before use.



2. Connecting products with metal rods

Products with metal rods cannot be connected to KQ2 series One-touch fittings.

If connected, the metal rod cannot be retained by the chuck of the One-touch fitting and products with metal rods may project during pressurization, causing serious personal injury or accident.

After attaching products with attached metal rods, to the One-touch fitting, do not use tubes, resin plugs, or reducers, etc. This may cause releasing.

For details about One-touch fittings that can connect KCJ model, contact SMC.

Tube Insertion and Removal under Pressurized Condition

Caution

@SMC

 When inserting/removing the tubing is difficult under a pressurized condition, it should be inserted or removed by lowering the pressure or after fully exhausting.