
Blow Gun

VMG Series




The electricity used by compressors for air accounts for **approximately 20**% of that consumed by the entire factory. Also, 70% of the air consumed in the process is used for air blowing. SMC blow guns have minimal pressure loss compared with current models, so they can achieve equivalent performance at lower pressures and with less volume of air consumption. As a result, it is possible to achieve a 20% reduction in power consumption.


Energy Saving Pneumatic System Proposal

Energy Saving Effects

When the yearly total working hours spent on air blowing amounts to 8,300 hours, use of current models results in power consumption costs totaling 194,220 yen. When using the SMC system (Blow gun + S coupler + Coil tube), however, the yearly cost is reduced to 155,625 yen, for a total yearly saving of 38,595 yen, or 20% of the total.



Energy saving effects with Blow gun (VMG) only



Calculation conditions


- Blowing distance: 100 mm
- Impact pressure: 0.011 MPa
- · Cost of electricity: 15 yen/kWh


Work model


- Blow time: 10 seconds
- Frequency: 12 times/hour
- Working hours: 10 hours/day
- Working days: 250 days/year
- Units used: 100
- Resulting total working hours: 8,300 hours

Valve Construction and Pressure Loss

Straighter flowing fluid "improves pressure loss!"











Example of Improvement

Review the air-blow job and change to the SMC blow gun, S coupler and coil tube to create a larger effective area.






		After improvement	Before improvement
	Coupler	S coupler	Current model
Equipment	Piping	TCU1065-1-20-X6	Current coil tube model (I.D. Ø5, equivalent length 5 m)
	Air gun	VMG (Nozzle size ø2.5)	Current model (Nozzle size ø3)
Effective	Coupler, Piping (S ₀)	13.45 mm²	5.1 mm²
	Air gun (S ₁)	30 mm²	6 mm²
area	Nozzle (S ₂)	4.4 mm ²	6.3 mm ²
Effective area ratio (S ₀ to S ₁ : S ₂)		3.04 : 1	0.69 : 1
Impact pressure		0.011 MPa (at a distance of 100 mm)	0.011 MPa (at a distance of 100 mm)
Regulator pre	essure	0.4 MPa	0.5 MPa
Pressure insi	de nozzle	0.385 MPa	0.276 MPa
Compressor pressure		0.5 MPa	0.6 MPa
Air consumption		257 dm³/min (ANR)	287 dm³/min (ANR)
Power consumption by compressor		wer consumption by compressor 1.25 kW	



Blow Gun, Coil Tube and S Coupler Selection

Recommended system in accordance with the distance

Energy saving effects are enhanced through the appropriate blow gun model selection in accordance with the distance from the target object.




	Recommended system					
Distance	Blow gun	Nozzle size	Fitting	Coil tube*	S coupler	
Up to 20 mm	VMG1□□-02-01	ø1	KQ2H06-02AS	TCU0604□-1-20-X6	KK4P-06H	
Up to 40 mm	VMG1□□-02-02	ø1.5	KQ2H06-02AS	TCU0604□-1-20-X6	KK4P-06H	
Up to 60 mm	VMG1□□-02-03	ø 2	KQ2H08-02AS	TCU0805□-1-20-X6	KK4P-08H	
Over 60 mm	VMG1□□-02-04	ø 2. 5	KQ2H10-02AS	TCU1065□-1-20-X6	KK4P-10H	


^{*□:} B (Black), W (White), R (Red), BU (Blue), Y (Yellow), G (Green), C (Clear), YR (Orange)

Energy Saving Flow


Air guns with an effective area around 6 mm² are most commonly used. But the SMC blow gun achieves a 30 mm² effective area.




Related Product



Variations



With Flow Rate Adjustment Function (Made to Order) D. 1558



Operability, Safety, Environment

Not affected by supply pressure, assured operability

When using this product even at a high pressure, the same gripping force is required as for a lower pressure due to the unique balance-poppet construction.



Use of shockresistant resin

Shock-resistant resin is used in the main body. No cracks, breaks or other damage occurred in a drop test from a 2-meter height or in a human stomp test.



Components are separable. Environmentally friendly

Resin parts are inscribed with the name of the material. Additionally, all parts can be separated by material.




VMG Series





VMG11W-02-32-C



Body color

W	White
BU	Dark blue

Connection size

		COI	inection size
Symbol	Piping connection method	Size ar	nd model no.
02			Rc1/4
03			Rc3/8
N02	Threaded	Thread size	NPT1/4
N03	Illieaded		NPT3/8
F02			G1/4
F03			G3/8
11	S coupler	Model no. of	KK4P-02MS
12	plug	coupler used	KK130P-02MS
H06	Metric size	Mandal	KQ2H06-02AS
H08	One-touch fitting	Model no. of fitting used	KQ2H08-02AS
H10	One-touch litting	illing used	KQ2H10-02AS
H07	Inch size	Model no. of	KQ2H07-35AS
H09	One-touch fitting	fitting used	KQ2H09-35AS
H11	One loadin litting	mung useu	KQ2H11-35AS

Note 1) S coupler and fitting are included in the same

package.

Note 2) Port size is Rc1/4 if using the S coupler plug.

Note 3) The blow gun port size is Rc1/4 if using the

metric size One-touch fitting.

Note 4) The blow gun port size is NPT1/4 if using the inch size One-touch fitting.

Specifications

Fluid	Air	
Operating pressure range	0 to 1.	0 MPa
Proof pressure	1.5 [MPa
Ambient and fluid temperature	−5 to 60°C (No freezing)	
Flow rate characteristics (With nozzle removed)	C (dm³/s·bar): 6.0, b: 0.25 (Effective area: 30 mm²)	
Port size	Rc, NPT,	G 1/4, 3/8
Piping entry	Bottom Top	
Nozzle port size	Rc1/4	
Weight (Main unit only)	165 g	
Operational force (when the valve is fully open)	7 N	



Made to Order (For details, refer to page 1558.)

	or details, refer to page 1556.
Symbol	Specifications
-VE/I	With flow rate adjustment function

With nozzle cover (Only for male thread nozzle, o6 extension nozzle)

Nil	None
С	With nozzle cover/HNBR
CF	With nozzle cover/Fluororubber

Nozzle

Symbol	Type	Nozzle size	Nozzle part no.
Nil		Vithout nozzle	HOLLIO PARTITO.
01		g1	KN-R02-100
02		ø1.5	KN-R02-150
03		ø2	KN-R02-200
04	Male thread nozzle	ø2.5	KN-R02-250
05		ø3	VMG1-R02-300
06		ø3.5	VMG1-R02-350
07		ø4	VMG1-R02-400
11		ø1	KNH-R02-100
12	High efficiency nozzle	ø1.5	KNH-R02-150
13		ø2	KNH-R02-200
21		ø0.75 x 4	KNS-R02-075-4
22	Low noise nozzle	ø0.9 x 8	KNS-R02-090-8
23	with male thread	ø1 x 4	KNS-R02-100-4
24		ø1.1 x 8	KNS-R02-110-8

Extension nozzle


Symbol	Type	Nozzle length	Nozzle size	Nozzle part no.
31		200	ø1.5	VMG1-06-150-300
32		300 mm	ø2	VMG1-06-200-300
33	ø6 copper	600 mm	ø1.5	VMG1-06-150-600
34	extension	600 11111	ø2	VMG1-06-200-600
35	nozzle Note)	100 mm	ø1.5	VMG1-06-150-100
36		100 11111	ø2	VMG1-06-200-100
37		150 mm	ø1.5	VMG1-06-150-150
38		130 111111	ø2	VMG1-06-200-150
41		100 mm	ø2.5	VMG1-08-250-100
42			ø3	VMG1-08-300-100
43			ø3.5	VMG1-08-350-100
44		150 mm	ø2.5	VMG1-08-250-150
45	ø8 copper		ø3	VMG1-08-300-150
46	extension		ø3.5	VMG1-08-350-150
47	nozzle Note)		ø2.5	VMG1-08-250-300
48		300 mm	ø3	VMG1-08-300-300
49			ø3.5	VMG1-08-350-300
50			ø2.5	VMG1-08-250-600
51		600 mm	ø3	VMG1-08-300-600
52			ø3.5	VMG1-08-350-600

Note) Part number for set of extension nozzle and fitting. Extension nozzle and fitting are included in the same package.

Refer to "How to attach extension nozzle" in the operation manual for assembly procedures.

VMG Series

Construction



Component Parts


00	pononi i arto		
No.	Description	Material	Note
1	Body L	PBT	
2	Body R	PBT	
3	Main valve	PBT	
4	Valve guide	POM	
5	Nozzle holder	Aluminium alloy	Anodized
6	Port	Aluminium alloy	Anodized
7	Elbow	PBT	Only for the VMG12□
8	Cover	Stainless steel	
9	Ring	Stainless steel	
10	Arm	PBT	
11	Spring	Stainless steel	
12	Main valve seal	HNBR	
_13	Lever	PBT	
14	Piping (bottom)	РОМ	Only for the VMG11 Combined with the elbow 7.
15	O-ring	NBR	
16	O-ring	NBR	
17	Parallel pin	Stainless steel	
18	Cross recessed round head screw	Stainless steel	
19	Hexagon nut	Stainless steel	

Note) Grease is used on rubber and sliding sections.


Flow Rate Characteristics

Note) Values when the main valve is fully open


Male thread nozzle




High efficiency nozzle




Low noise nozzle with male thread



Copper extension nozzle



Dimensions



					(mm)
Symbol	Ту	pe	Nozzle part no.	Nozzle size	A Note)
01			KN-R02-100	ø1	23.4
02			KN-R02-150	ø1.5	23
03	Male thre	and	KN-R02-200	ø2	22.5
04	nozzle	au	KN-R02-250	ø2.5	22.1
05	HOZZIC		VMG1-R02-300	ø3	22
06			VMG1-R02-350	ø3.5	21.5
07			VMG1-R02-400	ø4	21.5
11	11:-140		KNH-R02-100	ø1	
12	High effic	ciency	KNH-R02-150	ø1.5	44
13	HOZZIE		KNH-R02-200	ø2	
21			KNS-R02-075-4	ø0.75 x 4	
22	Low nois	e nozzle	KNS-R02-090-8	ø0.9 x 8	12
23	with male	e thread	KNS-R02-100-4	ø1 x 4	12
24			KNS-R02-110-8	ø1.1 x 8	
31		Nozzle length:	VMG1-06-150-300	ø1.5	298
32		300 mm	VMG1-06-200-300	ø2	290
33	ø6 copper extension nozzle ^{Note)}	Nozzle length:	VMG1-06-150-600	ø1.5	598
34		600 mm	VMG1-06-200-600	ø2	296
35		Nozzle length:	VMG1-06-150-100	ø1.5	98
36	I IOZZIE	100 mm	VMG1-06-200-100	ø2	30
37		Nozzle lenath:	VMG1-06-150-150	ø1.5	140

VMG1-06-200-150

38

150 mm

Note) Reference dimensions after installation

102 117.5

41			VMG1-08-250-100	ø2.5	
42		Nozzle length: 100 mm	VMG1-08-300-100	ø3	98
43		100 111111	VMG1-08-350-100	ø3.5	
44			VMG1-08-250-150	ø2.5	
45		Nozzle length: 150 mm	VMG1-08-300-150	ø3	148
46	ø8 copper	130 11111	VMG1-08-350-150	ø3.5	
47	extension nozzle Note)		VMG1-08-250-300	ø2.5	
48	TIOZZIG	I NOZZIO ICIIGIII.	VMG1-08-300-300	ø3	298
49		300 mm	VMG1-08-350-300	ø3.5	
50			VMG1-08-250-600	ø2.5	
51		Nozzle length: 600 mm	VMG1-08-300-600	ø3	598
52		000 11111	VMG1-08-350-600	ø3.5	

Nozzle part no.

			(mm)
Type	One-touch fitting model	B Note)	C Note)
Metric size	KQ2H06-02AS	12	153.2
One-touch fitting	KQ2H08-02AS	17.3	158.6
	KQ2H10-02AS	22.6	163.8
Inch size	KQ2H07-35AS	12.3	153.2
One-touch fitting	KQ2H09-35AS	17.7	158.9
	KQ2H11-35AS	20.7	162

Note) Reference dimensions after installation

Type

Symbol



(mm) A Note)

Nozzle size

VMG Series

Dimensions: Nozzles/KN Series

Male thread nozzle: KN

(mm)



Part no.	Nozzle size D	Connection thread	Width across flats H1	L ₁	A *
KN-R02-100	ø1		14	31.4	25.4
KN-R02-150	ø1.5			31	25
KN-R02-200	ø2			30.5	24.5
KN-R02-250	ø2.5	R1/4		30.1	24.1
VMG1-R02-300	ø3			30	24
VMG1-R02-350	ø3.5			29.5	23.5
VMG1-R02-400	ø4			29.5	23.5



High efficiency nozzle: KNH (Compliant with OSHA Standards: Operating pressure at 0.5 MPa or less.) (mn



Part no.	Nozzle size D	Connection thread	H1	L ₁	A *
KNH-R02-100	ø1				
KNH-R02-150	ø1.5	R1/4	14	52	46
KNH-R02-200	ø2				




Low noise nozzle with male thread: KNS

(mm)



Part no.	Nozzle size D	Connection thread	Width across flats H1	L1	A *
KNS-R02-075-4	ø0.75 x 4				
KNS-R02-090-8	ø0.9 x 8	R1/4	14	20	14
KNS-R02-100-4	ø1 x 4	H 1/4	14	20	1**
KNS-R02-110-8	ø1.1 x 8				



Copper extension nozzle set


(mm)



Part no.	Nozzle size D	Outside diameter	L ₁	L ₂ Note1)	L Note1)	Width across flats H1
VMG1-06-150-100	ø1.5		100	100	106	
VMG1-06-200-100	ø2					
VMG1-06-150-150	ø1.5		150	150	156]
VMG1-06-200-150	ø2	ø6	150	150	156	12
VMG1-06-150-300	ø1.5	96	300	300	306	12
VMG1-06-200-300	ø2		300	300	300]
VMG1-06-150-600	ø1.5		600	600	606	
VMG1-06-200-600	ø2		600			
VMG1-08-250-100	ø2.5		100	100	106	
VMG1-08-300-100	ø3					
VMG1-08-350-100	ø3.5					
VMG1-08-250-150	ø2.5					
VMG1-08-300-150	ø3		150	150	156	
VMG1-08-350-150	ø3.5	ø8				14
VMG1-08-250-300	ø2.5	00				14
VMG1-08-300-300	ø3		300	300	306	
VMG1-08-350-300	ø3.5]
VMG1-08-250-600	ø2.5					
VMG1-08-300-600	ø3		600	600	606	
VMG1-08-350-600	ø3.5					

Note 1) Reference dimensions after installation

Note 2) Copper extension nozzle and self-align fitting are included in the same package, (but unassembled). Refer to "How to attach extension nozzle" in the operation manual for assembly procedures.



^{*} Reference dimensions after R thread installation

^{*} Reference dimensions after R thread installation


^{*} Reference dimensions after R thread installation

Dimensios: Nozzle Cover


Cover for male thread nozzle



Nozzle cover part no.	Material	Applicable blow gun model			
Nozzie cover part no.	iviateriai	Model	Nozzle type		
P5670129-01	HNBR	VMG1□□-□-01 to 04	Male thread nozzle		
P5670129-01F	Fluororubber	VIVIG 1□□-□-01 to 04	ø1 to ø2.5		
P5670129-02	HNBR	VMG1□□-□-05 to 07	Male thread nozzle		
P5670129-02F	Fluororubber	VIVIG 100-0-05 to 07	ø3 to ø4		



VMG1□-□□-1 to 04



VMG1□-□□-05 to 07

Cover for copper extension nozzle





Namela announced as	Material	Applicable blow gun model		
Nozzle cover part no.	ivialeriai	Model	Nozzle type	
P5670129-11	HNBR	VMG1□□-□-31 to 38	ø6 copper	
P5670129-11F	Fluororubber	VMG1□□-□-31 t0 38	extension nozzle	



VMG1□-□□-31 to 38

VMG Series Made to Order

Please contact SMC for detailed dimensions, specifications, and delivery times.





1 With Flow Rate Adjustment Function

The flow rate can be easily adjusted according to the amount of force applied to the lever.



With nozzle cover/Fluororubber





Specifications


Flow rate characteristics (With nozzle removed)	C (dm³/s·bar):3.3 *1 (Effective area: 16.5 mm²)
Piping entry	Bottom
Operational force (when the valve is fully open)	9 N *2


CF

- *1) Though the value is smaller than that of the standard model, the flow rate characteristics when a nozzle is mounted are the same as those of the standard model.
- *2) The operational force is higher than that of the standard model for ease of flow adjustment with the lever.

Dimensions

* Reference dimensions after installation







VMG Series Specific Product Precautions 1

Be sure to read this before handling the products.

Selection

△Warning

1. Check the specifications.

The products in this catalog are designed to be used in compressed air systems only. If the products are used in an environment where pressure or temperature is out of the specified range, damage and/or malfunction may result. Do not use under such conditions.

∕ Caution

 Do not apply the blow gun to flammable, explosive or toxic substances such as gas, fuel gas or refrigerant. Such substances may exude from inside the blow gun.

Mounting

<u> ∧</u>Warning

- Install a stop valve on the supply pressure side of the blow gun to enable emergency shut off in case of unexpected leakage or damage.
- 2. When installing a nozzle on the blow gun, wrap pipe tape around the threads of the nozzle.
- 3. When installing the nozzle, secure the nozzle holder of the blow gun by applying a wrench of 22 mm width across flats to the two chamfered surfaces of the holder without applying force to the body. Then, tighten the nozzle with force within the torque range below. As a guideline, it is equivalent to 2 to 3 additional turns with a tool after manual tightening.



Nozzle tightening torque range 12 to 14 N·m

Insufficient tightening may cause loosening of the nozzle.

Piping

∧Caution

1. Check the model, type and size before installation.

Also, confirm that there is no scratches, gouges or cracks on the product.

2. Before piping

Before piping, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe.

Piping

∧ Caution

3. Winding of sealant tape

When screwing together pipes and fittings, etc., be certain that chips from the pipe threads and sealing material do not get inside the blow gun. Also, when the sealant tape is used, leave 1.5 to 2 thread ridges exposed at the end of the threads.



4. When tightening the threads, secure the nozzle holder of the blow gun by applying a wrench of 22 mm width across flats to the two chamfered surfaces of the holder without applying force to the body. Then, tighten the nozzle with torque specified in the table below. As a guideline, it is equivalent to 2 to 3 additional turns with a tool after manual tightening.

Be careful that tightening with torque beyond the ranges in the table below may cause damage to the body.



Male thread	Tightening torque N·m
R1/4	12 to 14
R3/8	22 to 24

- Allow extra length when connecting a tube to accommodate changes in tube length due to pressure.
- Confirm that no twisting, turning or tensile force or moment load is applied to the port or tube. This may cause fittings to fracture or tubes to be crushed, burst or come loose.
- Do not abrade, entangle or scratch the tube. This may cause the tube to be crushed, burst or come loose.

Lubrication

△Warning

1. Do not lubricate the product.

It may contaminate or damage the target object.

Air Supply

∧ Warning

1. Use clean air.

Do not use compressed air which includes chemicals, synthetic oils containing organic solvents, salt or corrosive gases, etc., as it can cause damage or malfunction.





VMG Series Specific Product Precautions 2

Be sure to read this before handling the products.

Air Supply

- 1. Install air filters.
 - Install air filters at the upstream side of blow gun. Choose the filtration degree of 5 μm or finer.
- 2. Install an after-cooler, air dryer or water droplet separator, etc.

Air excessive drainage may cause a malfunction of blow gun and contaminate or damage the target object. To prevent this, install an after-cooler, air dryer or water droplet separator, etc.

Operating Environment

- Do not use in an atmosphere of corrosive gases, chemicals, sea water, water or water vapor or in an environment where such substances may adhere.
- 2. Provide shading in an environment where the product is exposed to the sunlight.
- Do not use in an environment where a heat source is at a close distance.
- 4. Do not use in an environment where static electricity is a problem. It may cause malfunction or failure of the system. Please contact SMC for use in such an environment.
- Do not use in an environment where spatters are generated. There is danger of fires caused by spattering. Please contact SMC for use in such an environment.
- 6. Do not use in an environment where the product is exposed to cutting oil, lubricating oil or coolant oil. Please contact SMC for use in an environment where the product is exposed to such liquid as cutting oil, lubricating oil or coolant oil.

Maintenance

∧ Caution


- 1. In periodical inspections, check the following items and replace the parts if necessary.
 - a) Scratches, gouges, abrasion, corrosion
 - b) Air leakage
 - c) Twisting, crushing and turning of connected tubes
 - d) Hardening, deterioration and softening of connected tubes
 - e) Loosening of nozzles
- When removing the product, first stop the pressure supply, exhaust compressed air in the piping and check the condition of atmospheric release.
- Do not disassemble or remodel the body of the product.

Handling

⚠ Warning

- To prevent lurching of the nozzle due to air pressure, confirm that the nozzle is not loosened or rattling by pulling it by hand before operation.
- 2. Make sure to wear safety goggles to protect yourself from splashed substances.
- Do not direct the tip of the nozzle at the face or other parts of a human body. It may cause danger to personnel.
- Do not use the product to clean or remove toxic substances or chemicals.
- Do not drop, step on or hit the product. It may cause damage to the product.
- Do not use the product to disturb public order or public hygiene.
- 7. This product is not a toy.
- After blowing, make sure to hang the product on a hook, etc.

If leaving the product in a dusty place, particles will enter the product and may result in a malfunction.



- When the blow gun is used or stored, confirm that no twisting, turning or tensile force or moment load is applied to the port or tube. This may cause fittings to fracture or tubes to be crushed, burst or come loose.
- 10. When attaching a nozzle cover, align the hex parts of the nozzle and nozzle cover before covering. When attaching an extension nozzle cover, confirm that the nozzle tip is completely inserted into the extension nozzle cover.
- 11. Do not use a nozzle cover or extension nozzle cover if it is cracked or does not fit securely, and replace with a new cover.