
³ Port Air Operated Valve VPA3145/3165/3185 Series

How to Order







VPA3165-06


VPA3145-03

<Vacuum pressure>

Symbol <Positive pressure>



Pilot Pressure Range



Specifications

Fluid	Air				
Type of actuation	N.C. only (N.O. only for vacuum)				
Operating pressure range	For vacuum and low pressure	For ordinary pressure			
operating pressure range	-101.2 kPa to 0.2 MPa	0.2 to 0.8 MPa			
Pilot pressure range	Refer to the graph of pilot pressure.				
Ambient and fluid temperature (°C)	0 (No freezing) to 60				
Lubrication	Required (Turbine oil, Class 1 ISO VG32 equivalent)				
Mounting orientation	Fre	Free			
Impact/Vibration resistance (m/s ²) Note)	150/50				

Impact/Vibration resistance (m/s²)^{Note}

Note) Impact resistance: No malfunction from test using drop impact tester, to axis and right angle directions of main valve, each one time when pilot signal ON and OFF. (Value in the initial stage)

Vibration resistance: No malfunction from test with 45 to 1000 Hz one sweep, to axis and right angle direction of main valve, each one time when pilot signal ON and OFF. (Value in the initial stage)

▲ Precautions

Be sure to read this before I handling the products. Refer to page 8 for safety instructions and pages 9 to 15 for 3/4/5 port solenoid valve precautions.

A Caution

1. Lubrication

- Since this valve needs lubrication, use turbine oil Class 1 (ISO VG32).
- Refer to pages 1117 and 1124 for information about the pressure applied to piping and ports, quality of air and piping for vacuum applications.


VPA31 5 Series

Flow Rate Characteristics/Weight

	Port size		Flow rate characteristics							
Valve model		size	1→2(IN→OUT)			2→3(OUT→EXH)			Weight (kg)	
	1(IN), 2(OUT)	3(EXH)	C[dm ³ /(s·bar)]	b	Cv	C[dm3/(s·bar)]	b	Cv		
	3/8		19	0.43	5.5	18	0.47	5.4		
VPA3145	1/2	3/4	23	0.32	6.2	21	0.39	5.8	1.0	
	3⁄4		28	0.36	7.6	26	0.35	7.0		

Valve model	Port	size	Effective a	Weight (kg)		
	1(IN), 2(OUT)	3(EXH)	1→2(IN→OUT)	2→3(OUT→EXH)		
	3/4		230	280		
VPA3165	1	11/4	11/4 280 3		1.5	
	11/4		310	330		
	11/4		570	650		
VPA3185	11/2	2	650	670	2.3	
	2		650	670		

Dimensions



Model	Port s IN, OUT	ize Rc EXH	A	в	с	D	Е	F	G	н	J	к	L	Mounting hole
VPA3145	3/8 1/2 3/4	3⁄4	71	85	14	52	55	93	32	87.4	36	71	80	Ø8.5
VPA3165	3/4 1 1 ¹ /4	1 1⁄4	82.6	110	17	68	75	118	45	113	36	71	95	Ø8.5
VPA3185	11/4 11/2 2	2	118	132	14	80	95	140	52	140	41	81	105	ø13