# **One-touch Fittings Manifold** KM Series



Compact piping possible. Manifold piping possible. Many varieties (40 types) are available.

One-touch fittings give the most efficient operation.






#### Model

| Model    | Por               | ting              | No. of | Port B     | F  | ort A siz | ze e |
|----------|-------------------|-------------------|--------|------------|--|-----------|------|
| wodei    | Port A            | Port B            | Port A | size       | ø4   | ø6        | ø8   |
|          |                   |                   |        | ø8         | •  |           |      |
| KM11     | One-touch fitting | One-touch fitting | 6, 10  | ø10        |  | •         |      |
|          |                   |                   |        | ø12        |  |           | •    |
| KM12     | One-touch fitting | Rc female thread  | 6, 10  | Rc 1/4     | •  | •         |      |
| IXIVI 12 | One todor litting | Tio fornaio unoda | 0, 10  | Rc 3/8     |  |           | •    |
|          |                   |                   |        | ø6         | •  |           |      |
| KM13     | One-touch fitting | One-touch fitting | 3      | ø8         | •  | •         |      |
|          |                   |                   |        | ø10        |  | •         | •    |
|          |                   |                   |        | ø6, R 1/8  | •  |           |      |
|          |                   |                   |        | ø6, R 1/4  | •  |           |      |
|          |                   |                   |        | ø6, R 3/8  |  |           |      |
|          |                   | One-touch fitting |        | ø8, R 1/8  | •  | •         |      |
| KM14     | One-touch fitting | R male thread     | 3      | ø8, R 1/4  | •  | •         |      |
|          |                   |                   |        | ø8, R 3/8  | •  | •         |      |
|          |                   |                   |        | ø10, R 1/4 |  | •         | •    |
|          |                   |                   |        | ø10, R 3/8 |  | •         | •    |
|          |                   |                   |        | ø10, R 1/2 |  | •         | •    |
|          |                   | One-touch fitting |        | ø6         | •  |           |      |
| KM15     | One-touch fitting | Rod               | 3      | 8 size     | •  |           |      |
|          |                   | Hod               |        | ø10        |  | •         | •    |
| KM16     | One-touch fitting | One-touch fitting | 3      | ø4         | Rc 3/6  ø6  ø8  ø10  ø6, R 1/4  ø6, R 3/4  ø7, R 3/4  ø |           |      |
| IXIVI TO | One todal litting | One todor inting  | ١      | ø6         |  |           |      |

**Applicable Tubing** 



# Made to Order (Refer to page 287 for details.)

# Specifications

| Specifications                |      |   |                      |                                      |      |      |
|-------------------------------|------|---|----------------------|--------------------------------------|------|------|
| Model                         | KM11 | KM12  | KM13                 | KM14                                 | KM15 | KM16 |
| Fluid                         |      |   | Air/Wa               | ter (1, 2)                           |      |      |
| Operating pressure range      |      |   | -100 kPa             | to 1 MPa                             |      |      |
| Proof pressure                |      |   | 3 N                  | 1Pa                                  |      |      |
| Ambient and fluid temperature |      |   | -5 to 60°C, Water: 0 | to 40°C (No freezing)                |      |      |
| Thread                        | _    | JIS B 0203 (Taper thread for piping)            | _                    | JIS B 0203 (Taper thread for piping) | _    | _    |
| Accessory                     | None | Hexagon socket head blank plug with seal: 1 pc. | None                 | None                                 | None | None |

Note 1) The surge pressure must be under the maximum operating pressure.

Note 2) Deionized water is not recommended for use as it may affect the material used in the fittings. In addition, it is known to degrade the water quality.


#### **Principal Parts Material**

| Model                  | KM11 | KM12  | KM13      | KM14      | KM15      | KM16 |
|------------------------|------|-------|-----------|-----------|-----------|------|
| Body                   |      |       | PI        | BT .      |           |      |
| Stud                   | _    | C3604 | _         | C3604     | C3604-PBT | _    |
| Chuck                  |      |       | Stainless | steel 304 |           |      |
| Guide                  |      |       | Stainless | steel 304 |           |      |
| Collet, Release button |      |       | PC        | OM        |           |      |
| Seal, O-ring           |      |       | N         | 3R        |           |      |



# Construction


## **KM11**



Port A: One-touch fitting Port B: One-touch fitting


# Port B: One-touch lit

# **KM13**




Port A: One-touch fitting Port B: One-touch fitting


## **KM15**



## **KM12**




## KM14



Port A: One-touch fitting Port B: One-touch fitting, R male thread


#### **KM16**



Port A: One-touch fitting Port B: One-touch fitting


# **Dimensions**

## KM11




| Applicable tub | oing O.D. (mm) | Model         | N  | L1  | L2   | L3   | L4       | L5      | L6     | Р        | Q1   | Q2   | МА   | МВ   | Port B         | Weight |    |
|----------------|----------------|---------------|----|-----|------|------|----------|---------|--------|----------|------|------|------|------|----------------|--------|----|
| FA             | FB             | Wodei         | IN | L . | LZ   | L3   | L4       | Lo      | LO     | P        | 3    | Q2   | IVIA | IVID | Min. port size | (g)    |    |
| 4              |                | KM11-04-08-6  | 6  | 65  | 10   | 18   | 29.5     | 19.5    | 27     | 10.6     | 40   | 12   | 16   | 18.5 |                | 19     |    |
| 4              | 4 8            | KM11-04-08-10 | 10 | 86  | 10   | 10   | 29.5     | 19.5    | 21     | 10.6     | 61.5 | 12   | 16   | 10.5 | 0              | 26     |    |
|                | 6 10           | KM11-06-10-6  | 6  | 76  | 10   | 10 F | 01.5     | 01.5    | 0.1    | 10       | 47   | 13.5 | 17   | 21   | 7.5            | 29     |    |
| 0              | 6 10           | KM11-06-10-10 | 10 | 102 | 10   | 19.5 | 9.5 31.5 | 21.5    | 1.5 31 | 31 13    | 73   | 13.5 | ''   | 21   | 7.5            | 39     |    |
| 8 1            | 12             | KM11-08-12-6  | 6  | 85  | 11.5 | 22.5 | 35.5     | 24 34.5 | 34.5   | 4.5 15.5 | 55   | 55   | 14.7 | 18.5 | 22             |        | 41 |
|                | 12             | KM11-08-12-10 | 10 | 116 | 11.5 | 22.5 | 35.5     | 24      | 34.5   | 15.5     | 86   | 14.7 | 10.5 | 22   | 9              | 57     |    |

**KM12** 



| Applicable tubing O.D. F (mm) | Connection<br>thread Rc<br>T | Model         | N  | (Width across<br>flats) | L1  | L2   | L3   | L4   | L5   | L6   | Р    | Q1   | Q2   | М    | Port B<br>Min. port size | Weight (g) |
|-------------------------------|------------------------------|---------------|----|-------------------------|-----|------|------|------|------|------|------|------|------|------|--------------------------|------------|
| 4                             | 1/4                          | KM12-04-02-6  | 6  | 17                      | 89  | 10   | 18   | 29.5 | 19.5 | 20   | 10.6 | 40   | 12   | 16   | 6                        | 65         |
| 4                             | 74                           | KM12-04-02-10 | 10 | 17                      | 110 | 10   | 10   | 29.5 | 19.5 | 29   | 10.6 | 61.5 | 12   | 10   | 0                        | 72         |
| 6                             | 1/4                          | KM12-06-02-6  | 6  | 17                      | 99  | 10   | 10.5 | 31.5 | 21 5 | 01   | 13   | 47   | 13.5 | 17   | 7.5                      | 81         |
|                               | 74                           | KM12-06-02-10 | 10 | 17                      | 125 | 10   | 19.5 | 31.3 | 21.5 | 5    | 13   | 73   | 15.5 | 17   | 7.5                      | 91         |
| Q                             | 3/8                          | KM12-08-03-6  | 6  | 19                      | 108 | 11.5 | 22.5 | 35.5 | 24   | 34.5 | 15.5 | 55   | 14.7 | 18.5 | ۵                        | 97         |
|                               | -/8                          | KM12-08-03-10 | 10 | 19                      | 139 | 11.5 | 22.5 | 33.5 | ~ 4  | 34.5 | 13.5 | 86   | 14.7 | 10.5 | "                        | 112        |

**KM13** 



| Applicable tub | oing O.D. (mm) | Model        | øD1  | øD2  | L1   | L2   | L3   | Р    | Q1   | Q2   | M1    | M2   | Port B         | Weight |
|----------------|----------------|--------------|------|------|------|------|------|------|------|------|-------|------|----------------|--------|
| (a)            | Ф              | Model        | וטט  | ØD2  | LI   | L2   | L3   | Р    | Q    | Q2   | IVI I | IVIZ | Min. port size | (g)    |
| 4              | 6              | KM13-04-06-3 | 10.4 | 12.8 | 60   | 18   | 13   | 10.4 | 38.2 | 9.9  | 17    | 16   | 4.5            | 11     |
| 4              | 8              | KM13-04-08-3 | 10.4 | 15.2 | 63.5 | 19   | 15.5 | 10.4 | 36.2 | 11.1 | 18.5  | 10   | 6              | 14     |
| 6              | 8              | KM13-06-08-3 | 12.8 | 15.2 | 70.5 | 20   | 15.5 | 12.8 | 45.4 | 11.1 | 18.5  | 17   | 6              | 16     |
| •              | 10             | KM13-06-10-3 | 12.0 | 18.5 | 74.5 | 21   | 19   | 12.0 | 45.4 | 12.8 | 21    | 17   | 7.5            | 22     |
| 8              | 10             | KM13-08-10-3 | 15.2 | 18.5 | 81.5 | 22.5 | 19   | 15.2 | 52.6 | 12.8 | 21    | 18.5 | 7.5            | 26     |


Click here for applicable color caps.



#### **Dimensions**

# **KM14**






| Applicable tub | oing O.D. (mm) | Connection<br>thread | Model            | H<br>(Width across flats) | ø <b>D</b> 1 | ø <b>D2</b> | L1   | L2   | L3   | Р    | Α    | Q1   | Q2   | M1   | M2   | Port B<br>Min. port size | Weight (g) |
|----------------|----------------|----------------------|------------------|---------------------------|--------------|-------------|------|------|------|------|------|------|------|------|------|--------------------------|------------|
| a              | U)             | 1/8                  | KM14-04-06-01S-3 | 13                        |              |             | 67.1 |      |      |      | 64   |      |      |      |      | Willi. port size         | 18         |
| 4              | 6              | 1/4                  | KM14-04-06-02S-3 | 14                        | 10.4         | 12.8        | 71   | 18   | 13   | 10.4 | 65.5 | 38.2 | 9.9  | 17   | 16   | 4.5                      | 25         |
|                |                | 3/8                  | KM14-04-06-03S-3 | 17                        |              |             | 72.4 |      |      |      | 67.5 |      |      |      |      |                          | 38         |
|                |                | 1/8                  | KM14-04-08-01S-3 |                           |              |             | 72.6 |      |      |      | 69.5 |      |      |      |      |                          | 30         |
| 4              | 8              | 1/4                  | KM14-04-08-02S-3 | 17                        | 10.4         | 15.2        | 76   | 19   | 15.5 | 10.4 | 70.5 | 38.2 | 11.1 | 18.5 | 16   | 6                        | 30         |
|                |                | 3/8                  | KM14-04-08-03S-3 | ]                         |              |             | 76.4 | ]    |      |      | 71   |      |      |      |      |                          | 38         |
|                |                | 1/8                  | KM14-06-08-01S-3 |                           |              |             | 79.1 |      |      |      | 76.5 |      |      |      |      |                          | 31         |
| 6              | 8              | 1/4                  | KM14-06-08-02S-3 | 17                        | 12.8         | 15.2        | 82.5 | 20   | 15.5 | 12.8 | 77   | 45.4 | 11.1 | 18.5 | 17   | 6                        | 31         |
|                |                | 3/8                  | KM14-06-08-03S-3 | ]                         |              |             | 82.9 | ]    |      |      | 78   |      |      |      |      |                          | 39         |
|                |                | 1/4                  | KM14-06-10-02S-3 | 19                        |              |             | 87   |      |      |      | 81.5 |      |      |      |      |                          | 43         |
| 6              | 10             | 3/8                  | KM14-06-10-03S-3 | ] 19                      | 12.8         | 18.5        | 87.4 | 21   | 19   | 12.8 | 82   | 45.4 | 12.8 | 21   | 17   | 7.5                      | 44         |
|                |                | 1/2                  | KM14-06-10-04S-3 | 22                        | ]            |             | 91.1 |      |      |      | 84   |      |      |      |      |                          | 66         |
|                |                | 1/4                  | KM14-08-10-02S-3 | 19                        |              |             | 93.5 |      |      |      | 88   |      |      |      |      |                          | 47         |
| 8              | 10             | 3/8                  | KM14-08-10-03S-3 | ] 19                      | 15.2         | 18.5        | 93.9 | 22.5 | 19   | 15.2 | 89   | 52.6 | 12.8 | 21   | 18.5 | 7.5                      | 4/         |
|                |                | 1/2                  | KM14-08-10-04S-3 | 22                        |              |             | 97.6 |      |      |      | 90.5 |      |      |      |      |                          | 70         |

#### **KM15**






|   | Applio<br>tub<br>O.D. | cable<br>ing<br>(mm) | Applicable fitting size ød | Model        | ø <b>D</b> 1 | ø <b>D2</b> | L1   | L2   | L3   | Р    | Q1   | Q2   | A    | МА   | МВ   | Port B<br>min.<br>port size | Weight<br>(g) |
|---|-----------------------|----------------------|----------------------------|--------------|--------------|-------------|------|------|------|------|------|------|------|------|------|-----------------------------|---------------|
| ı | 4                     | 6                    | 6                          | KM15-04-06-3 | 10.4         | 12.8        | 78.5 | 18   | 13   | 10.4 | 38.2 | 9.9  | 61.5 | 16   | 17   | 4.5                         | 12            |
|   | 4                     | 8                    | 8                          | KM15-04-08-3 | 10.4         | 15.2        | 85.5 | 19   | 15.5 | 10.4 | 30.2 | 11.1 | 67   | 16   | 18.5 | 6                           | 24            |
| Ī | 6                     | 8                    | 8                          | KM15-06-08-3 | 12.8         | 15.2        | 92.5 | 20   | 15.5 | 12.8 | 45.4 | 11.1 | 74   | 17   | 18.5 | 6                           | 25            |
|   | 0                     | 10                   | 10                         | KM15-06-10-3 | 12.0         | 18.5        | 98   | 21   | 19   | 12.0 | 45.4 | 12.8 | 77   | ' '  | 21   | 7.5                         | 37            |
| Ī | 8                     | 10                   | 10                         | KM15-08-10-3 | 15.2         | 18.5        | 105  | 22.5 | 19   | 15.2 | 52.6 | 12.8 | 85   | 18.5 | 21   | 7.5                         | 41            |

# KM16





| Applicable tub | ing O.D. (mm) | Model        | ~D4  | øD2  |    | L2   |    |    | ь    | <b>~</b> 1 | Q2   | 844  | 840  |                | Weight |
|----------------|---------------|--------------|------|------|----|------|----|----|------|------------|------|------|------|----------------|--------|
| (a)            | (b)           | iviodei      | וטטו | 002  | LI | [2   | Lo | L4 |      | Q1         | Q2   | IVII | IVIZ | Min. port size | (g)    |
| 4              | 4             | KM16-04-04-3 |      |      |    |      |    |    |      |            |      | 16   | 16   | 3              | 18     |
| 4              | 6             | KM16-04-06-3 | 12.8 | 12.8 | 68 | 20.9 | 16 | 11 | 14.5 | 50         | 10.5 | 17   | 16   | 4.5            | 16     |
| 6              | 6             | KM16-06-06-3 | ]    |      |    |      |    |    |      |            |      | 17   | 17   | 4.5            | 15     |
|                |               |              |      |      |    |      |    |    |      |            |      |      |      |                |        |

#### Click here for applicable color caps.

# **Handling of One-touch Fittings**

# **⚠** Caution

- Refer to pages 14 to 18 for "Fittings & Tubing Precautions" for the details of installation/ removal of One-touch fittings.
- 2. Connecting products with metal rods Products with metal rods cannot be connected to KQ2 series One-touch fittings. If connected, the metal rod cannot be retained by the chuck of the One-touch fitting and products with metal rods may project during pressurization, causing serious personal injury or accident.

When mounting tubes, resin plugs, reducers etc., do not press the release button. Also, do not press the release button unnecessarily before mounting them. This may cause those parts to come off.

After attaching products with attached metal rods, to the One-touch fitting, do not use tubes, resin plugs, or reducers, etc. This may cause releasing.

For details about One-touch fittings that can connect KM15 model, contact SMC.

# Made to Order Specifications Please contact SMC for detailed dimensions, specifications and lead times.



# 1 Grease-free Specifications

| Symbol | Specifications   |
|--------|--|
| X17    | Grease-free Rubber material: NBR (With fluorine coating) Release button color: Light blue  |
| X29    | Grease-free Rubber material: NBR (With fluorine coating) Release button color: Light blue Copper-free (With electroless nickel plated) |
| X94    | Grease-free<br>Rubber material: FKM (With fluorine coating)<br>Release button color: Light blue  |

Suffix "-X17" to the end of part number. Example) KM11-04-08-10-X17

# 2 Other Specifications

| Symbol | Specifications   |
|--------|--|
| X2     | Copper-free (With electroless nickel plated)             |
| X12    | Lubricant: White Vaseline<br>Release button color: White |
| X34    | Rubber material: FKM                                     |

Suffix "-X2" to the end of part number. Example) **KM12-04-02-6-X2** 

# Inch size One-touch Fittings Manifold **KM Series**

**Applicable Tubing: Inch size** 

Compact piping possible. Manifold piping possible. Many varieties (12 types) are available. One-touch fittings give the most efficient operation.



#### Model

| Model | Por               | ting              | No. of | Port B  | Р      | ort A siz | ze     |
|-------|-------------------|-------------------|--------|---------|--------|-----------|--------|
| Model | Port A            | Port B            | Port A | size    | ø5/32" | ø 1/4"    | ø5/16" |
|       |                   |                   |        | ø 5/16" | •      |           |        |
| KM11  | One-touch fitting | One-touch fitting | 6, 10  | ø3/8"   |        | •         |        |
|       |                   |                   |        | ø 1/2"  |        |           | •      |
| KM12  | One-touch fitting | NPT thread        | 6, 10  | NPT 1/4 | •      | •         |        |
| KWIIZ | One-touch litting | INFT tilleau      | 0, 10  | NPT 3/8 |        |           | •      |

# **Applicable Tubing**

| Tubing material | FEP, PFA, Nylon, Soft nylon, Polyurethane |
|-----------------|---|
| Tubing O.D.     | ø5/32', ø1/4", ø5/16', ø3/8", ø1/2"       |

## **Specifications**

| Model                         | KM11                                       | KM12                |  |  |  |  |
|-------------------------------|--|---------------------|--|--|--|--|
| Fluid                         | Air/Water (2, 3)                           |                     |  |  |  |  |
| Maximum operating pressure    | re 1 MPa                                   |                     |  |  |  |  |
| Proof pressure                | 3 MPa                                      |                     |  |  |  |  |
| Ambient and fluid temperature | -5 to 60°C, Water: 0 to 40°C (No freezing) |                     |  |  |  |  |
| Thread                        |  | ANSI/ASMEB1.20.     |  |  |  |  |
| Triread                       | _  | 1-1983 (NPT thread) |  |  |  |  |

Note 1) The surge pressure must be under the maximum operating pressure.


Note 2) Deionized water is not recommended for use as it may affect the material used in the fittings. In addition, it is known to degrade the water quality.




## **Principal Parts Material**

| Model                  | KM11                       | KM12  |  |  |  |
|------------------------|----------------------------|-------|--|--|--|
| Body                   | PE                         | BT .  |  |  |  |
| Stud                   | _                          | C3604 |  |  |  |
| Chuck                  | Stainless steel 304        |       |  |  |  |
| Guide                  | Stainless steel 304, C3604 |       |  |  |  |
| Collet, Release button | POM                        |       |  |  |  |
| Seal, O-ring           | NBR                        |       |  |  |  |

## Construction




Port A: One-touch fitting Port B: One-touch fitting




# **Dimensions**

# KM11



| Applicable tub | ing O.D. (inch) | Model         | N  | 1.1       | L2        | L3        | L4   | L5   | L6   | Р    | Q1   | Q2 | МА   | МВ   |                | Weight |
|----------------|-----------------|---------------|----|-----------|-----------|-----------|------|------|------|------|------|----|------|------|----------------|--------|
| FA             | FB              | Model         | IN |           |           | LJ        | L4   | [3   |      | -    | Q I  | QZ | IVIA | IVID | Min. port size | (g)    |
| 5/32           | 5/16            | KM11-03-09-6  | 6  | 65        | 10        | 18        | 29.5 | 19.5 | 27   | 10.6 | 40   | 12 | 16   | 18.5 | 6              | 19     |
| 9/32           | 9/16            | KM11-03-09-10 | 10 | 86        | 10        | 10        | 29.5 | 19.5 | 21   | 10.6 | 61.5 | 12 | 16   | 10.5 | U              | 26     |
| 1/4            | 9/              | KM11-07-11-6  | 6  | 77.8      | 10        | 10.5      | 31.5 | 21.5 | 20.5 | 13.2 | 48   | 13 | 17   | 21   | _              | 30     |
| - 1/4          | 3/8             | KM11-07-11-10 | 10 | 10 104 10 | 10   19.5 | 31.5      | 21.5 | 30.5 | 13.2 | 73.5 | 13   | 17 | 21   | '    | 40             |        |
| E/             | 1/              | KM11-09-13-6  | 6  | 85        | 12.7      | 23.7      | 37.7 | 25   | 35.9 | 15.2 | 52.8 | 15 | 18.5 | 22   | 9.5            | 41     |
| 5/16 1/        | 1/2             | KM11-09-13-10 | 10 | 115       | 12.7      | 12.7 23.7 | 31.1 | 25   | 33.9 | 13.2 | 83   | 15 | 10.5 | 22   | 9.5            | 57     |

## KM12



| Applicable tubing O.D. F (inch) | Connection<br>thread<br>NPT | Model         | N  | H<br>(Width across flats) | L1  | L2     | L3   | L4       | L5   | L6      | Р    | Q1         | Q2 | м    | Port B<br>Min. port size | Weight (g) |
|---------------------------------|-----------------------------|---------------|----|---------------------------|-----|--------|------|----------|------|---------|------|------------|----|------|--------------------------|------------|
| 5/32                            | 1/4                         | KM12-03-35-6  | 6  | 17.46                     | 87  | 10     | 18   | 29.5     | 19.5 | 29      | 10.6 | 40         | 12 | 16   | 6                        | 65         |
| 9/32                            | 74                          | KM12-03-35-10 | 10 |                           | 110 |        |      |          |      |         |      | 61.5       | 12 |      |                          | 72         |
| 1/4                             | 1/4                         | KM12-07-35-6  | 6  | 17.46                     | 95  |        | 19.5 | 31.5     | 21.5 | 31.25   | 13.2 | 48<br>73.5 | 10 | 17   | 7                        | 82         |
| 1/4                             |                             | KM12-07-35-10 | 10 |                           | 121 |        |      |          |      |         |      |            | 13 | ''   |                          | 92         |
| 5/16                            | 3/8                         | KM12-09-36-6  | 6  | 22.22                     | 102 | 12.7   | 23.7 | 3.7 36.8 | 24   | 24 36.5 | 15.2 | 52.8       | 15 | 18.5 | 9.5                      | 97         |
|                                 |                             | KM12-09-36-10 | 10 |                           | 132 | 2 12.7 |      |          | 24   |         |      | 83         | 15 |      |                          | 112        |

Click here for applicable color caps.

# Handling of One-touch Fittings

# **⚠** Caution

Refer to pages 14 to 18 for "Fittings & Tubing Precautions" for the details of installation/removal of One-touch fittings.



# Made to Order Specifications Please contact SMC for detailed dimensions, specifications and lead times.



# 1 Grease-free Specifications

| Symbol | Specifications   |
|--------|--|
| X17    | Grease-free Rubber material: NBR (With fluorine coating) Release button color: Light blue  |
| X29    | Grease-free Rubber material: NBR (With fluorine coating) Release button color: Light blue Copper-free (With electroless nickel plated) |
| X94    | Grease-free<br>Rubber material: FKM (With fluorine coating)<br>Release button color: Light blue  |

Suffix "-X17" to the end of part number.

Example) KM11-03-09-10-X17

# 2 Other Specifications

| Symbol | Specifications   |  |  |  |  |  |
|--------|--|--|--|--|--|--|
| X2     | Copper-free (With electroless nickel plated)             |  |  |  |  |  |
| X12    | Lubricant: White Vaseline<br>Release button color: White |  |  |  |  |  |
| X34    | Rubber material: FKM                                     |  |  |  |  |  |

Suffix "-X2" to the end of part number.

Exampe) KM12-03-35-6-X2