
# Polyurethane Coil Tubing TCU Series



## For flexible tubing Compact piping possible

#### Max. Operating Pressure



### **⚠** Precautions

Be sure to read this before handling the products.
Refer to back page 50 for Safety Instructions
and pages 13 to 17 for Fittings and Tubing
Precautions.


#### **∧** Caution

- Please consult with SMC regarding use with any fluids other than air.
- Abnormal temperature rise caused by adiabatic compression may result in the tube bursting.
- Please do not cut the coil and insert it into the fitting. This may cause air leakage, or tubing to come out after installation.
- Very slight leakage may occur in the multi-core tubing due to its characteristics.

#### Model/Specifications

Model		TCU 0425B-1					TCU 0604B-3	TCU 0805B-1				
Number of cores		1 core	2 cores	3 cores	1 core	2 cores	3 cores	1 core				
Tubing O.D. (mm)			4			8						
Tubing I.D. (mm)			2.5			5						
Fluid		Air										
Max. operating	20°C	0.8										
pressure (MPa)	40°C	0.65										
pressure (iiii u)	60°C	0.5										
Applicable fittings		One-touch fittings, Insert fittings, Self-align fittings, Miniature fittings										
Operating tempera	−20 to +60°C											
Material		Polyurethane										
Color		Black (Opaque)										

#### **Dimensions**




	Specifications	Tubing s	ize (mm)	Coil	(mm)	No. of	No. of coil windings	Max. operating	Standard unit
Model		O.D.	I.D.	L	øD	cores	per tube length	length (m)	of packing
TCU	0425B-1			210	18	1	52 ± 2	1.5	5 tubes/case
TCU	0425B-2	4	2.5	280	28	2	35 ± 1	1.5	
TCU	0425B-3			265	20	3	22 ± 1	1	
TCU	0604B-1		4	325	24	1	54 ± 2	2	
TCU	0604B-2	6		323	37	2	27 ± 1	1.5	
TCU	0604B-3			305	37	3	17 ± 1	1	
TCU	0805B-1	8	5 330		31	1	41 ± 2	2	]

<sup>\*</sup> The number of coil windings per tube length and dimensions are changeable due to material.

#### Made to Order

#### Change of coil turns, Change of color

(Please contact SMC for specifications in detail, dimensions and delivery.)



Specifications Tubing size (mm)		Coil	(mm)	No. of	No. of coil windings per	Max. operating	Specifications	Tubing size (mm)		Coil (mm)		No. of	No. of coil	Max. operating		
Model		O.D.	I.D.	L	øD	cores	tube length (N)	length (mm)	Model	O.D.	I.D.	L	øD	cores	windings per tube length (N)	length (mm)
TCU0425	□-1-N-X6		2.5	N x 4	18	1	3 to 90	L x 5.9 + 200	TCU0805 □-1-N-X6	8	5	N x 8	31	1	3 to 90	L x 5.2 + 200
TCU0425	□-2-N-X6	4		N x 8	28	2	3 to 90	L x 4.4 + 200	TCU0805 □-2-N-X6	l °		N x 16	42	2	3 to 40	L x 3 + 200
TCU0425	□-3-N-X6			N x 12	28	3	3 to 63	L x 2.9 + 200	TCU1065 □-1-N-X6	10	6.5	N x 10	52	1	3 to 45	L x 5 + 200
TCU0604	□-1-N-X6			Nx6	24	1	3 to 90	L x 5.3 + 200	TCU1065 □-2-N-X6	] ''	6.5	N x 20	52	2	3 to 35	L x 3 + 200
TCU0604	□-2-N-X6	6	6 4	N x 12	37	2	3 to 66	L x 3.8 + 200	TCU1208 -1-N-X6	12	8	N x 12	67	1	3 to 35	L x 5 + 200
TCU0604	□-3-N-X6			N x 18	37	3	3 to 44	L x 2.5 + 200	TCU1208 □-2-N-X6	12		N x 24	67	2	3 to 30	L x 3 + 200

<sup>\*</sup> D: B (Black), W (White), R (Red), BU (Blue), Y (Yellow), G (Green), C (Clear), YR (Orange)

**SMC** 

KQ2

KQB2

KM

KF

H/DL L/LL

KC

KK

KK130

DM

KDM

KB

KR

KA KQG2

KG

KFG2

MS

KKA

KP LO

MQR

MQR

IDK