Rubber Seal 3-Port/Poppet Type VT315 Series

Compact with a large flow capacity

Dimensions (W x H x D)…45 x 95 x 45 (Grommet)

C: 1.7 dm³/(s·bar) (Passage $2 \rightarrow 3$)

A single valve with 6 valve functions (Universal porting type)


6 valve functions can be selected according to the selected piping ports. (Enabling of the N.C. valve, N.O. valve, divider valve, selector valve, etc.)


Suitable for use in vacuum applications -101.2 kPa

(Vacuum specification type: VT/VO315V)









please contact SMC.

Specifications	
Type of actuation	Direct operated type 2-position single solenoid
Fluid	Air
Operating pressure range	0 to 1.0 MPa
Ambient and fluid temperatures	-5 to 60°C (No freezing. Refer to "Best Pneumatics No.1.")
Max. operating frequency	10 Hz
Response time*1	30 ms or less (at 0.5 MPa)
Lubrication	Not required (Use turbine oil Class 1 ISO VG32 if lubricating.)
Manual override	Non-locking push type
Impact/Vibration resistance*2	150/50 m/s ²
Enclosure	Dustproof

Without connector



Based on JIS B 8374: 1981 dynamic performance test (Coil temperature 20°C, at rated voltage, without surge voltage suppressor)

*2 Impact resistance : No malfunction occurred when tested with a drop tester in the axial direction and at right angles to the main valve and the armature in both an energized and de-energized state, once in each condition. (Value in the initial state)

27-2

Vibration resistance : No malfunction occurred in a one-sweep test between 45 and 2000 Hz in the axial direction and at right angles to the main valve and the armature in both an energized and de-energized state, once in each condition. (Value in the initial state)

Solenoid Specifications

Electrical entry	Electrical entry			Grommet, Conduit, DIN terminal, Conduit terminal			
Coil rated voltage	Coil rated voltage			, 200 VAC, 50/60 Hz, 24 VDC			
Allowable voltage fluctuat	Allowable voltage fluctuation			to +10% of the rated voltage			
	AC	Inrush	50 Hz	36 VA			
Apparent power*3		mrusn	60 Hz	28 VA			
Apparent powerse	AC	Holding	50 Hz	20 VA			
		потатту	60 Hz	16 VA			
Power consumption*3	DC		6 to 7 W				

*3 At the rated voltage



VT315 Series

Flow Rate Characteristics/Weight

	Flow rate characteristics								Waight				
Valve model	1 →	$2 (P \rightarrow I)$	A)	2 →	3 (A \rightarrow	R)	3 →	2 (R \rightarrow)	A)	2 →	1 (A \rightarrow	P)	Weight
	C [dm3/(s·bar)]	b	Cv	C [dm³/(s·bar)]	b	Cv	C [dm3/(s·bar)]	b	Cv	C [dm3/(s·bar)]	b	Cv	Grommet
VT315													0.38 kg
VT315V (Vacuum spec. type)	1.6	0.30	0.39	1.7	0.39	0.45	1.9	0.38	0.49	1.7	0.36	0.45	0.39 kg (For AC)
VT315E (Continuous-duty type)													0.38 kg (For DC)

* These are the values for a single valve unit. They are not applicable to manifolds. Refer to the manifold specifications on page 12 for details.

Valve Options

1. Continuous-duty type

Recommended for continuous operation for long periods of time

▲ Caution

- 1) This model is for continuous duty, not for high frequency cycles. But even for low frequency
- cycles, if energizing the valve more than once a day, please contact SMC.
- 2) The solenoid should be energized at least once every 30 days.

2. For vacuum


Pressure range -101.2 kPa to 0.1 MPa

This vacuum model has less air leakage than the standard model under low pressure. It is recommended for vacuum applications.

ACaution

1) Since this valve has slight air leakage, it cannot be used for vacuum retention (including positive pressure retention) in the pressure container.

3. With surge voltage suppressor, with indicator light



Circuit for Indicator Light								
	AC	DC						
DIN terminal with indicator light (DL)	Neon & Book	Varistor						
Conduit terminal with indicator light (TL)	° Neon bulb °	Coil						

Coil rated AC 100, 110, 200, 220 VAC (50/60 Hz) voltage DC 12, 24 VDC

Holding: 18 VA (50 Hz)

Apparent power

Light/Surge Voltage Suppressor

	AC	DC
DIN terminal	Neon bulb	● <u>LED</u>
with indicator light	Varistor 🖇 🖁 🗒	Varistor 🕸 🖓 🖏
(DLS)		
Conduit terminal	o <u>Ne</u>	on bulb
with indicator light	Varistor S	
(TLS)		

The DIN terminal has a surge voltage suppressor inside the connector.

· Grommet type

Surge voltage suppressor

b


4. Manual override with lock

1) Using a screwdriver, push the manual override button that is located in the head portion of the solenoid valve in order to directly push the spool valve downward, thus causing the valve to switch.

2) With the button remaining pushed down, turn it approximately 90° clockwise or counterclockwise to maintain the manual override locked state.

 To revert to the original state, keep the button pushed down and turn it approximately 90° clockwise or counterclockwise.

Construction



Operation principle <De-energized>

The spool valve (3) is pushed up by the spring reaction force, sealing port 1 and opening ports 2 and 3. Air flow direction: $1 \leftrightarrow Block, 2 \leftrightarrow 3$

<Energized>

The armature (6) is suctioned toward the magnetic pole piece (5), and the spool valve (3) is pushed down via the push rod (7). This seals port (3) and opens ports (1) and (2). At this time, the armature (6) and the magnetic pole piece (5) are brought into close contact with each other by the magnetic pole piece (5) being suctioned toward the armature (6).

Air flow direction: $1 \leftrightarrow 2$, $3 \leftrightarrow Block$


Component Parts

00111	ponent i uno				
No.	Description	Material	Note		
1	Body	Aluminum die-casted	Platinum silver		
2	Cover	Steel	Platinum silver		
3	Spool valve	Aluminum, NBR			

SMC


Rubber Seal 3-Port/Poppet Type VT315 Series

Dimensions





*1 There is also an option with a 600 mm lead wire length (VT315- \Box H).

Conduit terminal (T)




Conduit terminal with indicator light (TL)







DIN terminal (D)



DIN terminal with indicator light (DL)




With locking manual override



VT315 Series **Manifold Specifications**


The VT315 type manifold is a B-mounted system with 2 types: a common exhaust type and an individual exhaust type.



exhaust

How to Order									
VVT320-05	0 1 -								
 Porting specifications 	Thread type								
Symbol P A R	Nil Rc								
0 Side Side Side	F G								
1 Side Bottom Side	N NPT								
	T NPTF								
Valve stations	• Exhaust type								
02 2 stations	1 Common exhaust								
	2 Individual exhaust								
20 20 stations									
* To order valves and blanking plate assem- blies mounted onto the manifold, list the	Mounting bracket								
valve and blanking plate assembly part num-	0 Without mounting bracket								
bers with the manifold base part number.	A With mounting bracket								
<example> VVT320-05011 pc. * VO315-001G4 pcs. * DXT010-36-2A1 pc. The asterisk denotes the symbol for assembly. Prefix it to the part nos. of</example>									

How to Order Valves (For Manifold)



Accessory for Applicable Solenoid Valves

Description	Part no.	Qty
O-ring	KA00087(P8)	4
Round head combination screw	DXT010-66-2	2

Option

option						
Description	Part no.	Note				
Mounting bracket	DXT010-37-4 A	Common exhaust				
assembly	DXT010-37-3□A	Individual exhaust				
Blanking plate		Common exhaust				
(O-ring, With screw)	DXT010-36-2A	Individual exhaust				
: Thread type (Refer to "How to Order.")						

Manifold Specifications

the solenoid valve, etc.

Manifold type			B mount						
Max. number of	fstations		20 stations*1						
Applicable sole	noid valve		VO315□-00□□□						
	location/F	n/Port size Port direction							
Exhaust port type	Р	А	R	Р	A	R			
Common	Base	Base	Base	Side	Side/Bottom	Side			
Common	1/4(3/8)	1/4	1/4(3/8)	Side	Side/Bollom	Side			
Individual	Base	Base	Base	Side	Side/Bottom	Side			
mumuuai	1/4(3/8)	1/4	1/8	Side	Side/Bollom	Side			

upply air to both sides of the P port. The common exhau exhaust from both of the R ports.

The mounting bracket can change the P and R ports (only the P port for the individual exhaust type) to 3/8". The common exhaust type needs a specific base.

Flow Rate Characteristics/Weight

	Flow rate characteristics										Weight		
Valve model	1 →	$2 (P \rightarrow I)$	A)	2 →	$3 (A \rightarrow $	R)	$3 \rightarrow$	2 (R \rightarrow)	A)	2 →	1 (A \rightarrow	P)	weight
	C [dm³/(s·bar)]	b	Cv	C [dm ³ /(s·bar)]	b	Cv	C [dm3/(s.bar)]	b	Cv	C [dm³/(s·bar)]	b	Cv	Grommet
VO315													0.39 kg
VO315V (Vacuum spec. type)	1.4	0.12	0.33	1.2	0.18	0.29	1.5	0.16	0.35	1.2	0.13	0.28	
VO315E		••••											0.40 kg (For AC)
(Continuous-duty type)													0.39 kg (For DC)



VT315 Series Specific Product Precautions

Be sure to read this before handling the products. Refer to the "Handling Precautions for SMC Products" (M-E03-3) for safety instructions and solenoid valve precautions.

Mounting

A Warning

When mounting valves on the manifold base, the mounting orientation is decided. If it is mounted in the wrong direction, connected equipment may malfunction. Mount it by referring to how to switch over from N.C. to N.O. specifications.

▲Caution


The valves are assembled as N.C. valves at the time of shipment.

By removing the two retaining screws from the desired valves, and rotating each valve body 180° and reassembling it on the manifold base, it is possible to reassemble an N.C. valve as an N.O. valve. (Make sure that there are O-rings fixed on 4 positions of the valve surface.) Properly tighten the screws.

Tightening torque of the mounting screw: 1.4 $\ensuremath{\text{N}$\cdot\text{m}$}$


Changing from N.C. to N.O.

Universal porting permits convertibility N.C./N.O. by a simple 180 degree rotation. Mounting conditions for N.C. and N.O. is indicated as below figure.



VT315 Series

Dimensions




SMC

Dimensions

L2

L3

L4






VT315 Series Specific Product Precautions

Be sure to read this before handling the products. Befer to the "Handling Precautions for SMC Products

Refer to the "Handling Precautions for SMC Products" (M-E03-3) for safety instructions and solenoid valve precautions.

A Caution

- A bleed port for the main valve is located at the bottom of the solenoid valve. Please refrain from blocking it as doing so may result in malfunction.
- * Generally, when the solenoid valve is mounted on a metal surface, it can breathe through the breather hole, via the breather groove. However, if it is mounted on a rubber surface, the rubber could become deformed and block the hole.



Bottom of the solenoid valve

- 2. Make sure that dust and/or other foreign matter do not enter the valve from the unused ports (e.g. exhaust port). Also, since there is a bleed port for the armature in the manual override, do not allow an accumulation of dust and/or other foreign matter to block the bleed port.
- Do not touch the solenoid valve because the coil generates heat when energized, which may cause the external surface to become hot, resulting in burns, etc., depending on the energized state.

A Caution

How to Use the DIN Terminal

1. Disassembly

- After loosening the screw ①, if the housing ④ is pulled in the direction of the screw ①, the connector can be removed from the body of the equipment (solenoid, etc.).
- 2) Pull out the screw ①, then remove the gasket @ or @.
- 4) Remove the cable gland (5), plain washer
 (6), and rubber seal (7).

2. Wiring

- Pass the cable (a) through the cable gland (5), washer (6), and rubber seal (7), in this order, and then insert them into the housing (4).
- Skin the cable (8) and crimp the crimped terminal (9) to the edges.
- 3) Remove the screw with a washer (2) from the bracket (3). (Loosen in the case of the Y-shape type terminal.) As shown in the figure on the right, mount the crimped terminal (3), and then tighten the screw (3) again.
 - * Tighten within the tightening torque range of 0.5 N·m \pm 15%.
- Note: a It is possible to wire using bare wires. In such a case, loosen the screw with a washer ③, place the lead wire into the bracket ③, and then tighten it once again.
 - b The max. size for the round terminal ③ is 1.25 mm²—3.5, and for the Y terminal, it is 1.25 mm²—4.
 - c Cable ⑧ outside diameter: ø6 to ø12 mm
 - * For those with an outside diameter ranging from ø9 to ø12, remove the inside parts of the rubber seal ⑦ before using.

3. Assembly

 The terminal box ③ connected to the housing ④ should be put back in place.
 (Push it down until you hear it click.)


- Put the rubber seal ⑦ and the plain washer ⑥, in this order, into the cableintroducing slit on the housing ④, and then firmly tighten the cable gland ⑤.
- 3) After inserting the gasket (2) or (2) between the bottom part of the terminal box (3) and the plug on the equipment, screw in the screw (1) on top of the housing (4) and tighten it.

* Tighten within the tightening torque range of 0.5 N·m ±20%.

Changing the entry direction

The cable entry direction of a connector can be changed as desired (4 directions at 90° intervals), depending on the combination of the housing (4) and terminal block (3).

Exploded view



Electrical Connection

If the rated voltage for the solenoid valve is DC and there is polarity, connect terminal no.1 to the positive (+) side and no.2 to the negative (-) side.

Connector for DIN Terminal

Description	Part no.
DIN connector	GDM2B

How to Calculate the Flow Rate

For obtaining the flow rate, refer to "Best Pneumatics No.1."