## Flame Resistant (Equivalent to UL-94 Standard V-0)

# FR Soft Nylon Tubing

# TRS Series

Model/Specifications




(RoHS)

Suitable for air and water piping in environments where sparks from spot welders, etc., may be a problem.

#### Flame resistant tubing

#### Max. Operating Pressure



Model/Specification	● — 20 m roll	□ — 100 m reel			
Model	TRS0603	TRS0805	TRS1065	TRS1208	
Tubing O.D. (mm)	6	8	10	12	
Tubing I.D. (mm)	3	5	6.5	8	
Black (B)	<u> </u>		<u> </u>		
White (W)	<del>  •</del>	<u> </u>	<u> </u>	<u> </u>	
Red (R)	<u> </u>	<u> </u>	<u> </u>		
Blue (BU)		•	•	<u> </u>	
Green (G)	<u> </u>	<u> </u>	•		
	_				
	I				

Fluid		Air/Water							
Max. operating pressure (MPa)	20°C	1.2							
	40°C	1.2							
	60°C	0.7							
Applicable fittings			FR one-touch fittings: KR-W2 series						
Minimum bending radius (mm)		1	7	1	9	2	7	3:	2
Operating temperature	temperature -20 to +60°C (Water: 0 to 60°C) (No free			ezing)					
Material Fla			Flame resistant nylon (Equivalent to UL-94 standard V-0)						

## **∧** Precautions

Be sure to read this before handling the products. ■ Refer to back page 50 for Safety Instructions ■ ■ and pages 13 to 17 for Fittings and Tubing ■ Precautions.


### **∕** Caution

1. Applicable for general industrial water. Please consult with SMC if using for the other kind of fluid.

Also, the surge voltage pressure must be under the maximum operating pressure. If the surge pressure exceeds the maximum operating pressure, it will result in damage to fittings and tubes.

2. Abnormal temperature rise caused by adiabatic compression may result in the tube bursting.

#### **How to Order**



BU

G

Blue (Opaque)

Green (Opaque)

LO

IDK

**ØSMC** 

KQ2

KQB2

KS KX

KM KF

> M H/DL L/LL

KC

KK KK130

DM

KDM KB

KR

KA

KQG2 KG

KFG2

MS KKA

KΡ

MQR