
# 3 Port Solenoid Valve

# VT307 Series

# **Direct Operated Poppet Type**



Vacuum applications
-101.2



# A single valve with various valve functions

(Universal porting type)

N.C. valve	N.O. valve	
Divider valve	Selector valve	etc.

Low concentration ozone resistant
Rubber seal material: HNBR for main valve

Mounting dimensions are

interchangeable with current product



#### Body ported type






# ■ A variety of valve options



# ■ Application examples



# 3 Port Solenoid Valve, Universal Porting Type Variations

Poppet type	Direct operated poppet type			Pilot poppet type		
Series	VT307 VT317		VT325	VP300/500/700		
Cv (P←→A)	0.19	0.62	1.4	0.8 to 3.6		
Page	Page 1243	Page 1251	Page 1259	Page 1053		

# 3 Port Solenoid Valve Direct Operated Poppet Type C € CA


# VT307 Series



**Rubber Seal** 

Note) CE/UKCA compliant: Electrical entry is applicable only for the DIN terminal

#### How to Order



	Body type •
Т	Body ported
0	For manifold

#### Valve option

Nil	Standard type	
E*	Continuous duty type	
Y* Energy-saving type		
V*	Vacuum specification type	
W*	Energy-saving type, Vacuum specification ty	

<sup>\*</sup> Semi-standard

#### Pressure specifications

Nil	Standard type (0.7 MPa)
K*	High-pressure type (1 MPa)


<sup>\*</sup> Semi-standard

#### Rated voltage

valve option		Nil	E	Υ	ν	w
	Rated voltage		_			
1	100 VAC, 50/60 Hz	•	•	_	•	_
2	200 VAC, 50/60 Hz	•	•	_	•	_
3*	110 VAC, 50/60 Hz	•	•	_	•	_
4*	220 VAC, 50/60 Hz	•	•	_	•	_
5	24 VDC	•	•	•	•	•
6*	12 DCV	•	•	•	•	•
7*	240 VAC, 50/60 Hz	•	•	_	•	_

<sup>\*</sup> Semi-standard

#### Electrical entry



Note) A gasket must be ordered separately for DO. Refer to page 1245 for gasket part numbers.

#### CE/UKCA-compliant None

CE/UKCA-compliant\* \* Electrical entry and light/surge voltage suppressor: D/DO/DZ/DOZ only

#### Bracket

Nil	None
F	With bracket

#### Thread type

Nil	Rc
F	G
N	NPT
Т	NPTF


#### Port size

Nil	Without port (For manifold)
01	1/8 (6A)
02	1/4 (8A)

#### Light/Surge voltage suppressor

Light/ourge voltage suppliessor		
Nil	None	
s	With surge voltage suppressor	
3	(Grommet type only)	
z	With light/surge voltage suppressor	
	(DIN terminal type only)	

#### With surge voltage suppressor







#### Manifold

	Model	Applicable manifold type	Accessories	
	VO307□(-Q)	Common or individual exhaust	Function plate (DXT152-14-1A) Note)	
		Common or individual exhaust	Mounting screw (NXT013-3)	

Note) It is not applicable to the continuous duty type. Refer to the accessories on page 1247.

#### Option

Description	Part no.
Bracket	DXT152-25-1A (With screw)

#### **⚠** Caution

Make sure that dust and/or other foreign materials do not enter the valve from the unused port (e.g. exhaust port).

#### Standard Specifications

Type of actuation		Dire	ct operated type 2 position single solenoid				
Fluid		Air					
Operating pressure range	0 t	0 to 1 MPa (High-pressure type), 0 to 0.7 MPa (Standard type)					
Ambient and fluid temperature	е	-10 to 50°C (No freezing)					
Response time Note 1)			20 ms or less (at 0.5 MPa)				
Max. operating frequency			10 Hz				
Lubrication	No	ot required	d (Use turbine oil Class 1 ISO VG32, if lubricated.)				
Manual override			Non-locking push type				
Mounting orientation			Unrestricted				
Impact/Vibration resistance No	te 2)	150/50 m/s <sup>2</sup>					
Enclosure		Dustproof					
Electrical entry		Grommet, DIN terminal					
Coil rated voltage (V)	AC (5	0/60 Hz)	100, 200, 110*, 220*, 240*				
Con rated voltage (v)		DC	24, 12*				
Allowable voltage fluctuation			-15 to +10% of rated voltage				
Apparent power Note 3) Note 4)	AC	Inrush	12.7 VA (50 Hz), 10.7 VA (60 Hz)				
Apparent power	AC	Holding	7.6 VA (50 Hz), 5.4 VA (60 Hz)				
Power consumption Note 3) Note 4)		DC	Without indicator light: 4 W, With indicator light: 4.2 W				
Light/Surge voltage suppressor		AC Varistor, LED					
(DIN terminal type only)		DC	Diode, LED				

<sup>\*</sup> Semi-standard

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 1000 Hz. Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period)

Note 3) At rated voltage
Note 4) The value is different for continuous duty type (VT307E), and energy-saving type (VT307Y/W).
Refer to "Valve Options" shown below. Flow Rate Characteristics/Weight

						Flow	rate ch	naracteristic						
Valve model	Port	1 → 2 (P → A)			2 → 3 (A → R)			3 → 2 (R → A)			2 → 1	(A → I	P)	Weight
	Size	C[dm3/(s-bar)]	b	Cv	C[dm3/(s-bar)]	b	Cv	C[dm3/(s-bar)]	b	Cv	C [dm3/(s-bar)]	b	Cv	Grommet
VT307 VT307V (Vacuum spec. type)		0.71	0.35	0.18	0.68	0.27	0.17	0.65	0.36	0.17	0.63	0.35	0.17	
VT307E (Continuous duty type) VT307Y (Energy-saving type) VT307W (Energy-saving, Vacuum spec. type)	1/8	0.41	0.26	0.10	0.44	0.35	0.11	0.48	0.27	0.12	0.35	0.33	0.10	0.451
VT307 VT307V (Vacuum spec. type)		0.71	0.31	0.19	0.71	0.25	0.17	0.68	0.33	0.17	0.71	0.26	0.18	0.15 kg
VT307E (Continuous duty type) VT307Y (Energy-saving type) VT307W (Energy-saving, Vacuum spec. type)	1/4	0.49	0.20	0.12	0.44	0.34	0.11	0.48	0.17	0.12	0.46	0.28	0.11	

Note) Values for a single valve unit. It is not applicable to the manifold. Refer to the manifold specifications on page 1247.

#### **Valve Options**

#### Continuous duty type: VT307E

Exclusive use of VT307E is recommended for continuous duty with long time loading.

#### 

- 1. This model is for continuous duty, not for high cycle rates. But even in low cycle rates, if energizing the valve more than once a day, please consult with SMC.
- 2. Energizing solenoid should be done at least once in 30 days.

Specifications different from standard are as follows.										
		7.9 VA (50 Hz), 6.2 VA (60 Hz)								
AC	Holding	5.8 VA (50 Hz), 3.5 VA (60 Hz)								
Power consumption/DC 1.8 W, With indicator light: 2 V										
Response time Note) 30 ms or less (at 0.5 MPa)										
Note) Refer to Note 1) of the standard specifications.										

#### Energy-saving type: VT307Y (VT307W)

If low power consumption is required for electronic control, "VT307Y(W)" (1.8 W) is recommended.

Specifications different from standard are as follows. Power consumption/DC | 1.8 W, With indicator light: 2 W Response time Note) 25 ms or less (at 0.5 MPa) Note) Refer to Note 1) of the standard specifications.

#### Vacuum spec. type: VT307V (VT307W)

This vacuum model has less air leakage than the standard model under low pressure. It is recommended for vacuum application.

#### 

Since this valve has slight air leakage, it can not be used for vacuum holding (including positive pressure holding) in the pressure container.

Specifications different from standard are as follows. Operating pressure range -101.2 kPa to 0.1 MPa




Note 1) Based on dynamic performance test, JIS B 8419: 2010. (Coil temperature: 20°C, at rated voltage, without surge voltage suppressor)

Note 2) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction

and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

#### Construction



#### Operation principle

<De-energized>

Poppet valve ② is pushed upward by the return spring ③, port ① is closed. Then, port ② and port ③ are connected.

Air flow direction:

How to Use DIN Terminal

1) After loosening the screw 1, then if the

the body of equipment (solenoid, etc.).

3) On the bottom part of the terminal block 3

there's a cut-off part 9. If a small flat head

screwdriver is inserted between the opening

in the bottom, terminal block 3 will be

4) Remove the cable gland 4, plain washer 5

1) Pass the cable 7 through the cable gland 4,

and then insert them into the housing ②.

2) Loosen the screw ① attached to the terminal

plain washer 5 and rubber seal 6 in this order,

Note 1) Tighten within the tightening torque of 0.5 N·m ±15%.

Note 2) Cable ⑦ outside diameter: ø6 to ø8 mm (ø4.5 to ø7 mm for CE/UKCA-compliant

Note 3) Crimped terminal like round-shape or Y-shape cannot be used.

2) Pull the screw 1) out of the housing 2).

removed from the housing ②

and rubber seal 6.

products)

2. Wiring

housing ② is pulled in the direction of the

screw (1), the connector will be removed from


Port  $1 \leftrightarrow Block, 2 \leftrightarrow 3$ 

#### Component Parts

1. Disassembly

No.	Description	Material	Note
1	Body	Aluminum die-casted	Color: White
2	Poppet valve	Aluminum, HNBR	
3	Return spring	Stainless steel	
4	Molded coil	Resin	
	Return spring	Stainless steel	

#### **Energized**



#### <Energized>

When energizing the molded coil ③, the armature ⑤ is magnetically attracted to the core ⑥, and through the push rod ⑦, it pushes down the poppet valve ② and port ⑤ is closed. Then, port ⑥ il and port ② are connected. At this time, there will be gaps between the armature ⑤ and the core ⑥, but the armature ⑤ will be magnetically firmly attracted to the core ⑥.

Air flow direction: Port 1 ↔ Port 2, Port 3 ↔ Block

#### 3. Assembly

- Pass the cable ⑦ through the cable gland ④, plain washer ⑤ and rubber seal ⑥ in this order and connect to the terminal block ③. Then, mount the terminal block ③ on the housing ②.
  - (Push it down until you hear the click sound.)
- 2) Put the rubber seal (6) and plain washer (5) in this order into the cable entry of the housing (2), and then tighten the cable gland (4) securely.
- 3) Insert the gasket ® between the bottom part of terminal block ③ and the plug attached to the equipment. Then, screw in ① from the top of the housing ② to tighten it.


Note 1) Tighten within the tightening torque of 0.5 N·m ±20%.


#### Changing the entry direction

The orientation of a connector can be changed 180°, depending on the combination of a housing ② and a terminal block ③.

#### 

#### Light/Surge Voltage Suppressor






#### **Electrical Connection**

DIN terminal is connected inside as in the figure below. Connect to the corresponding power supply.

#### **DIN terminal block**



Applicable cable O.D.
 ø6 to ø8 (ø4.5 to ø7 mm for CE/UKCA-compliant products)


Lead Wire Color									
Voltage Color									
100 VAC	Blue								
200 VAC	Red								
DC	Red (+), Black (-)								
Others Gray									

Connector	ioi Din Terillilai, Gasket
Description	Part no.
DIN connector	B1B09-2A (Standard)
	GM209NJ-B17 (CE/UKCA-compliant)
Gasket	CAXT623-6-7-12 (Standard)
	CAXT623-6-7-11 (CE/UKCA-compliant)

# VT307 Series


#### **Dimensions**

#### Grommet: VT307-□G1



Note) There is also "VT307-□H1" (lead wire length: 600 mm).

#### DIN terminal: VT307-□D1



### VT307 Series

# **Manifold Specifications**


VT307 manifold is available both as a common exhaust and individual exhaust model.

Manifold valve can be easily converted from N.C. (Normally Closed) to N.O. (Normally Open) merely by turning over the function plate.





#### **How to Order Manifold Base**



#### **Manifold Specifications**

Manifold ty	ре		B mount					
Max. numb	er of stations		20 stations Note)					
Applicable	solenoid valve		VO307□-□□□□ (-Q)					
Exh	aust port		Port location (Direction)/Port size					
Symbol	Type	P	Р		Α	R		
2	Common	Base (		Ва	se (Side)	Base (Side)		
3	Individual	Base (Side)		Base (Side)		Base (Top)		

Note) For 6 stations or more, supply air both sides of P port. The common exhaust type should exhaust from both of the R port.

#### Option

Description	Part no.
Blanking plate (With gasket, screw) Note)	DXT060-51-13 <sup>A</sup>

#### **Accessories for Applicable Solenoid Valve**

Description	Part no.	Qty.
Function plate (With gasket) Note)	DXT152-14-1 A	1 pc.
Mounting screws	NXT013-3	2 pcs.

Note) DXT060-51-13B, DXT152-14-1B are for the continuous duty type.


#### Flow Rate Characteristics/Weight


					Flo	w rate ch	aracteristic	s					Weight
Valve model	1 → 2 (P → A)		$2 \rightarrow 3 (A \rightarrow R)$			$3 \rightarrow 2 (R \rightarrow A)$			$2 \rightarrow 1 (A \rightarrow P)$			vveigni	
	C[dm3/(s-bar)]	b	Cv	C[dm3/(s-bar)]	b	Cv	C[dm3/(s-bar)]	b	Cv	C[dm3/(s-bar)]	b	Cv	Grommet
VO307	0.34	0.28	0.089	0.34	0.22	0.082	0.36	0.28	0.091	0.34	0.10	0.080	
VO307V (Vacuum spec. type)	0.34	0.26	0.069	0.34	0.22	0.062	0.36	0.26	0.091	0.34	0.18	0.060	
VO307E (Continuous duty type)													0.15 kg
VO307Y (Energy-saving type)	0.30	0.18	0.070	0.30	0.15	0.072	0.32	0.20	0.075	0.30	0.15	0.069	
VO307W (Energy-saving, Vacuum spec. type)	1												


# VT307 Series


#### **Dimensions: Common Exhaust**

#### VV307-01-□2-01-F










L Dir	L Dimension n: Station:													
_ n	2	3	4	5	6	7	8	9	10	Formula				
L <sub>1</sub>	88	114	140	166	192	218	244	270	296	L1 = 26 x n + 36				
L <sub>2</sub>	62	88	114	140	166	192	218	244	270	L2 = 26 x n + 10				


<sup>\*</sup> The numbers in brackets indicate the dimensions of the CE/UKCA-compliant model (-Q).





#### **Dimensions: Individual Exhaust**

#### VV307-01-□3-□-F









L Dir	L Dimension n: Stations												
	2	3	4	5	6	7	8	9	10	Formula			
L <sub>1</sub>	76	102	128	154	180	206	232	258	284	L1 = 26 x n + 24			
L <sub>2</sub>	64	90	116	142	168	194	220	246	272	L2 = 26 x n + 12			

<sup>\*</sup> The numbers in brackets indicate the dimensions of the CE/UKCA-compliant model (-Q).



# $\Lambda$


# VT307 Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 15 for 3/4/5 port solenoid valve precautions.

#### Mounting

# **∧**Warning

When mounting a valve on the manifold base, N.C. and N.O. can be reversed by the function plate orientation. Also, since the cylinder operates in reverse, confirm if the function plate is correctly mounted or not.



### **∧** Caution

- Each valve is fixed to the manifold base with two M4 mounting screws. Tighten the screws firmly when re-mounting.
- For mounting, tighten M4 or equivalent screws evenly into the mounting holes of the manifold base.

Tightening torque of the mounting screw (M4): 1.4 N·m

#### Changing from N.C. to N.O.

# **∧** Caution

This product is delivered as N.C. valve.

If N.O. valve is required, remove mounting screws of the required valve and turn over the function plate. (Make sure that there are gaskets on both sides of the plate.) Then, tighten the mounting screws to fix the valve to the manifold base.




Figure: For N.C.

Specifications	Function plate
N.C.	No mark
N.O.	NO

#### **Piping**

### **⚠** Caution

1. For the common exhaust type, pressurization or evacuation of the 3(R) port can cause a malfunction.