## Manifold Regulator Modular Type

## ARM2500/3000 Series

- A modular type that can be freely mounted on a manifold station.
- Optimal for central pressure control.
- Easily set up using the new knob. Also has a One-touch lock system.





#### ARM 2500 - 05 02 G1 Made to Order Nil None Regulator for With backflow X216 manifold function Accessory (Pressure gauge) Body size Nil None (With plug) 2500 G1 Back side thread: G33-10- □01 3000 G2 Vertical side thread: GA33-10-□01 Pressure gauges are shipped togethe Number of stations (but not assembled) 02 2 stations Port size (OUT side) Symbol Port size Applicable model 10 stations 1/4 ARM2500 03 ARM3000 Thread type Nil Rc NPT G Piping Symbol Туре

How to Order

## **Standard Specifications**

otaniaara opoomoationo	
Proof pressure	1.5 MPa
Maximum operating pressure	1.0 MPa
Regulating pressure range	0.05 to 0.85 MPa
Ambient and fluid temperature	-5 to 60°C (No freezing)
Fluid	Air
Construction	Relieving type

Common IN

Individual IN

From end plate

From OUT port or G port

(ka)

#### Symbol

Common IN Individual IN





JIS Symbol
With backflow function

### Port Size/Weight


		o,g	-						
				Port size		Pressure	Weigl	nt (kg)	
Mo	Model	Piping	IN s	side	OUT side	gauge	Regulator	End plate	
			Body	End plate	OUT Side	port size	negulatoi		
A DIV	ARM2500	Common IN	_	3/8	1/4	1/8	0.26	0.06	
ANIV	12500	Individual IN	1/4	_	1/4	1/8	0.26	0.06	
A DIV	12000	Common IN	_	1/2	3/8	1/8	0.47	0.11	
ARM3000	Individual IN	3/8 —		3/8	1/8	0.47	0.11		

Weight by the Number of Stations

									( 0,
Model Stations	2	3	4	5	6	7	8	9	10
ARM2500	0.68	0.96	1.23	1.51	1.78	2.06	2.33	2.61	2.89
ARM3000	1.25	1.75	2.25	2.75	3.26	3.76	4.26	4.76	5.26

## Manifold Regulator ARM2500/3000 Series

#### Option: Pressure Gauge (Max. pressure indication: 1.0 MPa)



Note 1) in the gauge part no. (e.g. G33-10- in indicates the type of threads used for connection. For Rc, leave the symbol blank, and for NPT, enter "N".

Please consult with SMC for the supply of a pressure gauge with NPT port threads.

Note 2) Use caution not to tighten excessively when mounting a pressure gauge, otherwise it will may result


in a breakdown. For sealing, use a sealant tape.

Option/Mounting Bolt Assembly

Model	Part no.	Dimensions	Qty.	Note
ARM2500	136313	Hexagon socket head cap screw (M5 x 70)	4	With flat washer
ARM3000	136413	Hexagon socket head cap screw (M6 x 85)	4	With flat washer

#### **Option/Bracket Assembly**


Individual IN type can be used as a single unit regulator.




Model	Part no.	Composition of assembly	Α	В	С	D	Е	F	G	Н
ARM2500	136314	Set nut (1349172)		34	70	- 4	45.4			M33 x 1.5
ARM2500	130314	Bracket (B220)	30	34	70	5.4	15.4	55	2.3	M33 x 1.5
ARM3000	136414	Set nut (131532)			75.5	6.5	8	53	2.3	M42 x 1.5
ARM3000	130414	Bracket (B320)	41	40						

Note) Tighten the set nut securely and fix it. Recommended torque for set nut ARM2500: 17.5 ± 3.5 N·m ARM3000: 22.5 ± 4.5 N·m


#### Flow Rate Characteristics (Representative Value) Inlet pressure: = 0.7 MPa






Pressure Characteristics Initial setting
(Page 20 Limin (ANR))


Page 20 Limin (ANR)





## ARM2500/3000 Series

#### Construction



#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum die-casted	Chromate treated/Platinum silver painted
-2	Bonnet	Polyacetal	

#### **Replacement Parts**

No.	Description	Material	Par	t no.	
INO.	Description	Maleriai	ARM2500	ARM3000	
3	Diaphragm assembly	Weather resistant NBR	1349161A	131515A	
4	Valve assembly	Brass, HNBR	13639A	13649A	
5	Valve spring	Stainless steel	136310	136410	
6	Valve O-ring	NBR	KA00892	KA00904	
	valve O-ring	NBH	11.5 x 8.5 x 1.5	14.5 x 10.5 x 2	
7	O-ring	NBR	KA00078	KA00083	
,	O-ring	INDI	JIS B 2401 P3	JIS B 2401 P5	
8	O-ring	NBR	KA00299	KA00961	
-	O-ring	INDR	28 x 25 x 1.5	35 x 31 x 2	

#### **Component Parts**

9 10	R	omponent	Qt	y.	ARM	2500	ARM	3000	
10	R	<u>'</u>		у.			ARM3000		
10	_	legulator			Common IN	Individual IN	Common IN	Individual IN	
-	Fr	Regulator			ARM2500-A-02	ARM2500-B-02	ARM3000-A-03	ARM3000-B-03	
11		nd plate R	1 1 1				13646A		
• •	Er	nd plate L						13646B (Except	
12		O-ring			13636A	13636B			
13	cket	Bracket A	2		13030A	(Except			
		Bracket B	1 set	1 set 2		O-ring)		O-ring)	
	Bra	Hex. socket head cap screw		2				]	
12		O-ring	1						
	Ŧ	Bracket A		2					
13	Š	Bracket B	1 set	2	136	312	136	412	
	Bra	Hex. socket head cap screw		2					
bly 13 Bracket A Bracket A Bracket B Hex. socket head cap screw 12 O-ring Bracket E Bracket A Bracket A Bracket A Bracket B Hex. socket		2 O-ring 1  Bracket A Bracket B Hex. socket head cap screw	2 O-ring 1  Bracket A   5   2   Bracket B   4   5   Bracket B   4   5   Bracket B   5   2   Bracket B   6   5   Bracket B   7   5   Bracket B   7	head cap screw   2	Deficient   Defi	Desire   D			


- (1) When adding n stations to ARM  $^{2500}_{3000}$   $\square\square$   $^{A}_{B}$
- Regulator n pcs.
   Bracket assembly n pcs.
   Bracket assembly n pcs.
   When regulators, end plate assembly and bracket assembly are assembled to make the manifold of n stations.

  - n pcs.
    - n pcs.
  - Regulator n pcs
     Bracket assembly n pcs
     End plate assembly 1 pc.



## Manifold Regulator ARM2500/3000 Series

#### **Dimensions**



#### **Dimensions**

 $\ast$  For products with pressure gauge, pressure gauges are shipped together with product.

Symbol	Α	В	С	D	E	F	G	н	ı	J	к	L	М	N	0	Р
ARM2500	6	17	44	56	42	126.5	58	45	17	21	38	42	29	48	68	33.5
ARM3000	7	21	54	68	55	153.5	70	53	23.5	27.5	48.5	55	35	59	85.5	42.5

**Dimensions by the Number of Stations** 

Model	Symbol	Manifold stations									
Widdel	Symbol	2	3	4	5	6	7	8	9	10	
	L1	118	160	202	244	286	328	370	412	454	
ARM2500	L2	106	148	190	232	274	316	358	400	442	
	L3	84	126	168	210	252	294	336	378	420	
	L1	152	207	262	317	372	427	482	537	592	
ARM3000	L2	138	193	248	303	358	413	468	523	578	
	L3	110	165	220	275	330	385	440	495	550	

**SMC** 



# ARM2500/3000 Series Specific Product Precautions

Be sure to read this before handling the products.

Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

#### Mounting/Adjustment

## **∧** Caution

- Release the lock to adjust the pressure. After the adjustment, engage the lock. Failure to observe this procedure could damage the knob or cause the secondary pressure to fluctuate.
  - On the ARM2500 type, pull the adjustment knob to release the lock and push the adjustment knob to engage the lock. If it does not lock easily, turn the knob slightly clockwise or counterclockwise before pushing it.
  - On the ARM3000 type, pull the adjustment knob to release the lock. (An orange colored line is provided at the bottom of the adjustment knob for visual checking.)
    - Push the adjustment knob to engage the lock. If it does not lock easily, turn the knob slightly clockwise or counterclockwise; then, push it until the orange colored line is no longer visible.
- Make sure to check the inlet pressure before setting the pressure. The outlet pressure must be set to 85% or less of the inlet pressure.
  - Failure to observe this procedure could cause the outlet pressure to fluctuate.
- In the case of the common IN type, supply pressure from the two IN ports from both ends. Failure to observe this procedure could lead to an excessive pressure drop.

#### Selection

## **⚠** Warning

 For ARM2500/3000, releasing the inlet pressure does not mean that all residual pressure is released (the outlet pressure cannot be released). When releasing residual pressure, use a manifold regulator with a backflow function (X216).

### 

 When operating at an inlet pressure lower than the inlet pressure used in the flow rate characteristics graph, the pressure drop on the outlet side may be greater. Therefore, be sure to conduct testing using the actual equipment.

For pressure control equipment selection, refer to page 123 in the "Product Selection Guide."

#### Maintenance

## **⚠** Warning

1. Make sure to perform a periodic inspection of the pressure gauge when the manifold regulator with a backflow function is installed between a solenoid valve and an actuator. Sudden pressure changes could happen and the durability of the product could be reduced. Using an electronic type pressure gauge is recommended, depending on the situation.

