
## Flame Resistant (Equivalent to UL-94 Standard V-0) FR Double Layer Tubing **TRB Series**

Suitable for air and water piping in environments where sparks from spot welders, etc., may be a problem.

Double layer design using flame resistant resin (equivalent to UL-94 Standard V-0) for outer layer.






Sectional view of FR double layer tubing


Model			TRB0604	TRB0806	TRB1075	TRB1209
Inner tubing O.D. (mm)			6	8	10	12
Inner tubing I.D. (mm)			4	6	7.5	9
Outer layer thickness (mm)			1	1	1	1
Note)	Black (B)					
colo	White (W)					
ayer	Red (R)		•	—— <u> </u> —	•	
External layer color (apple)	Blue (BU)		•	—— <b>•</b> ——	——•	— •
cterr	Yellow (Y)		•	—— <b>•</b> ——	•	—— <u> </u>
Ш	Green (G)		•	— •	•	— <b>•</b> —
Min. bending radius (mm)			15	28	35	45
•	ications					
Fluid			Air/Water			
Max. operating pressure (MPa) 20°C 40°C 60°C		1.0	1.0	1.0	1.0	
		1.0 0.8	0.8	0.8	0.8	
Recommended fittings		FR One-touch fittings: KR-W2 series				
Ambient and fluid temperature			-20 to +60°C (Water: 0 to 60°C) (No freezing)			
Material	Inner tul	oing	Nylon 12			
waterial	Outer layer		PVC (Equivalent to UL-94 Standard V-0)			

Note) The color of all inner tubing is black.

How to Order








## Installation on One-touch Fittings

## ▲ Caution

Length of tubing to be inserted into One-touch fittings is indicated on the outer layer of TRB tubing. Cut the tube according to this indication, (Step 1) and then strip off the outer layer (Step 2) for installing into fittings.



## ▲Caution

н

1. Applicable for general industrial water. Please consult with SMC if using for the other kind of fluid. Also, the surge voltage pressure must be under the maximum operating pressure.

If the surge pressure exceeds the maximum operating pressure, it will result in damage to fittings and tubing.

2. Abnormal temperature rise caused by adiabatic compression may result in the tube bursting.

KFG2

MS

KKA KP LO MQR T IDK

KQ2