Controller for Electro-Pneumatic Regulator

IC Series

Converts digital input signal into analog output signal







This product is mainly used in combination with ITV0000 series without a display function.

Controller for Electro-Pneumatic Regulator IC Series

How to Order



Option

When only optional parts are required, order using the part numbers listed below.

| Description | Part no. | Note |
|--------------------------|-----------|----------------------|
| Panel mount adapter set | P398050-1 | Gasket, Screw 2 pcs. |
| Display protective cover | P2992136 | - |



Display protective cover



Specifications

| | Model | IC1 | IC3 | IC5□ | IC9□ |
|-----------------------|-----------------------------|--|----------------------------|---------|----------|
| Pressure range | ge | 0.1 MPa | 0.5 MPa | 0.9 MPa | -0.1 MPa |
| Proof pressu | re | 500 kPa 1.5 MPa 500 kPa | | | |
| Fluid | | Air/Non-corrosive gas | | | |
| Dimensions | | 48 x 48 x 100.5 | | | |
| Power supply | / | 12 to 24 VDC (15 W or more), Ripple (p-p) 1% or less | | | |
| | | (1)No. of inputs: Up to 10 bit input from sequencer (parallel) Note 5) | | | |
| | | Input method: No-voltage contact or NPN open collector input | | | |
| Input | | Minimum pulse width: 50 msec | | | |
| | | ②Input method: 4 point input with keys | | | |
| | | (Interval time can be set by programming.) | | | |
| Power supply | (output | 12 VDC (Max. 300 mA) with accuracy of 12 to 14.4 VDC Note 2) | | | |
| i onci suppij | output | 24 VDC (Max. 300 mA) with accuracy of 22.0 to 26.8 VDC | | | |
| Command ou | itout | (1)0 to 10 Vc (Output resistance: 6.5 k Ω or more with accuracy of 0.5%F.S. or less) | | | |
| Command output | | (2)4 to 20 mA DC (Output resistance: 800 Ω or less with accuracy of 0.5%F.S. or less) | | | |
| | | Output: 4 points | | | |
| | | Output type: NPN, PNP open collector output | | | |
| Switch output | t | | Withstand voltage: Max. 30 |) V | |
| | - | Current: Max. 100 mA | | | |
| | | Internal voltage drop: 1 V or less | | | |
| | | Switching between N.O. and N.C. modes is possible. | | | |
| Switch respo | nse | 5 to 640 ms | | | |
| | | Power indication: 3 1/2-digit LED indicator (red) | | | |
| Display | | Output power supply voltage and current signal indication: 1-digit LED indicator (red) | | | |
| | New 4) | LED lights for RUN, CH, SW (red and green) | | | |
| Display accu | racy Note I) | ±0.5%F.S. ±1dig (at 25°C) | | | |
| Display sampling rate | | Approx. 4 times/s | | | |
| Temperature | characteristics | ±0.12%F.S./°C | | | |
| Error indicati | on | Displayed on pressure indication LED | | | |
| | Operating temperature range | 0 to 50°C | | | |
| | Storage temperature range | -20 to 60°C | | | |
| Resistance | Vibration registeres | 0 to 85%R.H. | | | |
| | | 10 to 55 Hz 1.5 mm amplitude X, Y, Z directions for 2 hrs. each | | | |
| | Water registance | 100 m/s ⁻ (approx. 10 G) X, Y, Z direction | | | |
| Sensor type | Water resistance | Univ display unit with cover is equivalent to IP65. It is equivalent IP40 without cover. | | | |
| Set value retention | | 10 years when dependized (EEDROM) | | | |
| Port size | | ME female (built in concer type) | | | |
| Port size | | Enclosure: POM | | | |
| | | Dienlay: PC | | | |
| Material | | Gaskat: NBB | | | |
| | | Panel mount adapter: POM | | | |
| | | Display protective cover: PC | | | |
| | | Approx, 330 g (Built-in sensor type) | | | |
| Weight | | Approx. 345 g (External sensor type) | | | |

Note 1) The display accuracy is the accuracy of the LED indication when the sensor port of the built-in sensor type is pressurized.

Note 2) The external sensor type has the same output power supply voltage specifications.

Note 3) The sensor for the external sensor type is not attached and must be ordered separately.

Any pressure sensor that transmits analog output signals can be connected.

Recommended sensor: PSE530 series (For more information, please refer to the Web Catalog.)

Note 4) Button operation is required when turning the power on again. However, the made-to-order specification (-X2) automatically returns to the pre-shutdown state when power is switched on again.

Note 5) For the ITV1000 to 3000 series 10-bit digital input type (CE/UKCA compliant), direct 10-bit input (parallel) through a sequencer is possible without going through an IC controller.

IC Series

Functions

4 point preset output

- Four points (CH1 to CH4) of pressure and switch output ranges can be set with the front panel keys.
- \cdot Up to 20 steps of programming is possible.
- · Interval time (1 to 999 sec) can be set by programming.
- \cdot The set pressures can be arranged in a random order.



10 bit parallel input

- · Up to 10 bits of parallel input is possible from PLC.
- \cdot Pressure can be set with $2^{10} = 1024$ steps.



Pressure switch function (4 point)

Switch output is enabled by setting the upper and lower limits.



Power supply voltage and output signal switch function

- Output power supply voltage and output signal to the electro-pneumatic regulator can be selected with the front panel keys.
- · No need of power supply for the electro-pneumatic regulator.
- · Stable power supply is possible.

| | Power supply voltage | Output signal |
|---|-------------------------|---------------|
| 1 | 12 VDC | 4 to 20 mA DC |
| 2 | 12 VDC | 0 to 10 VDC |
| 3 | 24 VDC | 4 to 20 mA DC |
| 4 | 24 VDC | 0 to 10 VDC |

Set pressure correction function (only for 4 point preset input)

Either automatic or manual adjustment is possible in pressure adjustment mode.

<Automatic adjustment mode>

The controller automatically calculates the deviation and converts the correction value into the output signal.

The deviation converges within the range of $\pm 0.5\%$ F.S.

Note) If the set pressure is 250 kPa and the output pressure on the pressure sensor is 245 kPa, the deviation is 250 – 245 = 5 kPa. In order to correct the deviation, the controller increases the output signal until the pressure on the pressure sensor converges at 250 kPa.

<Manual adjustment mode>

The deviation is corrected manually (with keys).

Zero span correction function

Deviation of the zero span point of the sensor can be corrected.

Keypad lock function

To prevent erroneous operation, operation on the key can be disabled. Keys which cannot be locked:

| F-ON |
|------|
| STOP |



P-ON/STOP key



Reset function

The data is reset to the initial condition at the time of shipment.

Anti-chattering function

Large bore cylinders and ejectors consume a large volume of air in operation and occasionally experience temporary drops in supply pressure. This function prevents detection of such momentary supply pressure drops. It regards them as abnormalities and changes the response time settings. Possible response time settings: 5 ms, 20 ms, 160 ms, 640 ms

<Principle>

The controller equalizes the pressures measured during the specified response time. It then compares the equalized pressure and the set pressure to output switch signals accordingly.

Error display

| Error name | | Error indication | Description | |
|----------------------|-----|------------------|--|--|
| | SW1 | Erl | | |
| Overcurrent | SW2 | ErZ | Excess current is running through | |
| error | SW3 | Er 3 | switch. | |
| | SW4 | Ery | | |
| Switch range error | | ٤٢٥ | Lower limit of switch output exceeds upper limit. | |
| Pressurization error | | | Pressure exceeding upper limit of set pressure is applied. | |

Descriptions



IC Series

Dimensions





SMC

Applicable panel thickness: 0.5 to 4 mm



IC Series Specific Product Precautions

Be sure to read this before handling the products. Refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smcworld.com

Controller for Electro-pneumatic Regulator

Handling

AWarning

- Do not drop, bump, or apply excessive impacts (980 m/s²) while handling. Although the body of the sensor may not be damaged, the inside of the sensor could be damaged and lead to a malfunction.
- The tensile strength of the cord is 20 N. Applying a greater pulling force on it can cause a malfunction.
 When handling, hold the body of the sensor – do not dangle it from the cord.
- 3. Do not exceed the tightening torque of 3.5 N·m when installing piping. Exceeding this value may cause malfunctioning of the sensor.
- 4. The minimum bending radius of the cable is 50 mm.
- 5. Do not use pressure sensors with corrosive and/or inflammable gases or liquids.

Operating Environment

∆Warning

 This controller for electro-pneumatic regulator is not rated as explosion proof.
Never use it in an atmosphere of corrosive or explosive gas.

≜Caution

1. Only the display unit of the controller for electropneumatic pressure regulator has an enclosure equivalent to IP65 rating. Connection

≜Caution

- 1. Incorrect wiring can damage the switch and cause a malfunction or erroneous switch output. Connections should be done while the power is turned off.
- Do not attempt to insert or pull the pressure sensor or its connector when the power is on. Switch output may malfunction.
- Wire separately from power lines and high voltage lines, avoiding wiring in the same conduit with these lines. Malfunctions may occur due to noise from these other lines.
- 4. If a commercial switching regulator is used, make sure that the F.G. terminal is grounded.

Mounting

A Caution

1. Mounting with panel mount adapter



Tighten screws by 1/4 to 1/2 turn after the heads are flush with the panel.