Diaphragm Type Pilot Operated 2 Port Solenoid Valve for High Pressure VXH Series € ^{ĽK}

Orifice diameter ø10 Max. operating pressure: 2.0 MPa



Valve Specifications

tarte opeenieatione												
Port size	Onlice	Min.operating pressure differential (MPa)	Max. operating pressure differential Note 2) (MPa)		Flow rate characteristics					Note 2) Max.system	Note 1)	
			Water	Air	Oil	Water, Oil		Air			pressure	Weight
						Kv	Cv converted	C[dm ³ /(s·bar)]	b	Cv	(MPa)	(g)
1⁄4						1.6	1.9	8.5	0.35	2.0		550
3⁄8	10	0.05	2.0	2.0	1.5	2.0	2.4	9.5	0.30	2.3	2.0	550
1/2						2.0	2.4	9.5	0.30	2.3		630

Note 1) Weight of grommet type. Add 10 g for conduit type, 30 g for DIN terminal, 60 g for conduit terminal type respectively. Note 2) Refer to "Glossary of Terms" on page 309 for details of max. operating pressure differential and max. system pressure.

Solenoid Specifications

	Frequency	Apparent p	oower (VA)	Power consumption (W)	Temperature rise (°C)	
Power source	(Hz)	Inrush	Holding	(Holding)	(Rated voltage)	
AC	50	53	18	7.5	60	
AC	60	44	12	6	50	

Symbol



When the valve is closed, flow is blocked from port 1 to port 2. However, if the pressure in port 2 is higher than port 1, the valve will not be able to block the fluid and it will flow from port 2 to port 1

How to Order VXH2230-02 G CE/UKCA-compliant 2 port valve Nil for high pressure Q CE/UKCA-compliant * For DIN terminal only Valve/Body Bracket 0 Normally Closed/Single unit Nil None With bracket R Electrical option Nil None Port size S With surge voltage suppressor 02 Rc 1/4 L With indicator light 03 Rc 3/8 With light/surge 04 Rc 1/2 z voltage suppressor * Refer to the table (1) given below for availability. Rated voltage Electrical entry 100 VAC 50/60 Hz 1 G Grommet 200 VAC 50/60 Hz 2 С Conduit 110 VAC 50/60 Hz 3 D DIN terminal 4 220 VAC 50/60 Hz т Conduit terminal 7 240 VAC 50/60 Hz * Refer to the table (1) given below 48 VAC 50/60 Hz 8 for availability. 9 Other (Only AC) Table (1) **Rated Voltage-Electrical Entry-Electrical Option** Insulation type Class B Electrical entry G С D.T S L,Z Electrical option S[№] 1 (100 V) 2 (200 V) • . . • -----3 (110 V) • . . . AC 4 (220 V) . . . •

Note) Surge voltage suppressor is attached in the middle of lead wire.

. . .

. . .

7 (240 V)

8 (48 V)

∧ Caution

Be sure to read this before handling the products.	٦
Refer to back page 50 for Safety Instructions and pages 17 to 19 for 2 Port	!
Solenoid Valve for Fluid Control Precautions.	1

VX2

VXK

VXD

VXZ VXS

VXB

VXE VXP VXR VXH


VXF

VX3


VXA


VXH Series

Construction/Dimensions




No.	Description	Material	Note
1	Body	C37	
2	Bonnet	C37	
3	Coil assembly	Epoxy mold	Class B insulation
4	Core assembly	Stainless steel, Cu	
5	Armature assembly	Stainless steel, NBR	
6	Diaphragm assembly	Stainless steel, NBR	
7	Return spring	Stainless steel	
8	Retainer	Stainless steel	
9	Upset bolt	Stainless steel	
10	Bracket	SPC	Option
11	Wave washer	Stainless steel	
12	Name plate	AL	
13	O-ring	NBR	
14	Terminal assembly	_	
15	Seal	CR	
16	DIN terminal	—	





DIN terminal



Conduit terminal

